



(2,00mm) .0787"

TMM SERIES

TMM-112-01-L-D-RA

TMM-108-03-T-Q

TMM-116-01-F-S

TMM-108-04-S-D

LOW PROFILE THROUGH-HOLE HEADER

SPECIFICATIONS

For complete specifications see www.samtec.com?TMM

Insulator Material:

Black Liquid

Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Sn or Au over 50µ" (1,27µm) Ni

Operating Temp Range:

-55°C to +105°C with Tin;

-55°C to +125°C with Gold

Voltage Rating:

500 VAC mated with SQW

450 VAC mated with SQT

RoHS Compliant:

Yes

Lead-Free Solderable:


Yes



Mates with:
CLT, SQT, SQW, ESQT,
TLE, SMM, MMS,
TCSD, TLSD



APPLICATION



Retention Clip Option (-RC)

Single, double
and quad rowUltra-low profile
(1,50mm) .059"Choice of five
lead styles

APPLICATIONS



HORIZONTAL

CURRENT RATING	
AMBIENT TEMP	Mated with SMM
20°C	3.9A
40°C	3.5A
60°C	3A
95°C	2A


6 POSITIONS (2x3) POWERED

Note: Some lengths, styles and options are non-standard, non-returnable.

Also Available


Press Fit

See PTT Series.




Surface Mount

See TMM Series.




Elevated

See TW Series.




High Density

See TMMH Series.



Shrouded Four Row Vertical & Right Angle

See TMMS Series.






Paste In Hole (PIH) processing.
Contact Samtec ASP Group.


TMM - 1 NO. PINS PER ROW - LEAD STYLE - PLATING OPTION - ROW OPTION - OTHER OPTION

01 thru 50

Specify LEAD STYLE from chart below.



LEAD STYLE	A	B	C
-01	(8,20) .224	(3,20) .126	(3,50) .138
-02	(5,69) .224	(3,70) .146	(3,00) .118
-03	(5,43) .214	(4,00) .158	(2,70) .106
-04	(5,69) .224	(1,91) .075	(2,29) .090
-05	(5,43) .214	(1,65) .065	(2,29) .090
-06	(9,58) .377	(3,20) .126	(4,88) .192



-RC

-F
= Gold flash on post,
Matte Tin on tail

-L
= 10µ" (0,25µm)
Gold on post,
Matte Tin on tail

-S
= 30µ" (0,76µm)
Gold on post,
Matte Tin on tail

-T
= Matte Tin

Note:
Other Gold plating options
available.
Contact Samtec.

-S
= Single Row


-D
= Double Row

-Q
= Four Row





-RA & -RE
= Right Angle
(Lead Style
-01 only)
(2 positions minimum, -Q row)

-RC
= Retention Clip
(Mates with
TCSD)
(Double row only,
4 positions minimum, only
available -06 lead style)

-“XXX”
= Polarized Position
(Specify position
of omitted pin)



-Q-RA



OPTION	D
-RA	(1,27) .050
-RE	(3,56) .140

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292
SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-6083 3766
SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683