



### FEATURES:

- Vertical stacking feature allows endless circuit connections and the right angle design keeps wires close to the chassis.
- An oversized shoulder allows easy connect and disconnect.
- Mates to Model #1581, 2854 or any standard banana jack.

### MATERIALS:

Conn: Right Angle Banana Plug

Material: Spring – Beryllium Copper per QQ-C-533, Alloy 172, Cond. HT.

Plug Body – Brass per QQ-B-626, Alloy 360, ½ Hard.

Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches.

Insulation: Polypropylene molded to plug body and wire. Color matches color of wire.

Marking: "POMONA ELECTRONICS POMONA CALIF."

Wire: 18 AWG stranding 65 x 36 t.c., PVC insulated 3.66 (.144) O.D. Marking: "POMONA 2864-XX-X"

### RATINGS:

Operating Temperature: +55° C. (+131° F.) Max.

Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 5000 WVDC Max.

Current: 15 Amperes

### ORDERING INFORMATION: Model 2864-XX-\*

XX = Cable Lengths, Standard Length: 24"

Additional lengths and colors can be quoted upon request.

\* = Color, -0 Black, -2 Red Ordering Example: 2864-24-2 Indicates 24" in length, color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA