


HE700 D.I.L. Relay Features and Benefits



Features

- Miniature dual in line package
- Choice of normally open, normally closed and change over contacts
- High voltage switching option
- Up to 2 normally open contacts
- Available with 5V, 12V or 24V coil options as standard
- Magnetic shield option
- Diode suppression option
- Diagonal coil option

Benefits

- One relay, various contacts choices reducing space and cost without compromising flexibility
- Lower power coil consumption than competing electromechanical devices.
- Hermetically sealed switching contact is immune to the effects of its environment
- Transfer molded package gives maximum component protection

Applications

- Security
- Telecom
- Instrumentation
- Process Control
- Industrial

DIMENSIONS (in) mm




Figure 1 HE700




Figure 2 HE751





Figure 3 HE700 (All)

Table 1

Relay Type	Body Type	l	w	h
HE700	Transfer Molded External Shield	(.768) 19,50 (.793) 20,14	(.284) 7,22 (.300) 7,62	(.217) 5,50 (.229) 5,82

HE700 PCB LAYOUT (Bottom View)



ORDERING INFORMATION

PART NUMBER

HE7X X X X XX

Model Number

HE72 - Standard
HE75 - High Voltage

Number of Contacts

1,2

General Options

00 - No Options
10 - Coil Suppression Diode
20 - Electrostatic Shield
30 - Coil Diode and E.S. Shield
40 - External Magnetic Shield
50 - External Magnetic Shield and Diode

Contact Type

A - Form A (SPST-NO or DPST-NO)
B - Form B (SPST-NC)
C - Form C (SPDT-CO)
E - Form C (SPDT-CO) alternate foot print 1
R - Form C (SPDT-CO) alternate foot print 2

Standard Coil

05 - 5 Volt
12 - 12 Volt
24 - 24 Volt

EXAMPLE: The HE721A0540 is 1 Form A with a 5 Volt coil and external magnetic shield.








See next page for: **Electrical and Operating Characteristics Description and Coil Characteristics**

Hamlin USA Tel: +1 920 648 3000 • Fax: +1 920 648 3001 • Email: sales.us@hamlin.com
Hamlin Europe Tel: +44 (0)1603 257700 • Fax: +44 (0)1603 257702 • Email: sales.uk@hamlin.com
Hamlin China Tel: +86 (0) 512 69365 800 • Fax: +86 (0) 512 69365 811 • Email: sales.cn@hamlin.com

Table 2 **HE700 Series** Recognised File #E47258  **Electrical and Operating Characteristics @ 25°C.**

Column Number			1	2	3	4
Contact Type			Form A SPST, DPST Standard	Form C SPDT-CO Standard	Form A SPST High Voltage	Form B SPST-NC Standard
Relay Types			HE721, HE722	HE721C, E, R	HE751	HE721
CONTACT RATINGS Contact Hamlin for specific load/life details	Power, Switching Voltage, Switching Current, Switching Current, Carry	Watt - max. Vdc - max. A - max. A - max.	10 200 0.5 1.2	5 175 0.25 1.5	10 300 0.5 1.2	10 200 0.5 1.2
VOLTAGE HOLD-OFF	Across Open Contacts Contacts to Coil Coil to E. Shield Between Isolated Terminals	Vdc - min. Vac - min. Vac - min. Vac - min.	250 500 150 500	200 500 150 N/A	450 4000 N/A N/A	250 500 N/A N/A
RESISTANCE	Contact, Initial Insulation Across Contacts Insulation Between Isolated Terminals	Ω - max. Ω - min. Ω - min.	0.150 10^{10} 10^{10}	0.200 10^{10} 10^{10}	0.150 10^{10} 10^{10}	0.150 10^{10} 10^{10}
TIMING	Operate Time Release Time	ms - max. ms - max.	1.0 1.0	3.0 3.0	1.0 1.0	1.0 1.0
ENVIRONMENTAL	Temperature, Operating Temperature, Storage Vibration Resistance Shock Resistance	°C °C G - max. 10-2000 Hz. G - max. 11 ms ½ sine	-40 to +85 -40 to +105 20 50	-40 to +85 -40 to +105 20 50	-20 to +85 -40 to +105 20 50	-40 to +85 -40 to +105 20 50

Table 3 **HE700 Series Miniature Relay** **Coil Characteristics @ 25°C.**

Contact Form	Electrical & Operating Characteristics	Dimensions	Part Number	Nominal Coil Voltage Vdc	Coil Resistance $\pm 10\%$ Ohms	Must Operate Vdc	Must Release Vdc	Maximum Coil Voltage Vdc	Top View 2,54 mm, 0.1 in. Grid Dot on Case: Pin 1 Numbers not printed on case.
1A SPST-NO	See Table 2 Column 1	Figure 1	HE721A0500 HE721A1200 HE721A2400	5 12 24	500 1000 2150	3.75 8.0 16.0	0.5 1.0 2.0	12 31 46	
1B SPST-NC	See Table 2 Column 4	Figure 1	HE721B0500 HE721B1200 HE721B2400	5 12 24	500 500 2150	3.75 9.0 18.0	0.5 1.0 2.0	6.5 14 28	
1C SPDT-CO	See Table 2 Column 2	Figure 1	HE721C0500 HE721C1200 HE721C2400	5 12 24	200 500 2000	3.75 8.0 16.0	0.5 1.0 2.0	14 22 44	
1C SPDT-CO	See Table 2 Column 2	Figure 1	HE721E0500 HE721E1200 HE721E2400	5 12 24	200 500 2000	3.75 8.0 16.0	0.5 1.0 2.0	14 22 44	
1C SPDT-CO	See Table 2 Column 2	Figure 1	HE721R0500 HE721R1200 HE721R2400	5 12 24	200 500 2000	3.75 8.0 16.0	0.5 1.0 2.0	14 22 44	
2A DPST-NO	See Table 2 Column 1	Figure 1	HE722A0500 HE722A1200 HE722A2400	5 12 24	200 500 2150	3.75 8.0 16.0	0.5 1.0 2.0	12 22 46	
1A SPST-NO High Voltage	See Table 2 Column 3	Figure 2	HE751A0500 HE751A1200 HE751A2400	5 12 24	500 1000 2150	3.75 8.0 16.0	0.5 1.0 2.0	12 31 46	

Notes: 1) HE721B - Exceeding recommended voltage may cause contact reclosure.
2) Optional external magnetic shield not available on Form B relays.

Hamlin USA Tel: +1 920 648 3000 • Fax: +1 920 648 3001 • Email: sales.us@hamlin.com
Hamlin Europe Tel: +44 (0)1603 257700 • Fax: +44 (0)1603 257702 • Email: sales.uk@hamlin.com
Hamlin China Tel: +86 (0) 512 69365 800 • Fax: +86 (0) 512 69365 811 • Email: sales.cn@hamlin.com