

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

Tyco Electronics AMP GmbH

ALL RIGHTS RESERVED.

LOC

DIST

FT

0

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD



CI

REVISED PER ECO-12-007964

02MAY2012

KH

MS



282965-3 AS SHOWN



MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
TERMINAL: COPPER ALLOY, TIN PLATED.



2 SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.

3 RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC., FILE N° E60677.

4 IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.




NOT CUMULATIVE TOLERANCE.



89.64	12	1-282965-2
82.02	11	1-282965-1
74.40	10	1-282965-0
66.78	9	282965-9
59.16	8	282965-8
51.54	7	282965-7
43.92	6	282965-6
36.30	5	282965-5
28.68	4	282965-4
21.06	3	282965-3
13.44	2	282965-2

DIM. A N° OF POS. PART NUMBER


RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±.3
1 PLC ±.25
2 PLC ±.25
3 PLC ±.25
4 PLC ±.25
ANGLES ±.2

MATERIAL



FINISH



DWN E. ZANOLINI 09OCT2001

CHK D. BIEVENOUR 09OCT2001

APVD D. BIEVENOUR 09OCT2001

PRODUCT SPEC

108-20166

APPLICATION SPEC

114-20079

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME
TERMINAL BLOCK HEADER ASSEMBLY
90 DEGREE, OPEN ENDS
7.62mm PITCH

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-282965

SCALE 4:1

SHEET

OF

REV C1