




NOTES:

1. TO BE USED WITH PANDUIT POLYESTER COATED METAL BANDING MBCH.
2. APPLICATION TOOL: GS4MT, ST2MT, PPTMT, ST3MT, OR HTMT.
3. TOOL TENSION SETTING: 4 TO 8 (GS4MT AND PPTMT ONLY)
4. DIMENSIONS IN [] ARE MILLIMETERS.
5. MINIMUM LOOP TENSILE STRENGTH: 250 LBS (1112 N)
6. TOLERANCES: .X = $\pm .030$ [$\pm .762$]
 .XX = $\pm .020$ [$\pm .508$]
 .XXX = $\pm .010$ [$\pm .254$]
 ANGLES = $\pm 2^\circ$



S41212_00

								 PANDUIT CORP. TINLEY PARK, ILLINOIS METAL TIE HEAD HEAVY PART NO. MTHCH-C316 316 STAINLESS STEEL			
00	5/05	JAMB		DRAWING RELEASED	12675						
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	CUST	DRAWN BY	CHK'D	SCALE	DRAWING NO.
								JAMB		4×	S41212