





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		A	REV PER EC 0S12-0647-04	10MAY05	JA	SF
			A1	REVISED PER ECO-09-024927	10NOV09	KK	AEG



1. WIRE RANGE 22-26 AWG.
2. INSULATION RANGE 0.91-1.37 [.036-.054] DIA.
3. PREPLATED 0.00127 [.000050] MIN MATTE TIN IN ZONES I & II, 0.000762 [.000030] MIN GOLD OVER 0.000762 [.000030] MIN NICKEL INLAY IN ZONE III.
4. PREPLATED 0.00127 [.000050] MIN MATTE TIN IN ZONES I & II, 0.00127 [.000050] MIN GOLD OVER 0.000762 [.000030] MIN NICKEL INLAY IN ZONE III.
5. PHOSPHOR BRONZE.
6. ZONE I (OUTSIDE SURFACES).
7. ZONE II (INSIDE SURFACES).
8. ZONE III (INSIDE SURFACES).
9. MAXIMUM CUTOFF.
10. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI




SECTION A-A



SECTION B-B

10	OBSOLETE	4	—5531216—6—	5531216—5
		4	5531216—4	5531216—3
		3	5531216—2	5531216—1
		FINISH	LOOSE PIECE PART NO	STRIP PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ALCORTA - DOCK5 CHK A. FRANTUM APVD S. FLICKINGER		10MAY05 10MAY05 10MAY05		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-25031		NAME CONTACT, RECEPTACLE, LOW PRESSURE MINI-TANDEM SPRING	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13[.005] 4 PLC ± - ANGLES ± -		APPLICATION SPEC 114-25021		RESTRICTED TO	
MATERIAL 5531216-4		FINISH -		WEIGHT -		SIZE A2	
CUSTOMER DRAWING				CAGE CODE 00779		DRAWING NO C=5531216	
				SCALE 4:1		SHEET 1 of 1	
				REV A1			