



I/O MFD 24VDC,Trans., 21 x PT100

Part no.

MFD-TP12-PT-A

Article no.

106042

Program

			Configurable temperature range
Supply voltage			24 V DC
Inputs			
Digital			6
of which can be used as analog			2
Pt100			2
Outputs			
Transistor			4
Temperature range			
Temperature detector			-40...+90 °C 0...+250 °C 0...+400 °C

Approbationen

UL approval
CSA approval
Product Standards

UL File No.
UL CCN
CSA File No.
CSA Class No.
NA Certification
Degree of Protection

Yes
Yes
IEC/EN see Technical Data; UL 508; CSA C22.2 No. 142-M1987; CSA C22.2 No. 213-M1987; CE marking
E135462
NRAQ
012528
2252-01 + 2258-02
UL listed, CSA certified
IEC: IP20, UL/CSA Type: -

General

Standards			EN 61000-6-1/-2/-3/-4, IEC 60068-2-6, IEC 60068-2-27
Dimensions (W x H x D)		mm	89 x 90 x 25 (installed)
Weight		kg	0.14
Mounting			Fitted into the power supply unit.

Terminal capacities

Solid		mm ²	0.24 (AWG 24 - 12)
Flexible with ferrule		mm ²	0.22.5 (AWG 24 - 12)
Standard screwdriver		mm	3.5 x 0.6

Climatic environmental conditions

Operating ambient temperature		°C	-25 to 55, cold as per IEC 60068-2-1, heat as per IEC 60068-2-2
Condensation			Take appropriate measures to prevent condensation
Storage		°C	- 40 - 70
Relative humidity, non-condensing (IEC/EN 60068-2-30)		%	5 - 95
Air pressure (operation)		hPa	795 - 1080

Ambient conditions, mechanical

Pollution degree			2
Protection type (IEC/EN 60529, EN50178, VBG 4)			IP20
Vibrations (IEC/EN 60068-2-6)		Hz	
Constant amplitude 0.15 mm		Hz	10 - 57
Constant acceleration 2 g		Hz	57 - 150
Mechanical shock resistance (IEC/EN 60068-2-27) semi-sinusoidal 15 g/11 ms		Impacts	18
Drop to IEC/EN 60068-2-31	Drop height	mm	50
Free fall, packaged (IEC/EN 60068-2-32)		m	1
Mounting position			Vertical or horizontal

Electromagnetic compatibility (EMC)

Electrostatic discharge (IEC/EN 61000-4-2, Level 3, ESD)		kV	
Air discharge		kV	8

Contact discharge		kV	6
Electromagnetic fields (RFI), to IEC EN 61000-4-2		V/m	10
Radio interference suppression			EN 55011 Class B, EN 55022 Class B
Burst Impulse (IEC/EN 61000-4-4, Level 3)			
Supply cables		kV	2
Signal lines		kV	2
Power pulses (surge) (IEC/EN 61000-4-5)		kV	2 (supply cables, symmetrical)
power pulses (surge) (IEC/EN 61000-4-5, level 2)		kV	0.5 (supply cables, symmetrical)
Radiated RFI (IEC/EN 61000-4-6)		V	10

Insulation resistance

Clearance in air and creepage distances			EN 50178, UL 508, CSA C22.2, No. 142
Insulation resistance			EN 50178

Digital inputs 24 V DC

Number			6
Inputs can be used as analog inputs			2 (I11, I12)
Potential isolation			
From power supply			No
Between digital inputs			No
From the outputs			Yes
to PC interface, memory card, easyNet, easyLink			Yes
Rated operational voltage	U _e	V DC	24
On 0 signal	U _e	V DC	< 5.0 (I1 - I4) < 8.0 (I11, I12)
On 1 signal	U _e	V DC	>15.0 (I1 - I4) > 8.0 (I11, I12)
Input current on 1 signal			
I11, I12		mA	2.2 (at 24 V DC)
Delay time from 0 to 1		ms	
Debounce ON		ms	20
Debounce OFF		ms	Normally 0.1 (I1 - I4), Normally 0.25 (I11 - I12)
Delay time from 1 to 0		ms	
Debounce ON		ms	20
Debounce OFF		ms	Normally 0.1 (I1 - I4), normally 0.2 (I11, I12)
Cable length (unscreened)		m	100
Frequency counter			
Quantity			4 (I1, I2, I3, I4)
Counter frequency		kHz	< 3
Pulse shape			Square
Incremental counter			
Quantity			2 (I1 + I2, I3 + I4)
Counter frequency		kHz	≤ 3
Pulse shape			Square
Signal offset			90°
Rapid counter inputs			
Number			4 (I1, I2, I3, I4)
Counter frequency		kHz	< 3
Pulse shape			Square
Cable length, screened		m	< 20

Analog inputs

Potential isolation			
From power supply			No
From the digital inputs			No
From the outputs			Yes
for Program code			Yes
Input type			DC voltage

Signal range		V DC	0 - 10
Resolution, analog		V	0.01
Resolution, digital		V	0.01
Resolution		Bit	10 (value 0 - 1023)
Input impedance		kΩ	11.2
Accuracy of actual value			
two MFD devices		%	± 3
Within a single device		%	± 2
Conversion time, analog/digital		ms	Each CPU cycle
Input current		mA	< 1
Cable length screened		m	< 30

Analog inputs temperature resistance Pt100 or Ni1000 sensors

Number			2 x Pt 100 or 2 x Ni1000 (according to part no.)
Input type resistance sensor			Platinum sensor Pt100 according to DIN EN 60751, IEC 751: MFD-TP12-PT... Nickel sensor Ni1000 according to DIN 43760: MFD-TP12-NI...
Temperature range		°C, (°F)	Pt100, area A, selectable: -40 - +90, (-40 - 194); 0 - 250 (32 - 482); 0 - 400, (32 - 752) Ni1000, area A, selectable: -40 - +90, (-40 - 194); 0 - 250 (32 - 482) Pt100, area B: -0 - +8500, (32 - 1562); -200 - 200 (-328 - 392)
Potential isolation			
From power supply			No
From the digital inputs			No
From the outputs			Yes
to PC interface, memory card, easyNet, easyLink			Yes
Resolution digital, scaling per sensor			With operands "IA" and "MD", selectable under scaling: 12 (0- 4095) Bit With operand "MD", selectable under scaling: 1, 0.1 °C (1, 0.1 °F)
Measurement value resolution analog/digital		Bit	Depending upon the scaling
Measuring current		mA	< 1.6
Damage limit (in the case of a wiring error)			Apply external voltage
Measuring principle			Two or three wire per sensor, selectable by connection of sensor
Accuracy (without electromagnetic compatibility interference)		%	Two MFD devices between each other: Typically 1; max. 1.6 (Pt), 1.2 (Ni) Pt100 sensor (offset error, linearity error, repetition accuracy, temperature error of device included): ± 0.8 of measuring range Ni1000 sensor (offset error, linearity error, repetition accuracy, temperature error of device included): ± 0.8 of measuring range
Conversion time, analog/digital		ms	without sampling time setting, selectable per sensor: 200 with sampling time (adjustable), selectable per sensor: 200 - 65535
additional measurement aids			Filtering (software), smoothing of analog input signal (PT1 behavior), only with set sampling time, selectable per sensor: yes Filter for the suppression of certain frequencies and their multiples: 50, 60, 250, 500 Hz
Diagnostics			Card diagnostic: yes Wire break diagnostic per sensor: yes Wire break diagnostic per sensor: yes below lower measurement range: yes Upper sensor measuring range exceeded: yes
Cable length screened		m	< 10

Transistor outputs

Number			4
Rated operational voltage	U _e	V DC	24
Admissible range	U _e	V DC	20.4 - 28.8
Supply current			
On 0 signal	Normally/m:	mA	18/32
On 1 signal	Normally/m:	mA	24 /44
Protection against polarity reversal			yes (Caution: A short circuit will result if 0 V or earth is applied to the outputs in the event that the supply voltage is connected to the wrong poles.)
Potential isolation			
Potential isolation of the power supply, inputs			Yes
From the inputs			Yes
to PC interface, memory card, easyNet, easyLink			Yes

Rated operational current at signal „1“ DC per channel	I_e	A	max. 0.5
Lamp load without R_v per channel		W	5 (Q1 - Q4)
Residual current on 0 signal per channel		mA	< 0.1
Max. output voltage			
On 0 signal with external load < 10 M Ω		V	2.5
On 1 signal with $I_e = 0.5$ A		V	$U = U_e - 1$ V
Short-circuit protection			Thermal (Q1 - Q4), (evaluation with diagnostics input I16)
Short-circuit tripping current for $R_a \leq 10$ m Ω		A	$0.7 \leq I_e \leq 2$ per output
Total short-circuit current		A	8
Peak short-circuit current		A	16
Thermal cutout			Yes
Max. operating frequency with constant resistive load $R_L < 100$ k Ω (depending on number of active channels and their load)		Ops./h	40000
Parallel connection of outputs			
With resistive load, inductive load with external suppressor circuit, combination within a group			Group 1: Q1 to Q4
Number of outputs	max.		4
Total max. current		A	2 (Caution! Outputs must be switched simultaneously and for the same period.)
Inductive load to EN 60947-5-1			
Without external suppressor circuit			
$T_{0.95} = 1$ ms, $R = 48$ Ω , $L = 16$ mH			
Utilization factor		g	0.25
Duty factor		% DF	100
Max. switching frequency $f = 0.5$ Hz (max. DF = 50 %)		Operations	≤ 500
DC-13, $T_{0.95} = 72$ ms, $R = 48$ Ω , $L = 1.15$ H			
Utilization factor		g	0.25
Duty factor		% DF	100
Max. switching frequency $f = 0.5$ Hz (max. DF = 50 %)		Operations	≤ 500
$T_{0.95} = 15$ ms, $R = 48$ Ω , $L = 0.24$ H			
Utilization factor		g	0.25
Duty factor		% DF	100
Max. switching frequency $f = 0.5$ Hz (max. DF = 50 %)		Operations	≤ 500
With external suppressor circuit			
Utilization factor		g	1
Duty factor		% DF	100
Max. switching frequency, max. duty factor		Operations	Depending on the suppressor circuit

Analog outputs

Potential isolation			
From power supply			No
From the digital inputs			No

Point-to-point connection


Potential isolation			
From power supply			Yes

Technical data according to ETIM 4.0

Output, voltage			YES
Number of outputs			4
Input, resistance thermometer			No
Number of inputs			6
Output, current			No
Input, voltage			No
Input, current			No
Output signal configurable			YES

Input, resistance		No
Resolution of the analog inputs	bit	12
Resolution of the analog outputs	bit	0
Width	mm	90
Depth	mm	89
Height	mm	44
Input signal configurable		YES
Input, thermocouple		YES

Dimensions



Additional product information (links)

IL05013020Z (IL05013020Z) MFD-Titan Temperature module	ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL05013020Z2010_11.pdf
AWB2528-1480 (MN05002001Z-EN) Multi-Function display - italiano	ftp://ftp.moeller.net/DOCUMENTATION/AWB_MANUALS/h1480i.pdf
AWB2528-1480 (MN05002001Z-EN) Multi-Function display - English	ftp://ftp.moeller.net/DOCUMENTATION/AWB_MANUALS/h1480g.pdf
AWB2528-1480 (MN05002001Z-EN) Multi-Function display - français	ftp://ftp.moeller.net/DOCUMENTATION/AWB_MANUALS/h1480f.pdf
AWB2528-1480 (MN05002001Z-EN) Multi-Function display - Deutsch	ftp://ftp.moeller.net/DOCUMENTATION/AWB_MANUALS/h1480d.pdf
Engineering	
Overview of functions	ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/Funktionen_easy_MFD_G.pdf
Labeleditor	ftp://ftp.moeller.net/MFD/EASY-SOFT-PRO/labeleditor_206.exe