

HCMOS SURFACE-MOUNT CRYSTAL CLOCK OSCILLATOR

ASA SERIES

Moisture Sensitivity Level (MSL) – This product is
Hermetically Sealed and not Moisture Sensitive -
MSL = N/A: Not Applicable



RoHS/RoHS II Compliant



2.0 x 1.6 x 0.7mm

FEATURES:

- Ultra miniature package, 2.0 x 1.6 x 0.7mm
- Tri-state function
- Suitable for high density SMT
- Suitable for RoHS compliant reflow process
- Seam sealed package assures high reliability

APPLICATIONS:

- CCD clock for VTR camera
- Computers and peripherals
- Portable electronics
- Mobile communication, PDA

STANDARD SPECIFICATIONS:

Parameters		Minimum	Typical	Maximum	Units	Notes	
Frequency Range		1.0		80	MHz		
Operating Temperature		-10		+60	°C	See options	
Storage Temperature		-40		+85	°C		
Overall Frequency Stability*		-50		+50	ppm	See options	
Supply Voltage (Vdd)		2.97	3.3	3.66	V	Standard	
		2.25	2.5	2.75		Option 1 (CMOS)	
		1.62	1.8	1.98		Option 2 (CMOS)	
Supply Current (I _{dd}) into 15pF Load	Vdd = 3.3 V		2.0	5.0	mA	1MHz ≤ F ≤ 20 MHz	
			4.0	10.0		20 MHz < F ≤ 50 MHz	
			7.0	15.0		50 MHz < F ≤ 80 MHz	
	Vdd = 2.5 V		2.0	5.0		1MHz ≤ F ≤ 20 MHz	
			3.0	10.0		20 MHz < F ≤ 50 MHz	
			5.0	10.0		50 MHz < F ≤ 80 MHz	
	Vdd = 1.8 V		1.5	5.0		1MHz ≤ F ≤ 20 MHz	
			2.5	5.0		20 MHz < F ≤ 50 MHz	
			4.0	10.0		50 MHz < F ≤ 80 MHz	
	Output Load				15	pF	
					2	TTL	
Output Voltage	V _{OH}	0.9*Vdd			V	CMOS	
	V _{OL}			0.1*Vdd		CMOS	
	V _{OH}	2.4				TTL	
	V _{OL}			0.4		TTL	
Tri-state function		"1" (VIH≥0.7*Vdd) or Open : Oscillation "0" (VIH<0.3*Vdd) : Hi Z					
Aging		-3.0		+3.0	ppm	@+25°C First year	
Symmetry @1/2Vdd		40	50	60	%	Standard	
		45	50	55		Option S	
Start-up Time				10.0	ms		
Rise/Fall Time (Tr/Tf)				10.0	ns		

*Overall frequency stability includes initial frequency tolerance @+25°C and stability over the operating temperature.

OPTIONS AND PART IDENTIFICATION:

(Left blank if standard)

ASA - MHz - - - -

Supply Voltage
Blank: 3.3V±10%
1: 2.5 V±10%
2: 1.8 V±10%

Packaging
Blank: Bulk
T: Tape & Reel (1kpcs)
T3: Tape & Reel (3kpcs)

Frequency in MHz
Please specify the frequency in MHz. e.g. 14.31818MHz

Operating Temp.
Blank: -10°C ~ +60°C
E: -20°C ~ +70°C
L: -40°C ~ +85°C

Overall Freq. Stability
Blank: ±50ppm
R**: ±25ppm
K***: ±30 ppm

Symmetry
Blank: 40/60% @1/2Vdd
S: 45/55% @1/2Vdd

**Available for -10 to +60°C only

***Available for -10 to +60°C, option E only

Contact Abracon for tighter frequency stability options

ABRACON IS
ISO9001:2008
CERTIFIED



ABRACON
CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale **Revised: 01.24.14**

30332 Esperanza, Rancho Santa Margarita, California 92688

tel 949-546-8000 | fax 949-546-8001 | www.abracon.com

 **RoHS/RoHS II Compliant**

PIN #	Name
1	Tri-state
2	GND
3	Output
4	Vdd

[illegible]

Figure 1 is a graph showing a typical reflow profile. The Y-axis represents Temperature (°C) and the X-axis represents Time (seconds). The profile starts at 25°C, rises to 150°C (Pre-Heat), then to 260°C (Reflow), and finally cools down. Key parameters include: 60~120s for Pre-Heat, 30~40s for Reflow, and 60~90s for Cool. A maximum dwell time of 5s at 260°C±5°C is specified.



ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.