


MICRO SWITCH
a Honeywell Division




FED. MFG. CODE 91929

SWITCH-ENCLOSED

CATALOG LISTING
622EN18-6B



CIRCUIT DIAGRAM




NOTES

- 1 - CORROSION RESISTANT STEEL ENCLOSURE
- 2 - SWITCH SEALED PER MIL-S-8805 SYMBOL 4
- 3 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
- 4 - CIRCUIT DIAGRAM, AND CATALOG LISTING SHOWN ON NAMEPLATE
- 5 - TO ADJUST ROLLER DIRECTION, REMOVE LOCK NUT, SCREW, AND ROLLER. DEPRESS PLUNGER UNTIL IT CAN BE ROTATED TO DESIRED POSITION. RETURN PLUNGER TO FREE POSITION AND REASSEMBLE ROLLER
- 6 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

THIRD ANGLE PROJECTION



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT

CHARACTERISTICS

OPERATING FORCE ——— 6 -12 LB
FULL OVERTRAVEL FORCE — 30 LB MAX
RELEASE FORCE ——— 4 LB MIN
PRETRAVEL ——— .040 MAX
DIFFERENTIAL TRAVEL — .020 MAX
OVERTRAVEL ——— .125 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
2X S P D T

LOAD	28 VDC	
	SEA LEVEL	50,000 FT.
RES	7	7
IND	4	2.5
MOTOR	4	

ANSI Y14.5M-1982 APPLIES

622EN18-6B

M

DRAWING
NUMBER

1

ISSUE

REPLACES

RELEASE NO. PR-19556

CHECK

REVISIONS

CHECK

17 SEP '91

DRAW

CHECK

16 SEP 91

DDM/CAD
DRAWN