




I-Net Profibus M12
360° EMI/RFI IP 67
Crimp für Feldkonfektion

I-Net Profibus M12
360° EMI/RFI IP 67
Crimp for field assembly



Bestell-Informationen / Ordering information								
Artikel-Nummern <i>Item numbers</i>		Bus-Interface	Kabelanschluss <i>Cable connection</i>		Kabelabgang <i>Cable exit</i>			Gedrehte Crimpkontakte <i>Turned crimp contacts</i>
Stift-version <i>Pin version</i>	Buchsen-version <i>Socket version</i>	M12	Crimp-flansch <i>Crimp flange</i>	Kabel-klemme <i>Cable clamp</i>	35°	90°	180°	
42-100001	42-100002	B-Code	x				x	x
42-100003	42-100004	B-Code	x				x	

Crimp-Kontakte / Crimp contacts

(für Steckverbinder ohne Kontakte/*for connectors without contacts*)

Gedrehte Crimpkontakte / Turned crimp contacts

Stiftversion / *Male version* **C052200G2**, Buchsenversion / *Female version* **C062200G2**

Andere Oberfläche auf Anfrage / *other plating upon request*

I-Net Profibus M12
360° EMI/RFI IP 67
Verbindungsleitungen

I-Net Profibus M12
360° EMI/RFI IP 67
Patch cords

Bestell-Informationen / Ordering information									
Artikel-Nummern Item numbers			Bus-Interface	Kabel-länge Cable length A	Kabel-abgang Cable exit		Anschlussart Termination style		
Verbindungsleitung Patch cord									
Stift/Buchse Male/Female	Buchse/ Buchse Female/ Female	Stift/Stift Male/Male	M12	in m	90°	180°	Kontakt Contact	Kabel-schirm Cable shield	
420-1000000	420-1000050	420-1000100	B-Code	0,3		x	Crimp	Crimp	
420-1000001	420-1000051	420-1000101	B-Code	0,5		x	Crimp	Crimp	
420-1000002	420-1000052	420-1000102	B-Code	0,75		x	Crimp	Crimp	
420-1000003	420-1000053	420-1000103	B-Code	1		x	Crimp	Crimp	
420-1000004	420-1000054	420-1000104	B-Code	1,5		x	Crimp	Crimp	
420-1000005	420-1000055	420-1000105	B-Code	2		x	Crimp	Crimp	
420-1000006	420-1000056	420-1000106	B-Code	2,5		x	Crimp	Crimp	
420-1000007	420-1000057	420-1000107	B-Code	3		x	Crimp	Crimp	
420-1000008	420-1000058	420-1000108	B-Code	4		x	Crimp	Crimp	
420-1000009	420-1000059	420-1000109	B-Code	5		x	Crimp	Crimp	
420-1000010	420-1000060	420-1000110	B-Code	10		x	Crimp	Crimp	

I-Net Profibus M12
360° EMI/RFI IP 67
Abschluss-Stecker

I-Net Profibus M12
360° EMI/RFI IP 67
Termination Connectors

Bestell-Informationen / Ordering information					
Artikel-Nummern <i>Item numbers</i>		Bus-Interface	Kabelabgang <i>Cable exit</i>		
Stiftversion <i>Pin version</i>	Buchsenversion <i>Socket version</i>	M12	35°	90°	180°
42-100005	42-100006	B-Code			x