





- Low profile DIP socket, sits only .122" above the PCB.
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 218 for details.
- Series 115 use MM #0501 pins. See page 133 for details.
- Insulators are high temperature thermoplastic.



Total number of pins				Quantity per tube	Ordering Information			
	A	B	C					
10	0.5	0.2	0.3	41	115-XX-210-41-001000	 For RoHS compliance select plating code.		
4	0.2	0.3	0.4	102	115-XX-304-41-001000			
6	0.3	0.3	0.4	67	115-XX-306-41-001000			
8	0.4	0.3	0.4	50	115-XX-308-41-001000			
10	0.5	0.3	0.4	40	115-XX-310-41-001000			
14	0.7	0.3	0.4	28	115-XX-314-41-001000			
16	0.8	0.3	0.4	25	115-XX-316-41-001000			
18	0.9	0.3	0.4	22	115-XX-318-41-001000			
20	1.0	0.3	0.4	20	115-XX-320-41-001000			
22	1.1	0.3	0.4	18	115-XX-322-41-001000			
24	1.2	0.3	0.4	16	115-XX-324-41-001000			
28	1.4	0.3	0.4	14	115-XX-328-41-001000			
20	1.0	0.4	0.5	20	115-XX-420-41-001000			
22	1.1	0.4	0.5	18	115-XX-422-41-001000			
24	1.2	0.4	0.5	16	115-XX-424-41-001000			
28	1.4	0.4	0.5	14	115-XX-428-41-001000			
32	1.6	0.4	0.5	12	115-XX-432-41-001000			
24	1.2	0.6	0.7	16	115-XX-624-41-001000			
28	1.4	0.6	0.7	14	115-XX-628-41-001000			
32	1.6	0.6	0.7	12	115-XX-632-41-001000			
36	1.8	0.6	0.7	11	115-XX-636-41-001000			
40	2.0	0.6	0.7	10	115-XX-640-41-001000			
42	2.1	0.6	0.7	9	115-XX-642-41-001000			
48	2.4	0.6	0.7	8	115-XX-648-41-001000			
50	2.5	0.6	0.7	8	115-XX-650-41-001000			
52	2.6	0.6	0.7	7	115-XX-652-41-001000			
50	2.5	0.9	1.0	8	115-XX-950-41-001000			
52	2.6	0.9	1.0	7	115-XX-952-41-001000			
64	3.2	0.9	1.0	6	115-XX-964-41-001000			

SPECIFY PLATING CODE XX=				93			43	
Sleeve (Pin)				200μ" Sn/Pb			200μ" Sn	
Contact (Clip)				30μ" Au			30μ" Au	