

Ceramic Double Row Terminal Blocks


TYPE 339-K (F)

20 mm spacing - 2 poles

Inventory Check



RoHS WEEE Pb free compliant




Description

The double terminal are screwed to the socket and cast at the base for insulation and mechanical fastening purposes.

Recommended mounting hardware: M4 pan head screw (#10-24 fillister head screw)

- Ceramic Double Row Terminal Block
- Medium Duty
- With Clamping Screws
- With Mounting Holes
- With Spring Washers and Plain Washers



Dimensions: mm (in.)

Technical Data

Center to Center Spacing: 20 mm (0.790 in.)

Nominal Cross Section:

4 mm² (6199 mils²)

Wire Stripping Length: 10 mm (0.39 in.)

(maximum load at 40°C (104°F) ambient temperature)

Recommended operating

Voltage: 400 V

Recommended operating

Current: 34A

Recommended operating Wire

Range: 18-12 AWG

L = 33.0 (1.30)

W = 24.0 (0.95)

M = 12.0 (0.47)

A = 20.0 (0.79)

H = 18.0 (0.71)

(version F):

H = 20.0 (0.79)

When locating connector, allow 0.5 mm clearance around it for process-induced variations.

Approval Information

Screw Tightening Torque:

10.0

Material

Molding: Steatite KER 220, DIN 40685, color white

Temperature upper limit: 200°C (392°F)

Terminal Body: Nickel plated brass

Screw: M4, Zinc plated blue passivated, steel substrate

Item	339-K (F)
Options	<input type="checkbox"/> G05: Gold Plating (5 micro inches) <input type="checkbox"/> G30: Gold Plating (30 micro inches) <input type="checkbox"/> S30: Silver Plating (30 micro inches) <input type="checkbox"/> BS: Copper Alloy Screws

Ordering Note: Plated component: terminal body

Accessories

SPRING WASHERS (DIN 127) AND PLAIN WASHERS:
with: F

339-K

