



DIMENSIONS:

A	2.813" ±0.063
B	3.313" ±0.125
C	3.421" ±0.063
D	2.250" ±0.063
E	2.125" ±0.063
G	0.203" x 0.375" ±0.015



NOTE: ALL LEADS 8" OUT MIN. STRIPPED 0.5"

PRIMARY SECONDARY



GRY - ELECTROSTATIC SHIELD 50/60Hz

ELECTRICAL DATA:

TESTS	CONDITIONS	ACCEPTANCE CRITERIA	
I _{ex}	@ 120V, 60Hz, WHT - BLK	83mA	Max.
Sec. N.L.V	@ 120V, 60Hz, WHT - BLK		
	RED - RED =	542.0V	±2%
	RED - RED/YEL = RED/YEL - RED =	271.0V	±2%
	RED/YEL - VIO =	51.25V	±2%
	YEL - YEL =	5.500V	±2%
	YEL - YEL/BLK = YEL/BLK - YEL =	2.750V	±2%
	GRN - GRN =	7.000V	±2%
	GRN - GRN/YEL = GRN/YEL - GRN =	3.500V	±2%
DCR	@ 20°C, WHT - BLK =	12.12 Ω	±20%
	@ 20°C, BRN - BLU =	13.10 Ω	±20%
	@ 20°C, RED - RED =	264.5 Ω	±20%
	@ 20°C, YEL - YEL =	0.110 Ω	±20%
	@ 20°C, GRN - GRN =	0.146 Ω	±20%
HIPOT	PRIMARY - SECONDARY	2500V, 60Hz, 1 SEC	

REV.#	REVISION	DATE	HAMMOND ELECTRONIC DIVISION			
0	RELEASED.	08/17/12	52 RANKIN PLACE, WATERLOO, ONTARIO, N2J 3Z5			
			PH # (519) 886-6181			
			FAX # (519) 886-9540			
			DWG. BY: C. ILIE	CHK'D BY:	TITLE: POWER TRANSFORMER	DWG. NO. 370CAX
			DATE: 08/17/12	APP'D. BY:		
				DIMENSIONS: IN(X) MM()		