


Specifications:

connector description (1)	dc plug, 5.5x2.5xL22.5 mm, molding style, brass nickel plated, P/N 50-00130
overmold (2,5)	30P, PVC, black
connector description (6)	dc jack, 5.5x2.5xL17.4 mm, molding style, P/N 50-00027
wire description (3)	2C, 18 AWG, UL2468, 300V, 80C, 4.4 mm, VW-1, PVC, 48P, P/N 30-00007
cable outer diameter	Ø4.4 mm
cable color	black
cable length	915 ± 50 mm
twist tie (4)	black
rating	3 A, 36 Vdc

Notes:

Function test: no open, no reversed polarity, no short circuit, no INT  
RoHS compliant  
Hi-Pot test: 600 Vac, 0.5 mA, 1 second

Mechanical drawing:



tolerance X:  $\pm 0.5$  mm .X:  $\pm 0.3$  mm .XX:  $\pm 0.05$  mm  
applicable unless otherwise indicated in specification or on drawings  
Tensility International Corporation reserves the right to substitute  
parts which are functionally equivalent to the ones specified.

Initial	Date
---------	------

**Revision notes:**

Rev	Date	Description
A	January 19, 2009	Re-issued; original specification issued by CUI, re-issued by Tensility without any material or mechanical changes.
A1	August 31, 2011	updated description, connector, and wire information
A2	September 10, 2013	updated connector

<b>Prepared:</b>	<b>Verified:</b>

**Specification Approval**

Spec sign-off verifies that you have reviewed the entire specification, tested a sample of the product, and confirm that it meets your requirements. This specification reflects the part as it will be ordered. Orders will not be processed until the specification pages have been initialed and the approval page has been signed. This specification is confidential and is not to be transmitted without prior approval from Tensility.

Signature \_\_\_\_\_

Title \_\_\_\_\_

Name \_\_\_\_\_

Date \_\_\_\_\_

Company \_\_\_\_\_

Branch \_\_\_\_\_