


C200H - LK201
3G2C7 - LK201
3G2A6 - LK201
CV500 - LK201 (Port 1)



25-pin

Cable Part Number

C500 - CN221 - EU



AT Computer (9-pin)

SD 2 ————— **2 RD**


RD 3 ————— **3 SD**

SG 7 ————— **5 SG**


RTS 4 

CTS 5


DTR 20

 **4 DTR**

6 DSR

 **7 RTS**

8 CTS



CABLE C500-CN221-EU

1. DB-25 MALE CONNECTOR WITH SOLDER CUPS
2. DE-9 FEMALE CONNECTOR WITH SOLDER CUPS
3. 3 CONDUCTOR, 24 AWG STRANDED, FOIL SHIELD, PVC JACKETED CABLE
4. OMRON DB-25 BACKSHEL W/ 2.6MM JACK SCREWS, P/N XM2S-2511
5. OMRON DE-9 BACKSHELL W/ #4-40 JACK SCREWS, P/N XM2S-0913
6. HEAT SHRINK TUBING TO COVER SOLDERED CONNECTION, BOTH ENDS
7. HEAT SHRINK TUBING, WHITE WITH PRINTED PART NUMBER AS SHOWN IN BLACK, 8 PT. HELVETICA. POSITION APPROXIMATELY AS SHOWN.

	FROM #1 PIN	TO #2 PIN	
TXD	2	2	RXD
RXD	3	3	TXD
	*4 to 5	nc	
	nc	*4 to 6	
	nc	*7 to 8	
COM	7	5	COM
	1 to SHIELD	nc	

* PIN TO PIN JUMPERS

-	-	-	-	-	APPROVAL	DATE	MATERIAL: -		C500 BASIC/ASCII/LINK TO IBM-AT COMPUTER CABLE	
-	-	-	-	-	DRWN	11-2-94				
-	-	-	-	-	CHCKD -		-	TOLERANCE: -		DRWG NO: PFP0015A
-	-	-	-	-		APRVD -				-
-	-	-	-	-			SCALE: NONE		SIZE: A	
REV	DESCRIPTION	COS NO.	DATE	SGND	-	-	SHEET: 1 OF 1		 Omron Electronics, Inc. Omron Manufacturing of America	


C200H - LK201
3G2C7 - LK201
3G2A6 - LK201
CV500 - LK201 (Port 1)



25-pin

Cable Part Number

C500 - CN222 - EU



XT Computer (25-pin)

SD 2 ————— **3 RD**

RD 3 ————— **2 SD**

SG 7 ————— **7 SG**

RTS 4 

CTS 5


DTR 20

 **6 DSR**

20 DTR

 **4 RTS**

5 CTS



CABLE C500-CN222-EU


1. DB-25 MALE CONNECTOR WITH SOLDER CUPS
2. DB-25 FEMALE CONNECTOR WITH SOLDER CUPS
3. 3 CONDUCTOR, 24 AWG STRANDED, FOIL SHIELD, PVC JACKETED CABLE
4. OMRON DB-25 BACKSHELL W/ 2.6MM JACK SCREWS, P/N XM2S-2511
5. OMRON DB-25 BACKSHELL W/ #4-40 JACK SCREWS, P/N XM2S-2513
6. HEAT SHRINK TUBING TO COVER SOLERED CONNECTION, BOTH ENDS
7. HEAT SHRINK TUBING, WHITE WITH PRINTED PART NUMBER AS SHOWN IN BLACK, 8 PT. HELVETICA. POSITION APPROXIMATELY AS SHOWN.

	FROM #1 PIN	TO #2 PIN	
TXD	2	3	RXD
RXD	3	2	TXD
	*4 to 5	nc	
	nc	*6 to 20	
	nc	*4 to 5	
COM	7	7	COM
	1 to SHIELD	nc	

* PIN TO PIN JUMPERS

-	-	-	-	-	APPROVAL	DATE	MATERIAL: -		C500 BASIC/ASCII/LINK TO IBM-XT COMPUTER CABLE	
-	-	-	-	-	DRWN	OBA	11-2-94	FINISH: -		
-	-	-	-	-	CHCKD			-	-	DRWG NO: PFP0016A
-	-	-	-	-	APRVD	-	-			FILE NAME: -
-	-	-	-	-	APRVD			-	-	SIZE: A
REV	DESCRIPTION	COS NO.	DATE	SGND	-	-	TOLERANCE: -			UNITS: ENGLISH
									SCALE: NONE	
							SHEET: 1 OF 1		omron Omron Electronics, Inc. Omron Manufacturing of America	


CV500 - LK201 (Port 2)
 CVM1 built-in Hostlink
 C200HS built-in Hostlink
 CQM1 built-in Hostlink
 IDSC built-in Hostlink




9-pin


Cable Part Number

C200HS - CN220 - EU



AT Computer (9-pin)





CABLE C200HS-CN220-EU


1. DE-9 MALE CONNECTOR WITH SOLDER CUPS
2. DE-9 FEMALE CONNECTOR WITH SOLDER CUPS
3. 3 CONDUCTOR, 24 AWG STRANDED, FOIL SHIELD, PVC JACKETED CABLE
4. OMRON DE-9 BACKSHELL W/ 2.6MM JACK SCREWS, P/N XM2S-0911
5. OMRON DE-9 BACKSHELL W/ #4-40 JACK SCREWS, P/N XM2S-0913
6. HEAT SHRINK TUBING TO COVER SOLDERED CONNECTION, BOTH ENDS
7. HEAT SHRINK TUBING, WHITE WITH PRINTED PART NUMBER AS SHOWN IN BLACK, 8 PT. HELVETICA. POSITION APPROXIMATELY AS SHOWN.

	FROM #1 PIN	TO #2 PIN	
TXD	2	2	RXD
RXD	3	3	TXD
	*4 to 5	nc	
	nc	*4 to 6	
	nc	*7 to 8	
SG	9	5	SG
	1 to SHIELD	nc	

* PIN TO PIN JUMPERS


-	-	-	-	-	APPROVAL	DATE	MATERIAL: -	HOST LINK PORT TO IBM-AT COMPUTER CABLE	
-	-	-	-	-	DRWN OBA	10-26-94	FINISH: -		
-	-	-	-	-	CHCKD -	-	TOLERANCE: -	DRWG NO: PFP0010A	FILE NAME: -
-	-	-	-	-	APRVD -	-	UNITS: ENGLISH	SCALE: NONE	SIZE: A
REV	DESCRIPTION	COS NO.	DATE	SGND	-	-	SHEET: 1 OF 1	omron Omron Electronics, Inc. Omron Manufacturing of America	

All C**H Series
PLC's




9-pin


**Omron does not make a cable
for this configuration**



AT Computer (9-pin)




CVM1 built-in Hostlink
 C200HS built-in Hostlink
 CQM1 built-in Hostlink



9-pin

Cable Part Number

C200HS - CN229 - EU



XT Computer (25-pin)

SD 2 _____ **3 RD**


RD 3 _____ **2 SD**

SG 9 _____ **7 SG**

RTS 4 
CTS 5

 **6 DSR**
20 DTR

 **4 RTS**
5 CTS



CABLE C200HS-CN229-EU


1. DE-9 MALE CONNECTOR WITH SOLDER CUPS
2. DE-25 FEMALE CONNECTOR WITH SOLDER CUPS
3. 3 CONDUCTOR, 24 AWG STRANDED, FOIL SHIELD, PVC JACKETED CABLE
4. OMRON DE-9 BACKSHELL W/ 2.6MM JACK SCREWS, P/N XM2S-0911
5. OMRON DE-25 BACKSHELL W/ #4-40 JACK SCREWS, P/N XM2S-2513
6. HEAT SHRINK TUBING TO COVER SOLDERED CONNECTION, BOTH ENDS
7. HEAT SHRINK TUBING, WHITE WITH PRINTED PART NUMBER AS SHOWN IN BLACK, 8 PT. HELVETICA. POSITION APPROXIMATELY AS SHOWN.

	FROM #1 PIN	TO #2 PIN	
TXD	2	3	RXD
RXD	3	2	TXD
	*4 to 5	nc	
	nc	*6 to 20	
	nc	*4 to 5	
SG	9	7	SG
	1 to SHIELD	nc	

* PIN TO PIN JUMPERS


-	-	-	-	-	APPROVAL	DATE	MATERIAL: -	HOST LINK PORT TO IBM-XT COMPUTER CABLE	
-	-	-	-	-	DRWN OBA	10-26-94	FINISH: -		
-	-	-	-	-	CHCKD	-	TOLERANCE: -	DRWG NO: PFP0011A	
-	-	-	-	-	APRVD	-	UNITS: ENGLISH	FILE NAME: -	SIZE: A
REV	DESCRIPTION	COS NO.	DATE	SGND	-	-	SCALE: NONE	omron Omron Electronics, Inc. Omron Manufacturing of America	
							SHEET: 1 OF 1		

C200H-ASC02
C200H-BASIC/ASCII





Cable Part Number

C200H - CN220 - EU



XT Computer (25-pin)






CABLE C200H-CN220-EU

1. DE-9 MALE CONNECTOR WITH SOLDER CUPS
2. DB-25 FEMALE CONNECTOR WITH SOLDER CUPS
3. 7 CONDUCTOR, 24 AWG STRANDED, FOIL SHIELD, PVC JACKETED CABLE
4. OMRON DE-9 BACKSHELL W/ 2.6MM JACK SCREWS, P/N XM2S-0911
5. OMRON DB-25 BACKSHELL W/ #4-40 JACK SCREWS, P/N XM2S-2513
6. HEAT SHRINK TUBING TO COVER SOLDERED CONNECTION, BOTH ENDS
7. HEAT SHRINK TUBING, WHITE WITH PRINTED PART NUMBER AS SHOWN IN BLACK, 8 PT. HELVETICA. POSITION APPROXIMATELY AS SHOWN.

FROM #1		TO #2	
PIN		PIN	
TXD	2	3	RXD
RXD	3	2	TXD
RTS	4	5	CTS
CTS	5	4	RTS
	6	nc	
DSR	7	20	DTR
DTR	8	6	DSR
COM	9	7	COM
1 to SHIELD		nc	

-	-	-	-	-	APPROVAL	DATE	MATERIAL: -		C200H BASIC/ASCII MODULE TO IBM-XT COMPUTER CABLE		
-	-	-	-	-	DRWN	OBA					10-18-94
-	-	-	-	-	CHCKD						
B	ADDED ITEMS #6 AND 7	-	10-18-94	-	-	-	TOLERANCE: -	UNITS: ENGLISH	DRWG NO: PFP0006B		
A	ORIGINAL	-	7-14-94	-	APRVD	-		SCALE: NONE	FILE NAME: -	SIZE: A	
REV	DESCRIPTION	COS NO.	DATE	SGND	-	-		SHEET: 1 OF 1	 Omron Electronics, Inc. Omron Manufacturing of America		

Shield 1

SD 2

2 RD

RD 3

3 SD

COM 9

5 COM

RTS 4

8 CTS

CTS 5


7 RTS

DSR 7

4 DTR

DTR 8

6 DSR




CABLE C200H-CN229-EU

1. DE-9 MALE CONNECTOR WITH SOLDER CUPS
2. DE-9 FEMALE CONNECTOR WITH SOLDER CUPS
3. 7 CONDUCTOR, 24 AWG STRANDED, FOIL SHIELD, PVC JACKETED CABLE
4. OMRON DE-9 BACKSHELL W/ 2.6MM JACK SCREWS, P/N XM2S-0911
5. OMRON DE-9 BACKSHELL W/ #4-40 JACK SCREWS, P/N XM2S-0913
6. HEAT SHRINK TUBING TO COVER SOLDERED CONNECTION, BOTH ENDS
7. HEAT SHRINK TUBING, WHITE WITH PRINTED PART NUMBER AS SHOWN IN BLACK, 8 PT. HELVETICA. POSITION APPROXIMATELY AS SHOWN.


FROM #1		TO #2	
PIN		PIN	
TXD	2	2	RXD
RXD	3	3	TXD
RTS	4	8	CTS
CTS	5	7	RTS
	6	nc	
DSR	7	4	DTR
DTR	8	6	DSR
COM	9	5	COM
1 to SHIELD		nc	

-	-	-	-	-	APPROVAL	DATE	MATERIAL: -		C200H BASIC/ASCII MODULE TO IBM-AT COMPUTER CABLE	
-	-	-	-	-	DRWN	OBA	10-18-94	FINISH: -		
-	-	-	-	-	CHCKD	-	-	TOLERANCE: -		
B	ADDED ITEMS #6 AND 7	-	10-18-94	-	APRVD	-	-	UNITS: ENGLISH	DRWG NO: PFP0005B	
A	ORIGINAL	-	7-14-94	-				SCALE: NONE	FILE NAME: -	
REV	DESCRIPTION	COS NO.	DATE	SGND				SHEET: 1 OF 1	SIZE: A	
									OMRON Omron Electronics, Inc. Omron Manufacturing of America	


NT11S, NT20S,
NT600S, NT30,
NT30C, NT620S/620C




Cable Part Number C200H - CN229 - EU



AT Computer (9-pin)





CABLE C200H-CN229-EU


1. DE-9 MALE CONNECTOR WITH SOLDER CUPS
2. DE-9 FEMALE CONNECTOR WITH SOLDER CUPS
3. 7 CONDUCTOR, 24 AWG STRANDED, FOIL SHIELD, PVC JACKETED CABLE
4. OMRON DE-9 BACKSHELL W/ 2.6MM JACK SCREWS, P/N XM2S-0911
5. OMRON DE-9 BACKSHELL W/ #4-40 JACK SCREWS, P/N XM2S-0913
6. HEAT SHRINK TUBING TO COVER SOLDERED CONNECTION, BOTH ENDS
7. HEAT SHRINK TUBING, WHITE WITH PRINTED PART NUMBER AS SHOWN IN BLACK, 8 PT. HELVETICA. POSITION APPROXIMATELY AS SHOWN.

FROM #1		TO #2	
PIN		PIN	
TXD	2	2	RXD
RXD	3	3	TXD
RTS	4	8	CTS
CTS	5	7	RTS
	6	nc	
DSR	7	4	DTR
DTR	8	6	DSR
COM	9	5	COM
1 to SHIELD		nc	

-	-	-	-	-	APPROVAL	DATE	MATERIAL: -		C200H BASIC/ASCII MODULE TO IBM-AT COMPUTER CABLE	
-	-	-	-	-	DRWN	OBA	FINISH: -			
-	-	-	-	-	CHCKD					
B	ADDED ITEMS #6 AND 7	-	10-18-94	-	-	-	SCALE: NONE			
A	ORIGINAL	-	7-14-94	-	APRVD	-	SHEET: 1 OF 1			
REV	DESCRIPTION	COS NO.	DATE	SGND	-	-				Omron Electronics, Inc. Omron Manufacturing of America



Shield		XT Computer (25-pin)	
	1		
SD	2	3	RD
RD	3	2	SD
COM	9	7	COM
RTS	4	5	CTS
CTS	5	4	RTS
DSR	7	20	DTR
DTR	8	6	DSR




CABLE C200H-CN220-EU

1. DE-9 MALE CONNECTOR WITH SOLDER CUPS
2. DB-25 FEMALE CONNECTOR WITH SOLDER CUPS
3. 7 CONDUCTOR, 24 AWG STRANDED, FOIL SHIELD, PVC JACKETED CABLE
4. OMRON DE-9 BACKSHELL W/ 2.6MM JACK SCREWS, P/N XM2S-0911
5. OMRON DB-25 BACKSHELL W/ #4-40 JACK SCREWS, P/N XM2S-2513
6. HEAT SHRINK TUBING TO COVER SOLDERED CONNECTION, BOTH ENDS
7. HEAT SHRINK TUBING, WHITE WITH PRINTED PART NUMBER AS SHOWN IN BLACK, 8 PT. HELVETICA. POSITION APPROXIMATELY AS SHOWN.

FROM #1		TO #2	
PIN		PIN	
TXD	2	3	RXD
RXD	3	2	TXD
RTS	4	5	CTS
CTS	5	4	RTS
	6	nc	
DSR	7	20	DTR
DTR	8	6	DSR
COM	9	7	COM
1 to SHIELD		nc	

-	-	-	-	-	APPROVAL	DATE	MATERIAL: -		C200H BASIC/ASCII MODULE TO IBM-XT COMPUTER CABLE	
-	-	-	-	-	DRWN	10-18-94				
-	-	-	-	-	OBA	10-18-94	TOLERANCE: -		DRWG NO: PFP0006B	
B	ADDED ITEMS #6 AND 7	-	10-18-94	-					CHCKD	-
A	ORIGINAL	-	7-14-94	-	APRVD	-	SCALE: NONE	omron Omron Electronics, Inc. Omron Manufacturing of America		
REV	DESCRIPTION	COS NO.	DATE	SGND	-	-	SHEET: 1 OF 1			


NT11S, NT20S,
NT600S, NT30,
NT30C, NT620/620S



9-pin male


Cable Part Number
C200H - CN510 - EU


CV500 - LK201 (Port 2)
CVM1 built-in port
C200HS built-in port
CQM1 built-in port
IDSC built-in port



9-pin male

CV500-LK201 (Port 2)
CVM1 built-in port
C200HS built-in port
CQM1 built-in port
IDSC built-in port





CABLE C200H-CN510-EU

1. DE-9 MALE CONNECTOR WITH SOLDER CUPS, QTY 2
2. OMRON DE-9 BACKSHELL W/ 2.6MM JACK SCREWS, QTY 2
OMRON CAT. NO. XM2S-0911, PIM NO. 4584252-0
3. 3 CONDUCTOR, 24 AWG STRANDED, FOIL SHIELD, PVC JACKETED CABLE*
4. HEAT SHRINK TUBING TO COVER SOLDERED CONNECTION, BOTH ENDS
5. HEAT SHRINK TUBING, WHITE WITH PRINTED PART NUMBER AS SHOWN IN BLACK, 8 PT. HELVETICA TYPE. POSITION APPROXIMATELY AS SHOWN.


* RECOMMENDED: CAROL #C0743, 6 CONDUCTOR CABLE

	FROM PIN	TO PIN	
TXD	2	3	RXD
RXD	3	2	TXD
	nc	4 to 5*	
	4 to 5*	nc	
+5	6	nc	
COM	9	9	COM
	nc	1 to SHIELD	

* JUMPER PINS 4 TO 5 IN
EACH CONNECTOR

-	-	-	-	-	APPROVAL	DATE	MATERIAL: -	S-SERIES PT to C-CV SERIES CPU PORT	
-	-	-	-	-	DRWN OBA	11-28-95	FINISH: -		
-	-	-	-	-	CHCKD	-	TOLERANCE: -	DRWG NO: PFP0017-A	
-	-	-	-	-	APRVD	-	UNITS: ENGLISH	FILE NAME: -	SIZE: A
REV	DESCRIPTION	COS NO.	DATE	SGND	-	-	SCALE: NONE	Omron Electronics, Inc. Omron Manufacturing of America	
							SHEET: 1 OF 1		

NT11S, NT20S, NT30,
NT30C, NT600S,
NT620C/620S




9-pin male


Cable Part Number
C200H-519-EU (50 cm)
C200H-329-EU (3M)
C200H-529-EU (5M)

C500 - LK203
C200H - LK201
3G2A6 - LK201
3G2C7 - LK201
CV500 - LK201 (Port 1)



25-pin





CABLE C200H-CN519-EU

1. DE-9 MALE CONNECTOR WITH SOLDER CUPS
2. DB-25 MALE CONNECTOR WITH SOLDER CUPS
3. 3 CONDUCTOR, 24 AWG STRANDED, FOIL SHIELD, PVC JACKETED CABLE
4. OMRON DE-9 BACKSHELL W/ 2.6MM JACK SCREWS, CAT. XM2S-0911, PIM 4584252-0
5. OMRON DB-25 BACKSHELL W/ 2.6MM JACK SCREWS, CAT. XM2S-2511, PIM 4584254-0
6. HEAT SHRINK TUBING TO COVER SOLDERED CONNECTION, BOTH ENDS
7. HEAT SHRINK TUBING, WHITE WITH PRINTED PART NUMBER AS SHOWN IN BLACK, 8 PT. HELVETICA TYPE. POSITION APPROXIMATELY AS SHOWN.


* RECOMMENDED: CAROL #C0743, 6 CONDUCTOR CABLE

	FROM #1 PIN	TO #2 PIN	
TXD	2	3	RXD
RXD	3	2	TXD
	nc	4 to 5*	
	---	---	
+5	6	nc	
COM	9	7	COM
	nc	1 to SHIELD	

* JUMPER PINS 4 TO 5

-	-	-	-	-	APPROVAL	DATE	MATERIAL: -	S-SERIES PT to C-CV SERIES HOST LINK MODULE	
-	-	-	-	-	DRWN OBA	11-28-95	FINISH: -		
-	-	-	-	-	CHCKD	-	TOLERANCE: -	DRWG NO:	PFP0020-A
-	-	-	-	-	APRVD	-	UNITS: ENGLISH	FILE NAME: -	SIZE: A
REV	DESCRIPTION	COS NO.	DATE	SGND	-	-	SCALE: NONE	omron Omron Electronics, Inc. Omron Manufacturing of America	
							SHEET: 1 OF 1		


CPM1 / CQM1 / C200H /
IDSC




9-pin male


Cable Part Number
C200H - CN320 - EU
C200H - CN520 - EU
(one-to-one link)

CPM1 / CQM1 / C200H /
IDSC



9-pin male





CABLE C200H-CN320-EU

1. DE-9 MALE CONNECTOR WITH SOLDER CUPS, QTY 2
2. OMRON DE-9 BACKSHELL W/ 2.6MM JACK SCREWS, QTY 2
OMRON CAT. NO. XM2S-0911, PIM NO. 4584252-0
3. 3 CONDUCTOR, 24 AWG STRANDED, FOIL SHIELD, PVC JACKETED CABLE*
4. HEAT SHRINK TUBING TO COVER SOLDERED CONNECTION, BOTH ENDS
5. HEAT SHRINK TUBING, WHITE WITH PRINTED PART NUMBER AS SHOWN IN
BLACK, 8 PT. HELVETICA TYPE. POSITION APPROXIMATELY AS SHOWN.


* RECOMMENDED: CAROL #C0743, 6 CONDUCTOR CABLE

	FROM PIN	TO PIN	
TXD	2	3	RXD
RXD	3	2	TXD
	nc	4 to 5*	
	4 to 5*	nc	
+5	6	nc	
COM	9	9	COM
	nc	1 to SHIELD	

* JUMPER PINS 4 TO 5 IN
EACH CONNECTOR

-	-	-	-	-	APPROVAL	DATE	MATERIAL: -	S-SERIES PT to C-CV SERIES CPU PORT	
-	-	-	-	-	DRWN OBA	11-28-95	FINISH: -		
-	-	-	-	-	CHCKD	-	TOLERANCE: -	DRWG NO: PFP0018-A	
-	-	-	-	-	APRVD	-	UNITS: ENGLISH	FILE NAME: -	SIZE: A
REV	DESCRIPTION	COS NO.	DATE	SGND	-	-	SCALE: NONE	omron Omron Electronics, Inc. Omron Manufacturing of America	
							SHEET: 1 OF 1		


NT11S, NT20S, NT30,
NT30C, NT600S,
NT620C/620S




9-pin male


Cable Part Number
C200H - CN320 - EU
C200H - CN520 - EU

CV500 - LK201 (Port 2)
CVM1 built-in port
C200HS built-in port
CQM1 built-in port
CPM1- CIF01
IDSC built-in port



9-pin male





CABLE C200H-CN520-EU

1. DE-9 MALE CONNECTOR WITH SOLDER CUPS, QTY 2
2. OMRON DE-9 BACKSHELL W/ 2.6MM JACK SCREWS, QTY 2
OMRON CAT. NO. XM2S-0911, PIM NO. 4584252-0
3. 3 CONDUCTOR, 24 AWG STRANDED, FOIL SHIELD, PVC JACKETED CABLE*
4. HEAT SHRINK TUBING TO COVER SOLDERED CONNECTION, BOTH ENDS
5. HEAT SHRINK TUBING, WHITE WITH PRINTED PART NUMBER AS SHOWN IN
BLACK, 8 PT. HELVETICA TYPE. POSITION APPROXIMATELY AS SHOWN.


* RECOMMENDED: CAROL #C0743, 6 CONDUCTOR CABLE

	FROM PIN	TO PIN	
TXD	2	3	RXD
RXD	3	2	TXD
	nc	4 to 5*	
	4 to 5*	nc	
+5	6	nc	
COM	9	9	COM
	nc	1 to SHIELD	

* JUMPER PINS 4 TO 5 IN
EACH CONNECTOR

-	-	-	-	-	APPROVAL	DATE	MATERIAL: -	S-SERIES PT to C-CV SERIES CPU PORT	
-	-	-	-	-	DRWN OBA	11-28-95	FINISH: -		
-	-	-	-	-	CHCKD	-	TOLERANCE: -	DRWG NO: PFP0019-A	
-	-	-	-	-	APRVD	-	UNITS: ENGLISH	FILE NAME: -	SIZE: A
REV	DESCRIPTION	COS NO.	DATE	SGND	-	-	SCALE: NONE	Omron Electronics, Inc. Omron Manufacturing of America	
							SHEET: 1 OF 1		


CV500 - LK201 (Port 2)
CVM1 built-in port
C200HS built-in port
CQM1 built-in port
CPM1- CIF01
IDSC built-in port




9-pin male


Cable Part Number
C200H - CN320 - EU
C200H - CN520 - EU

PT (NT600M - LK201)



9-pin male





CABLE C200H-CN320-EU

1. DE-9 MALE CONNECTOR WITH SOLDER CUPS, QTY 2
2. OMRON DE-9 BACKSHELL W/ 2.6MM JACK SCREWS, QTY 2
OMRON CAT. NO. XM2S-0911, PIM NO. 4584252-0
3. 3 CONDUCTOR, 24 AWG STRANDED, FOIL SHIELD, PVC JACKETED CABLE*
4. HEAT SHRINK TUBING TO COVER SOLDERED CONNECTION, BOTH ENDS
5. HEAT SHRINK TUBING, WHITE WITH PRINTED PART NUMBER AS SHOWN IN
BLACK, 8 PT. HELVETICA TYPE. POSITION APPROXIMATELY AS SHOWN.


* RECOMMENDED: CAROL #C0743, 6 CONDUCTOR CABLE

	FROM PIN	TO PIN	
TXD	2	3	RXD
RXD	3	2	TXD
	nc	4 to 5*	
	4 to 5*	nc	
+5	6	nc	
COM	9	9	COM
	nc	1 to SHIELD	

* JUMPER PINS 4 TO 5 IN
EACH CONNECTOR

-	-	-	-	-	APPROVAL	DATE	MATERIAL: -	S-SERIES PT to C-CV SERIES CPU PORT	
-	-	-	-	-	DRWN OBA	11-28-95	FINISH: -		
-	-	-	-	-	CHCKD	-	TOLERANCE: -	DRWG NO: PFP0018-A	
-	-	-	-	-	APRVD	-	UNITS: ENGLISH	FILE NAME: -	SIZE: A
REV	DESCRIPTION	COS NO.	DATE	SGND	-	-	SCALE: NONE	omron Omron Electronics, Inc. Omron Manufacturing of America	
							SHEET: 1 OF 1		


All C**H Series
PLC's



9-pin

**Omron does not make a cable
for this configuration**

NT11S/NT20S/NT30
NT600S/NT620



9-pin

