


Solid Tantalum Chip Capacitors

TANTAMOUNT®, Commercial, Surface Mount



PERFORMANCE/ELECTRICAL CHARACTERISTICS

Operating Temperature: - 55 °C to + 85 °C

(To + 125 °C with voltage derating)

Note: Refer to Doc. 40088

Capacitance Range: 0.10 µF to 680 µF

Capacitance Tolerance: ± 20 %, ± 10 % standard
(20 % only for P case code)

100 % Surge Current Tested (D & E Case Codes)

Voltage Rating: 4 WVDC to 50 WVDC

FEATURES

- Terminations: 100 % Tin, standard
SnPb available
- Compliant Terminations
- Molded case available in six case codes
- Compatible with “High Volume” automatic pick and place equipment
- Optical character recognition qualified
- Meets IEC Specification QC300801/US0001 and EIA 535BAAC



RoHS*
COMPLIANT

OTHER SPECIFICATIONS

CECC

30801-005
30801-009
30801-011
30801-801

IECQ

PQC32/GB003
300801/FR001
793DX
CTC3
CTC4
793DE

ORDERING INFORMATION

293D TYPE	107 CAPACITANCE	X9 CAPACITANCE TOLERANCE	010 DC VOLTAGE RATING AT + 85 °C	D CASE CODE	2WE3 TERMINATION AND PACKAGING
	This is expressed in picofarads. The first two digits are the significant figures. The third is the number of zeros to follow.	X0 = ± 20 % X9 = ± 10 % X5 = ± 5 % (Special Order)	This is expressed in volts. To complete the three-digit block, zeros precede the voltage rating. A decimal point is indicated by an “R” (6R3 = 6.3 volts).	See Ratings and Case Codes Table.	2TE3: 100 % tin terminations, 7" (178 mm) reel 2WE3: 100 % tin terminations, 13" (330 mm) reel 8T: 90/10 SnPb Solder Plate terminations, 7" (178 mm) reel 8W: 90/10 SnPb Solder Plate terminations, 13" (330 mm) reel 2T: Solderable coating, non-preferred 2W: Solderable coating, non-preferred

Note: We reserve the right to supply higher voltage ratings, tighter capacitance tolerance and higher grade capacitors in the same case size. Voltage substitutions will be marked with the higher voltage rating.

DIMENSIONS in inches [millimeters]




CASE CODE	EIA SIZE	L	W	H	P	TW	TH (MIN.)
A	3216-18	0.126 ± 0.008 [3.2 ± 0.20]	0.063 ± 0.008 [1.6 ± 0.20]	0.063 ± 0.008 [1.6 ± 0.20]	0.031 ± 0.012 [0.80 ± 0.30]	0.047 ± 0.004 [1.2 ± 0.10]	0.028 [0.70]
B	3528-21	0.138 ± 0.008 [3.5 ± 0.20]	0.110 ± 0.008 [2.8 ± 0.20]	0.075 ± 0.008 [1.9 ± 0.20]	0.031 ± 0.012 [0.80 ± 0.30]	0.087 ± 0.004 [2.2 ± 0.10]	0.028 [0.70]
C	6032-28	0.236 ± 0.012 [6.0 ± 0.30]	0.126 ± 0.012 [3.2 ± 0.30]	0.098 ± 0.012 [2.5 ± 0.30]	0.051 ± 0.012 [1.3 ± 0.30]	0.087 ± 0.004 [2.2 ± 0.10]	0.039 [1.0]
D	7343-31	0.287 ± 0.012 [7.3 ± 0.30]	0.170 ± 0.012 [4.3 ± 0.30]	0.110 ± 0.012 [2.8 ± 0.30]	0.051 ± 0.012 [1.3 ± 0.30]	0.095 ± 0.004 [2.4 ± 0.10]	0.039 [1.0]
E	7343-43	0.287 ± 0.012 [7.3 ± 0.30]	0.170 ± 0.012 [4.3 ± 0.30]	0.158 ± 0.012 [4.0 ± 0.30]	0.051 ± 0.012 [1.3 ± 0.30]	0.095 ± 0.004 [2.4 ± 0.10]	0.039 [1.0]
P	2012-12	0.079 ± 0.020 [2.0 ± 0.008]	0.049 ± 0.008 [1.25 ± 0.2]	0.047 Max. [1.2 Max.]	0.020 ± 0.008 [0.52 ± 0.20]	0.047 ± 0.004 [1.2 ± 0.10]	0.012 [0.3]

* Pb containing terminations are not RoHS compliant, exemptions may apply

RATINGS AND CASE CODES

μF	4 V	6.3 V	10 V	16 V	20 V	25 V	35 V	50 V
0.10							A	A
0.15							A	A/B
0.22							A	A/B
0.33							A	A/B
0.47						A	A/B	A/B/C
0.68					A	A	A/B	B/C
1.0		P	P	A	A	A/B	A/B	B/C
1.5		P	A	A	A	A/B	B/C	B/C
2.2	P	A/P	A/P	A/B	A/B	A/B	B/C	C/D
3.3	A/P	A/P	A/P	A/B	A/B	A*/B/C	B/C	C/D
4.7	A/P	A/B/P	A/B/P	A/B	A/B/C	A/B/C	C/D	D
6.8	A/P	A/B/P	A/B/P	A/B/C	A/B/C	B/C	C/D	D/E
10	A/B/P	A/B/C/P	A/B/C	A/B/C	B/C	B/C/D	C/D	D/E
15	A/B	A/B/C	A/B/C	B/C	B/C/D	C/D	D/E	
22	A/BC	A/B/C	A/B/C	B/C/D	B/C/D	D	D/E	
33	A/B/C	A/B/C	B/C/D	B/C/D	C/D	D/E		
47	A/B/C	B/C/D	B/C/D	C/D	D/E	E		
68	B/C/D	B/C/D	B*/C/D	D	D/E			
100	B/C/D	B/C/D	C/D	D/E	E			
150	B/C/D	C/D/E	D/E	D*/E				
220	B/C/D/E	C/D/E	D/E					
330	D/E	D/E	E					
470	D/E	E						
680	E							

* Preliminary values, contact factory for availability.

MARKING

Solid Tantalum Chip Capacitors
TANTAMOUNT®, Commercial, Surface Mount

Vishay Sprague

STANDARD/EXTENDED RATINGS

CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DC LEAKAGE AT + 25 °C (μ A)	MAX. DF AT + 25 °C 120 Hz (%)	MAX. ESR AT + 25 °C 100 kHz (Ohms)	MAX. RIPPLE 100 kHz I _{rms} (Amps)
4 WVDC AT + 85 °C, SURGE = 5.2 V . . . 2.7 WVDC AT + 125 °C, SURGE = 3.4 V						
2.2	P	293D225X_004P2T_E3	0.5	8	12	0.02
3.3	A	293D335X_004A2_E3	0.5	6	7.6	0.10
3.3	P	293D335X_004P2_E3	0.5	8	12	0.02
4.7	A	293D475X_004A2_E3	0.5	6	6.3	0.11
4.7	P	293D475X_004P2_E3	0.5	8	6.0	0.06
6.8	A	293D685X_004A2_E3	0.5	6	5.5	0.12
6.8	P	293D685X_004P2_E3	0.5	10	6.0	0.06
10	A	293D106X_004A2_E3	0.5	6	5.1	0.12
10	B	293D106X_004B2_E3	0.5	6	3.5	0.16
10	P	293D106X_004P2_E3	0.5	10	6.0	0.06
15	A	293D156X_004A2_E3	0.6	6	3.4	0.15
15	B	293D156X_004B2_E3	0.6	6	2.9	0.17
15	P	293D156X_004P2_E3	0.6	6	N/A	N/A
22	A	293D226X_004A2_E3	0.9	6	2.9	0.16
22	B	293D226X_004B2_E3	0.9	6	2.5	0.18
22	C	293D226X_004C2_E3	0.9	6	1.8	0.25
33	A	293D336X_004A2_E3	1.3	6	2.9	0.16
33	B	293D336X_004B2_E3	1.3	6	2.0	0.21
33	C	293D336X_004C2_E3	1.3	6	1.8	0.25
47	A	293D476X_004A2_E3	1.9	14	2.5	0.17
47	B	293D476X_004B2_E3	1.9	6	1.9	0.21
47	C	293D476X_004C2_E3	1.9	6	1.8	0.25
68	B	293D686X_004B2_E3	2.7	6	1.9	0.21
68	C	293D686X_004C2_E3	2.7	6	1.4	0.28
68	D	293D686X_004D2_E3	2.7	6	0.8	0.43
100	B	293D107X_004B2_E3	4.0	8	1.8	0.22
100	C	293D107X_004C2_E3	4.0	6	0.8	0.37
100	D	293D107X_004D2_E3	4.0	6	0.7	0.46
150	B	293D157X_004B2_E3	6.0	14	1.6	0.23
150	C	293D157X_004C2_E3	6.0	12	0.7	0.40
150	D	293D157X_004D2_E3	6.0	8	0.6	0.50
220	B	293D227X_004B2_E3	8.8	18	1.5	0.24
220	C	293D227X_004C2_E3	8.8	8	0.7	0.40
220	D	293D227X_004D2_E3	8.8	8	0.6	0.50
220	E	293D227X_004E2_E3	8.8	8	0.5	0.57
330	D	293D337X_004D2_E3	13.2	8	0.6	0.50
330	E	293D337X_004E2_E3	13.2	8	0.5	0.57
470	D	293D477X_004D2_E3	18.8	10	0.6	0.50
470	E	293D477X_004E2_E3	18.8	10	0.5	0.57
680	E	293D687X_004E2_E3	27.2	12	0.5	0.57
6.3 WVDC AT + 85 °C, SURGE = 8 V . . . 4 WVDC AT + 125 °C, SURGE = 5 V						
1.0	P	293D225X_6R3P2_E3	0.5	8	12	0.02
1.5	P	293D225X_6R3P2_E3	0.5	8	12	0.02
2.2	A	293D225X_6R3A2_E3	0.5	6	7.6	0.10
2.2	P	293D225X_6R3P2_E3	0.5	8	12	0.02
3.3	A	293D335X_6R3A2_E3	0.5	6	6.3	0.11
3.3	P	293D335X_6R3P2_E3	0.5	8	12	0.02
4.7	A	293D475X_6R3A2_E3	0.5	6	5.5	0.12
4.7	P	293D475X_6R3P2_E3	0.5	8	6.0	0.06
6.8	A	293D685X_6R3A2_E3	0.5	6	5.0	0.12
6.8	B	293D685X_6R3B2_E3	0.5	6	3.4	0.16
6.8	P	293D685X_6R3P2_E3	0.5	10	6.0	0.06
10	A	293D106X_6R3A2_E3	0.6	6	3.4	0.15
10	B	293D106X_6R3B2_E3	0.6	6	2.9	0.17
10	P	293D106X_6R3P2_E3	0.6	10	6.0	0.06
15	A	293D156X_6R3A2_E3	0.9	6	2.9	0.16
15	B	293D156X_6R3B2_E3	0.9	6	2.5	0.18
15	C	293D156X_6R3C2_E3	0.9	6	1.8	0.25
22	A	293D226X_6R3A2_E3	1.3	6	2.9	0.16
22	B	293D226X_6R3B2_E3	1.3	6	2.0	0.21
22	C	293D226X_6R3C2_E3	1.3	6	1.8	0.25
33	A	293D336X_6R3A2_E3	2.0	14	2.5	0.17
33	B	293D336X_6R3B2_E3	2.0	6	1.9	0.21
33	C	293D336X_6R3C2_E3	2.0	6	1.5	0.27
47	B	293D476X_6R3B2_E3	2.8	6	1.9	0.21
47	C	293D476X_6R3C2_E3	2.8	6	1.4	0.28

* For 10 % tolerance, specify "9"; for 20 % tolerance, change to "0".

STANDARD/EXTENDED RATINGS

CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DC LEAKAGE AT + 25 °C (μ A)	MAX. DF AT + 25 °C 120 Hz (%)	MAX. ESR AT + 25 °C 100 kHz (Ohms)	MAX. RIPPLE 100 kHz Irms (Amps)
6.3 WVDC AT + 85 °C, SURGE = 8 V ... 4 WVDC AT + 125 °C, SURGE = 5 V						
47	D	293D476X_6R3D2_E3	2.8	6	0.8	0.43
68	B	293D686X_6R3B2_E3	4.1	6	1.8	0.22
68	C	293D686X_6R3C2_E3	4.1	6	0.8	0.37
68	D	293D686X_6R3D2_E3	4.1	6	0.7	0.46
100	B	293D107X_6R3B2_E3	6.0	15	1.7	0.22
100	C	293D107X_6R3C2_E3	6.0	6	0.8	0.37
100	D	293D107X_6R3D2_E3	6.0	6	0.7	0.46
150	C	293D157X_6R3C2_E3	9.0	8	0.7	0.40
150	D	293D157X_6R3D2_E3	9.0	8	0.6	0.50
150	E	293D157X_6R3E2_E3	9.0	8	0.5	0.57
220	C	293D227X_6R3C2_E3	13.9	14	0.7	0.39
220	D	293D227X_6R3D2_E3	13.2	8	0.6	0.50
220	E	293D227X_6R3E2_E3	13.2	8	0.5	0.57
330	D	293D337X_6R3D2_E3	19.8	8	0.6	0.50
330	E	293D337X_6R3E2_E3	19.8	8	0.5	0.57
470	E	293D477X_6R3E2_E3	28.2	10	0.5	0.57
10 WVDC AT + 85 °C, SURGE = 13 V ... 7 WVDC AT + 125 °C, SURGE = 8 V						
1.0	P	293D105X_010P2_E3	0.5	8	12	0.02
1.5	A	293D155X_010A2_E3	0.5	6	8.0	0.10
1.5	P	293D155X_010P2_E3	0.5	8	12	0.02
2.2	A	293D225X_010A2_E3	0.5	6	6.3	0.11
2.2	P	293D225X_010P2_E3	0.5	8	12	0.07
3.3	A	293D335X_010A2_E3	0.5	6	5.5	0.12
3.3	P	293D335X_010P2_E3	0.5	8	12	0.02
4.7	A	293D475X_010A2_E3	0.5	6	5.0	0.12
4.7	B	293D475X_010B2_E3	0.5	6	3.4	0.16
4.7	P	293D475X_010P2_E3	0.5	8	6.0	0.06
6.8	A	293D685X_010A2_E3	0.7	6	4.2	0.13
6.8	B	293D685X_010B2_E3	0.7	6	2.9	0.17
6.8	P	293D685X_010P2_E3	0.5	8	6.0	0.06
10	A	293D106X_010A2_E3	1.0	6	3.4	0.15
10	B	293D106X_010B2_E3	1.0	6	2.5	0.18
10	C	293D106X_010C2_E3	1.0	6	1.8	0.25
15	A	293D156X_010A2_E3	1.5	6	2.9	0.16
15	B	293D156X_010B2_E3	1.5	6	2.0	0.21
15	C	293D156X_010C2_E3	1.5	6	1.8	0.25
22	A	293D226X_010A2_E3	2.2	8	2.5	0.17
22	B	293D226X_010B2_E3	2.2	6	1.9	0.21
22	C	293D226X_010C2_E3	2.2	6	1.5	0.27
33	B	293D336X_010B2_E3	3.3	6	1.9	0.21
33	C	293D336X_010C2_E3	3.3	6	1.4	0.28
33	D	293D336X_010D2_E3	3.3	6	0.8	0.43
47	B	293D476X_010B2_E3	4.7	6	1.8	0.22
47	C	293D476X_010C2_E3	4.7	6	1.1	0.32
47	D	293D476X_010D2_E3	4.7	6	0.7	0.46
68	C	293D686X_010C2_E3	6.8	6	1.0	0.33
68	D	293D686X_010D2_E3	6.8	6	0.7	0.46
100	C	293D107X_010C2_E3	10	8	0.9	0.35
100	D	293D107X_010D2_E3	10	8	0.6	0.50
150	D	293D157X_010D2_E3	15	8	0.6	0.50
150	E	293D157X_010E2_E3	15	8	0.5	0.57
220	D	293D227X_010D2_E3	22	8	0.6	0.50
220	E	293D227X_010E2_E3	22	8	0.5	0.57
330	E	293D337X_010E2_E3	33	10	0.5	0.57
16 WVDC AT + 85 °C, SURGE = 20 V ... 10 WVDC AT + 125 °C, SURGE = 12 V						
1.0	A	293D105X_016A2_E3	0.5	4	9.3	0.09
1.5	A	293D155X_016A2_E3	0.5	6	6.7	0.11
2.2	A	293D225X_016A2_E3	0.5	6	5.9	0.11
2.2	B	293D225X_016B2_E3	0.5	6	4.6	0.14
3.3	A	293D335X_016A2_E3	0.5	6	5.0	0.12
3.3	B	293D335X_016B2_E3	0.5	6	3.5	0.16
4.7	A	293D475X_016A2_E3	0.8	6	5.0	0.12
4.7	B	293D475X_016B2_E3	0.8	6	2.9	0.17

* For 10 % tolerance, specify "9"; for 20 % tolerance, change to "0".

Solid Tantalum Chip Capacitors
TANTAMOUNT®, Commercial, Surface Mount

Vishay Sprague

STANDARD/EXTENDED RATINGS						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DC LEAKAGE AT + 25 °C (μ A)	MAX. DF AT + 25 °C 120 Hz (%)	MAX. ESR AT + 25 °C 100 kHz (Ohms)	MAX. RIPPLE 100 kHz Irms (Amps)
16 WVDC AT + 85 °C, SURGE = 20 V . . . 10 WVDC AT + 125 °C, SURGE = 12 V						
6.8	A	293D685X_016A2_E3	1.1	6	4.2	0.13
6.8	B	293D685X_016B2_E3	1.1	6	2.5	0.18
6.8	C	293D685X_016C2_E3	1.1	6	1.9	0.24
10	A	293D106X_016A2_E3	1.6	6	3.0	0.16
10	B	293D106X_016B2_E3	1.6	6	2.0	0.21
10	C	293D106X_016C2_E3	1.6	6	1.8	0.25
15	B	293D156X_016B2_E3	2.4	6	2.0	0.21
15	C	293D156X_016C2_E3	2.4	6	1.5	0.27
22	B	293D226X0016B2_E3	3.5	6	1.9	0.21
22	C	293D226X_016C2_E3	3.5	6	1.4	0.28
22	D	293D226X_016D2_E3	3.5	6	0.8	0.43
33	B	293D336X0016B2_E3	5.3	6	1.8	0.22
33	C	293D336X_016C2_E3	5.3	6	1.1	0.32
33	D	293D336X_016D2_E3	5.3	6	0.7	0.46
47	C	293D476X_016C2_E3	7.5	6	1.0	0.33
47	D	293D476X_016D2_E3	7.5	6	0.7	0.46
68	D	293D686X_016D2_E3	10.9	6	0.6	0.50
100	D	293D107X_016D2_E3	16	8	0.6	0.50
100	E	293D107X_016E2_E3	16	8	0.6	0.52
150	E	293D157X_016E2_E3	24	8	0.5	0.57
20 WVDC AT + 85 °C, SURGE = 26 V . . . 13 WVDC AT + 125 °C, SURGE = 16 V						
0.68	A	293D684X_020A2_E3	0.5	4	10	0.09
1.0	A	293D105X_020A2_E3	0.5	4	8.4	0.09
1.5	A	293D155X_020A2_E3	0.5	6	6.3	0.11
2.2	A	293D225X_020A2_E3	0.5	6	5.9	0.11
2.2	B	293D225X_020B2_E3	0.5	6	3.5	0.16
3.3	A	293D335X_020A2_E3	0.7	6	5.9	0.11
3.3	B	293D335X_020B2_E3	0.7	6	3.0	0.17
4.7	A	293D475X_020A2_E3	0.9	6	5.0	0.12
4.7	B	293D475X_020B2_E3	0.9	6	2.9	0.17
4.7	C	293D475X_020C2_E3	0.9	6	2.3	0.22
6.8	A	293D685X_020A2_E3	1.4	6	4.5	0.13
6.8	B	293D685X_020B2_E3	1.4	6	2.5	0.18
6.8	C	293D685X_020C2_E3	1.4	6	1.9	0.24
10	B	293D106X_020B2_E3	2.0	6	2.5	0.18
10	C	293D106X_020C2_E3	2.0	6	1.7	0.25
15	B	293D156X_020B2_E3	3.0	6	2.3	0.19
15	C	293D156X_020C2_E3	3.0	6	1.5	0.27
15	D	293D156X_020D2_E3	3.0	6	0.9	0.41
22	B	293D226X_020B2_E3	4.4	6	2.1	0.20
22	C	293D226X_020C2_E3	4.4	6	1.1	0.32
22	D	293D226X_020D2_E3	4.4	6	0.7	0.46
33	C	293D336X_020C2_E3	6.6	6	1.0	0.33
33	D	293D336X_020D2_E3	6.6	6	0.7	0.46
47	D	293D476X_020D2_E3	9.4	6	0.7	0.46
47	E	293D476X_020E2_E3	9.4	6	0.6	0.52
68	D	293D686X_020D2_E3	13.6	6	0.7	0.46
68	E	293D686X_020E2_E3	13.6	6	0.6	0.52
100	E	293D107X_020E2_E3	20.0	8	0.5	0.57
25 WVDC AT + 85 °C, SURGE = 32 V . . . 17 WVDC AT + 125 °C, SURGE = 20 V						
0.47	A	293D474X_025A2_E3	0.5	4	12	0.08
0.68	A	293D684X_025A2_E3	0.5	4	8.4	0.09
1.0	A	293D105X_025A2_E3	0.5	4	7.6	0.10
1.0	B	293D105X_025B2_E3	0.5	4	5.0	0.13
1.5	A	293D155X_025A2_E3	0.5	6	6.7	0.11
1.5	B	293D155X_025B2_E3	0.5	6	4.6	0.14
2.2	A	293D225X_025A2_E3	0.6	6	6.3	0.11
2.2	B	293D225X_025B2_E3	0.6	6	3.8	0.15
3.3	B	293D335X_025B2_E3	0.8	6	3.1	0.17
3.3	C	293D335X_025C2_E3	0.8	6	2.3	0.22
4.7	A	293D475X_025A2_E3	1.2	6	5.5	0.12
4.7	B	293D475X_025B2_E3	1.2	6	2.8	0.17
4.7	C	293D475X_025C2_E3	1.2	6	2.0	0.24

* For 10 % tolerance, specify "9"; for 20 % tolerance, change to "0".





STANDARD/EXTENDED RATINGS

CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DC LEAKAGE AT + 25 °C (μ A)	MAX. DF AT + 25 °C 120 Hz (%)	MAX. ESR AT + 25 °C 100 kHz (Ohms)	MAX. RIPPLE 100 kHz I _{rms} (Amps)
25 WVDC AT + 85 °C, SURGE = 32 V . . . 17 WVDC AT + 125 °C, SURGE = 20 V						
6.8	B	293D685X_025B2_E3	1.7	6	2.4	0.19
6.8	C	293D685X_025C2_E3	1.7	6	1.7	0.25
10	B	293D106X_025B2_E3	2.5	6	2.3	0.19
10	C	293D106X_025C2_E3	2.5	6	1.5	0.27
10	D	293D106X_025D2_E3	2.5	6	1.0	0.39
15	C	293D156X_025C2_E3	3.8	6	1.2	0.30
15	D	293D156X_025D2_E3	3.8	6	0.8	0.43
22	D	293D226X_025D2_E3	5.5	6	0.7	0.46
33	D	293D336X_025D2_E3	8.3	6	0.7	0.46
33	E	293D336X_025E2_E3	8.3	6	0.6	0.52
47	E	293D476X_025E2_E3	11.8	6	0.6	0.52
35 WVDC AT + 85 °C, SURGE = 46 V . . . 23 WVDC AT + 125 °C, SURGE = 28 V						
0.10	A	293D104X_035A2_E3	0.5	4	20	0.06
0.15	A	293D154X_035A2_E3	0.5	4	18	0.07
0.22	A	293D224X_035A2_E3	0.5	4	15	0.07
0.33	A	293D334X_035A2_E3	0.5	4	13	0.08
0.47	A	293D474X_035A2_E3	0.5	4	10	0.09
0.47	B	293D474X_035B2_E3	0.5	4	8	0.10
0.68	A	293D684X_035A2_E3	0.5	4	7.6	0.10
0.68	B	293D684X_035B2_E3	0.5	4	6.5	0.11
1.0	A	293D105X_035A2_E3	0.5	4	7.5	0.10
1.0	B	293D105X_035B2_E3	0.5	4	5.0	0.13
1.5	B	293D155X_035B2_E3	0.5	6	4.2	0.14
1.5	C	293D155X_035C2_E3	0.5	6	3.8	0.17
2.2	B	293D225X_035B2_E3	0.8	6	3.8	0.15
2.2	C	293D225X_035C2_E3	0.8	6	2.9	0.20
3.3	B	293D335X_035B2_E3	1.2	6	3.5	0.16
3.3	C	293D335X_035C2_E3	1.2	6	2.1	0.23
4.7	C	293D475X_035C2_E3	1.6	6	1.9	0.24
4.7	D	293D475X_035D2_E3	1.6	6	1.3	0.34
6.8	C	293D685X_035C2_E3	2.4	6	1.8	0.25
6.8	D	293D685X_035D2_E3	2.4	6	1.1	0.37
10	C	293D106X_035C2_E3	3.5	6	1.6	0.26
10	D	293D106X_035D2_E3	3.5	6	0.8	0.43
15	D	293D156X_035D2_E3	5.3	6	0.7	0.46
15	E	293D156X_035E2_E3	5.3	6	0.7	0.49
22	D	293D226X_035D2_E3	7.7	6	0.6	0.52
22	E	293D226X_035E2_E3	7.7	6	0.6	0.52
50 WVDC AT + 85 °C, SURGE = 65 V . . . 33 WVDC AT + 125 °C, SURGE = 40 V						
0.10	A	293D104X_050A2_E3	0.5	4	19	0.06
0.15	A	293D154X_050A2_E3	0.5	4	17	0.07
0.15	B	293D154X_050B2_E3	0.5	4	14	0.08
0.22	A	293D224X_050A2_E3	0.5	4	15	0.07
0.22	B	293D224X_050B2_E3	0.5	4	12	0.08
0.33	A	293D334X_050A2_E3	0.5	4	14	0.07
0.33	B	293D334X_050B2_E3	0.5	4	10	0.09
0.47	A	293D474X_050A2_E3	0.5	4	12	0.08
0.47	B	293D474X_050B2_E3	0.5	4	8.4	0.10
0.47	C	293D474X_050C2_E3	0.5	4	6.7	0.13
0.68	B	293D684X_050B2_E3	0.5	4	7.6	0.11
0.68	C	293D684X_050C2_E3	0.5	4	5.9	0.14
1.0	B	293D105X_050B2_E3	0.5	4	6.7	0.11
1.0	C	293D105X_050C2_E3	0.5	4	4.6	0.16
1.5	B	293D155X_050B2_E3	0.8	6	6.0	0.12
1.5	C	293D155X_050C2_E3	0.8	6	3.4	0.18
2.2	C	293D225X_050C2_E3	1.1	6	2.9	0.20
2.2	D	293D225X_050D2_E3	1.1	6	2.1	0.27
3.3	C	293D335X_050C2_E3	1.7	6	2.5	0.21
3.3	D	293D335X_050D2_E3	1.7	6	1.7	0.30
4.7	D	293D475X_050D2_E3	2.4	6	1.2	0.37
6.8	D	293D685X_050D2_E3	3.4	6	0.9	0.41
6.8	E	293D685X_050E2_E3	3.4	6	0.9	0.43
10	D	293D106X_050D2_E3	5.0	6	0.8	0.43
10	E	293D106X_050E2_E3	5.0	6	0.8	0.45

* For 10 % tolerance, specify "9"; for 20 % tolerance, change to "0".



TYPICAL CURVES AT + 25 °C, IMPEDANCE AND ESR VS. FREQUENCY





Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.