


REV.	CHANGE	DATE	APPD.
A	MAKE DRAWING PER ECO 10058	--	--
B	ADD PACKAGING REQUIREMENT - ECO 13933	27DEC99	



LENGTH 1/2 ±1/16

DIAMETER .060 MAX

LEAD LENGTH 3.00 MIN

LEAD MATERIAL .008 DIA. TINNED DUMET

CURVE, MAT'L 11, E

USE GAUGE T-302

TESTING

60 100% LIMIT TEST

TEMP. (°F)	MINIMUM (OHMS)	NOMINAL (OHMS)	MAXIMUM (OHMS)	REF. TOL.
77	1960	2000	2040	±2%

75 PACK 10 PCS PER BOX

NOTE: WHEN DRAWING IS REVISED A COPY MUST BE SENT TO FEC

TOLERANCES UNLESS OTHERWISE NOTED, ALL DIMENSIONS ARE IN INCHES, AND TOLERANCES ARE AS SHOWN HERE. FRACTIONS = ±1/64 DECIMALS .XX = .01 .XXX = .005 ANGLES = 0°30'		DRAWN HS	DATE 26JUL96	 FENWAL ELECTRONICS 450 Fortune Boulevard, Milford, MA 01757-1745 (508) 478-6000 / FAX (508) 473-6035			
		CHECKED JF	DATE 7/26/96				
		APPROVED DL	DATE 7/26/96	TITLE THERMISTOR for PROBE ASSEMBLY			
USED ON		This information is the property of FENWAL ELECTRONICS. It is submitted in confidence, and is not to be disclosed or utilized without written permission.					
SHEET 1	OF 1	DO NOT SCALE DRAWING		SCALE --	SIZE A	DRAWING NUMBER 120-202EAD-Q02	REV. B