

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

33472-0709

Status:

Active

Overview:

MX150™ Sealed Connector System

Description:

MX150™ Sealed Female Connector, Dual Row, 6 Circuits, Polarization A, with Connector Position Assurance, with Clip Slot, Black, 1 Plugged Cavity



Series

image - Reference only

Documents:

Drawing (PDF)

Product Specification PS-33472-000 (PDF)

Application Specification AS-33472-100 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Comments

More Detailed Tech Information

Overview

Product Name

UPC

Crimp Housings

33472

Power, Wire-to-Wire

No Connector Position Assurance (CPA)

<http://ewcap.uscarteams.org>

MX150™ Sealed Connector System

MX150™

883906210854

Physical

Circuits (maximum)

Circuits Detail

Color - Resin

Gender

Glow-Wire Compliant

Keying to Mating Part

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

6

6

Green, Natural

Female

No

Yes

Yes

Modified Polystyrene Alloy

10.027/g

2

Bag

No

3.50mm

3.50mm

Yes

No

-40°C to +125°C

Electrical

Current - Maximum per Contact

22A

Material Info

Old Part Number

CVP33472-0709

Reference - Drawing Numbers

Application Specification

Product Specification

Sales Drawing

AS-33472-100

PS-33472-000

SD-33472-071

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

33472Series

Mates With

33482 Male Dual Row Sealed Connector

Use With

33012 MX150™ Female Terminal,

34345-0001 MLX 150 Cavity Plug Sealed

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION