




73929


WIRING DIAGRAM			
SFP		DB-9	
PIN	SIGNAL	PIN	SIGNAL
19	Tx-	9	Rx-
18	Tx+	5	Rx+
13	Rx+	1	Tx+
12	Rx-	6	Tx-



SFP NOTES:

1. MATERIALS


- BACKSHELLS - NICKEL PLATED ZINC
 - LATCH - GLASS FILLED POLYCARBONATE
 - PCB - FR-4
 - RIVETS - TIN PLATED STEEL
2. IMPEDANCE MATCHING SFP (100 OHMS) TO DB-9 (150 OHMS)



DB-9 NOTES:

1. MATERIALS

- CONTACTS - GOLD PLATED BRASS
- SHIELD - TIN PLATED STEEL
- BOOT - BLACK PVC
- JACKSCREWS
- SCREW - STEEL
- HEAD - PVC

2. CHARACTERISTIC IMPEDANCE 150 ± 10 OHMS MEASURED DIFFERENTIAL

PART NUMBER	LENGTH
73929-1001	1 M $\pm$ 0.05 M
73929-1002	3 M $\pm$ 0.07 M
73929-1003	5 M $\pm$ 0.08 M
73929-1005	2 M $\pm$ 0.06 M
73929-1006	4 M $\pm$ 0.07 M

CABLE NOTES:

1. CHARACTERISTIC IMPEDANCE 150 ± 10 OHMS MEASURED DIFFERENTIAL
2. SEE MOLEX DRAWINGS SD-71153-7*** FOR FURTHER DETAILS

EC NO: UOT20020803 DRWN: DSLEWIS 2002/03/08 CHK: DDVE 2002/02/12 APPR: DDVE 2002/02/14	QUALITY SYMBOLS ▽ - 0 ◁ - 0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)			SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	REVISE ON CAD ONLY		
				mm	INCH	DIMENSION STYLE		TITLE SFP PLUG TO MALE DB-9 FIBRE CHANNEL (150 OHM) CABLE ASSEMBLY			
						MM ONLY					
			4 PLACES	± ---	± ---	DRAWN BY	DATE	MOLEX MOLEX INCORPORATED			
			3 PLACES	± ---	± ---	DSL	2001/12/13				
			2 PLACES	± 0.25	± ---	CHECKED BY	DATE	MATERIAL NO 739291001 DOCUMENT NO SD-73929-100 SHEET NO 1 OF 1			
			1 PLACE	± 0.3	± ---	DLD	2001/12/17				
			ANGULAR ± 2 °			APPROVED BY	DATE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
			DRAFT WHERE APPLICABLE			DLD	1002/12/17				
			MUST REMAIN WITHIN DIMENSIONS								
A	REV										B