



# Three phase full Bridge with Trench MOSFETs in DCB isolated high current package

$$V_{DSS} = 75 \text{ V}$$

$$I_{D25} = 118 \text{ A}$$

$$R_{DSon \text{ typ.}} = 3.7 \text{ m}\Omega$$



| MOSFETs   |                                                       |                 |   |
|-----------|-------------------------------------------------------|-----------------|---|
| Symbol    | Conditions                                            | Maximum Ratings |   |
| $V_{DSS}$ | $T_{VJ} = 25^{\circ}\text{C to } 150^{\circ}\text{C}$ | 75              | V |
| $V_{GS}$  |                                                       | $\pm 20$        | V |
| $I_{D25}$ | $T_C = 25^{\circ}\text{C}$                            | 118             | A |
| $I_{D90}$ | $T_C = 90^{\circ}\text{C}$                            | 85              | A |
| $I_{F25}$ | $T_C = 25^{\circ}\text{C (diode)}$                    | 120             | A |
| $I_{F90}$ | $T_C = 90^{\circ}\text{C (diode)}$                    | 78              | A |

## Applications

### AC drives

- in automobiles
  - electric power steering
  - starter generator
- in industrial vehicles
  - propulsion drives
  - fork lift drives
- in battery supplied equipment

## Features

- MOSFETs in trench technology:
  - low  $R_{DSon}$
  - optimized intrinsic reverse diode
- package:
  - high level of integration
  - high current capability 300 A max.
  - aux. terminals for MOSFET control
  - terminals for soldering or welding connections
  - isolated DCB ceramic base plate with optimized heat transfer
- Space and weight savings

## Package options

- 3 lead forms available
  - straight leads (SL)
  - SMD lead version (SMD)
  - bent leads (BL)

| Symbol       | Conditions                                                                                                | Characteristic Values                                |      |      |     |
|--------------|-----------------------------------------------------------------------------------------------------------|------------------------------------------------------|------|------|-----|
|              |                                                                                                           | (T <sub>VJ</sub> = 25°C, unless otherwise specified) |      |      |     |
|              |                                                                                                           | min.                                                 | typ. | max. |     |
| $R_{DSon}$   | on chip level at<br>$V_{GS} = 10 \text{ V}; I_D = 60 \text{ A}$                                           | $T_{VJ} = 25^{\circ}\text{C}$                        |      | 3.7  | mΩ  |
|              |                                                                                                           | $T_{VJ} = 125^{\circ}\text{C}$                       |      | 8.4  | mΩ  |
| $V_{GS(th)}$ | $V_{DS} = 20 \text{ V}; I_D = 1 \text{ mA}$                                                               | 2                                                    |      | 4    | V   |
| $I_{DSS}$    | $V_{DS} = V_{DSS}; V_{GS} = 0 \text{ V}$                                                                  | $T_{VJ} = 25^{\circ}\text{C}$                        |      | 0.1  | μA  |
|              |                                                                                                           | $T_{VJ} = 125^{\circ}\text{C}$                       |      |      | mA  |
| $I_{GSS}$    | $V_{GS} = \pm 20 \text{ V}; V_{DS} = 0 \text{ V}$                                                         |                                                      |      | 0.2  | μA  |
| $Q_g$        | $V_{GS} = 10 \text{ V}; V_{DS} = 55 \text{ V}; I_D = 125 \text{ A}$                                       |                                                      | 100  |      | nC  |
| $Q_{gs}$     |                                                                                                           |                                                      | 19   |      | nC  |
| $Q_{gd}$     |                                                                                                           |                                                      | 28   |      | nC  |
| $t_{d(on)}$  | $V_{GS} = 10 \text{ V}; V_{DS} = 30 \text{ V}$<br>$I_D = 80 \text{ A}; R_G = 39 \Omega$<br>inductive load |                                                      | 80   |      | ns  |
| $t_r$        |                                                                                                           |                                                      | 80   |      | ns  |
| $t_{d(off)}$ |                                                                                                           |                                                      | 510  |      | ns  |
| $t_f$        |                                                                                                           |                                                      | 100  |      | ns  |
| $E_{on}$     |                                                                                                           |                                                      | 0.12 |      | mJ  |
| $E_{off}$    |                                                                                                           |                                                      | 0.40 |      | mJ  |
| $E_{recoff}$ |                                                                                                           |                                                      | 0.02 |      | mJ  |
| $R_{thJC}$   | with heat transfer paste (IXYS test setup)                                                                |                                                      | 1.3  | 1.0  | K/W |
| $R_{thJH}$   |                                                                                                           |                                                      |      | 1.6  | K/W |

**Source-Drain Diode**


| Symbol   | Conditions                                                                        | Characteristic Values |      |      |               |
|----------|-----------------------------------------------------------------------------------|-----------------------|------|------|---------------|
|          |                                                                                   | min.                  | typ. | max. |               |
| $V_{SD}$ | (diode) $I_F = 60\text{ A}$ ; $V_{GS} = 0\text{ V}$                               |                       | 0.9  | 1.2  | V             |
| $t_{rr}$ | $I_F = 80\text{ A}$ ; $-di_F/dt = 800\text{ A}/\mu\text{s}$ ; $V_R = 30\text{ V}$ |                       | 70   |      | ns            |
| $Q_{RM}$ |                                                                                   |                       | 1.1  |      | $\mu\text{C}$ |
| $I_{RM}$ |                                                                                   |                       | 30   |      | A             |

( $T_J = 25^\circ\text{C}$ , unless otherwise specified)

**Component**

| Symbol     | Conditions                                                                                                | Maximum Ratings |                  |
|------------|-----------------------------------------------------------------------------------------------------------|-----------------|------------------|
| $I_{RMS}$  | per pin in main current paths (P+, N-, L1, L2, L3)<br>may be additionally limited by external connections | 300             | A                |
| $T_{VJ}$   |                                                                                                           | -55...+175      | $^\circ\text{C}$ |
| $T_{stg}$  |                                                                                                           | -55...+125      | $^\circ\text{C}$ |
| $V_{ISOL}$ | $I_{ISOL} \leq 1\text{ mA}$ , 50/60 Hz, $f = 1\text{ minute}$                                             | 1000            | V~               |
| $F_C$      | mounting force with clip                                                                                  | 50 - 250        | N                |




| Symbol                   | Conditions                                                          | Characteristic Values |      |      |                  |
|--------------------------|---------------------------------------------------------------------|-----------------------|------|------|------------------|
|                          |                                                                     | min.                  | typ. | max. |                  |
| $R_{pin\text{ to chip}}$ | with heatsink compound                                              |                       | 0.6  |      | $\text{m}\Omega$ |
| $C_P$                    | coupling capacity between shorted pins and mounting tab in the case |                       | 160  |      | pF               |
| Weight                   | typ.                                                                |                       | 25   |      | g                |

**Equivalent Circuits for Simulation**
**Thermal Response**


junction - case (typ.)

$$C_{th1} = 0.039\text{ J/K}; R_{th1} = 0.28\text{ K/W}$$

$$C_{th2} = 0.069\text{ J/K}; R_{th2} = 0.57\text{ K/W}$$

**Straight Leads GWM 120-0075P3-SL**

**Bent Leads GWM 120-0075P3-BL**

**Surface Mount Device GWM 120-0075P3-SMD**


| Leads    | Ordering | Part Name & Packing Unit Marking | Part Marking   | Delivering Mode | Base Qty. | Ordering Code   |
|----------|----------|----------------------------------|----------------|-----------------|-----------|-----------------|
| Straight | Standard | GWM 120-0075P3 - SL              | GWM 120-0075P3 | Blister         | 36        | 502 843         |
| SMD      | Standard | GWM 120-0075P3 - SMD             | GWM 120-0075P3 | Blister         | 36        | 502 850         |
| Bent     | Standard | GWM 120-0075P3 - BL              | GWM 120-0075P3 | Blister         | 36        | contact factory |




Fig. 1 Drain source breakdown voltage  $V_{DS}$  vs. junction temperature  $T_J$




Fig. 2 Typical transfer characteristic




Fig. 3 Typical output characteristic




Fig. 4 Typical output characteristic




Fig. 5 Drain source on-state resistance  $R_{DS(on)}$  versus junction temperature  $T_J$




Fig. 6 Drain source on-state resistance  $R_{DS(on)}$  versus  $I_D$




Fig. 7 Gate charge characteristic




Fig. 8 Drain current  $I_D$  vs. case temperature  $T_C$




Fig. 9 Typ. turn-on energy & switching times vs. collector current, inductive switching




Fig. 10 Typ. turn-off energy & switching times vs. collector current, inductive switching




Fig. 11 Typ. turn-on energy & switching times vs. gate resistor, inductive switching




Fig. 12 Typ. turn-off energy & switching times vs. gate resistor, inductive switching




Fig. 13 Reverse recovery time  $t_{rr}$  of the body diode vs.  $di/dt$




Fig. 14 Reverse recovery current  $I_{RM}$  of the body diode vs.  $di/dt$




Fig. 15 Reverse recovery charge  $Q_{rr}$  of the body diode vs.  $di/dt$




Fig. 16 Source current  $I_S$  vs. source drain voltage  $V_{SD}$  (body diode)




Fig. 17 Definition of switching times




Fig. 18 Typ. therm. impedance junction to heatsink  $Z_{thJC}$