

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

JAN ,2006.

© COPYRIGHT 2006 BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

D

ECO-09-016840



10AUG2009

AM

BOB

NOTES:

- 1 PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3 Au PLATING
- 4 Ni PLATING
- 5 THIS ITEM MUST BE WHITE
- 6 HAND TOOL : 9-1478240-0
- 7 DIE SET : 9-1478242-0
- 8 ELECTRICAL CHARACTERISTICS
FREQUENCY RANGE: DC - 2 GHz
NOMINAL IMPEDANCE: 75 Ohm
INSULATION RESISTANCE: 5000 MOhm
WORKING VOLTAGE: 500 Volts RMS at Sea Level
DIELECTRIC WITHSTAND VOLTAGE: 1500 Volts RMS Max
CONTACT RESISTANCE:
CENTRE CONTACT: 1.50 mOhm Max
OUTER CONTACT: 0.20 mOhm Max
VSWR @ 2GHz: 1.25:1 Max
INSERTION LOSS dB @ x 2 GHz: 0.30 Max
- 9 MECHANICAL CHARACTERISTICS
COUPLING RETENTION FORCE: 445N Min
CABLE RETENTION FORCE: 170N Min
DURABILITY: 500 Cycles Min
- 10 ENVIRONMENTAL CHARACTERISTICS
OPERATING TEMPERATURE: -65 to +165 DegC



OBSOLETE

			1	BRASS	4	SHELL	13
			1	PTFE		INSULATION	12
			1	SILICONE RUBBER	5	GASKET	11
			1	BRASS	4	RETAINING RING	10
			1	SPRING STEEL		SPRING	9
			1	BRASS	4	WASHER	8
			1	BRASS	4	BODY II	7
			1	BRASS	3	CONTACT II	6
			1	BRASS	4	BODY I	5
			1	BRASS	4	CHASSIS	4
			1	PTFE		INSULATION	3
			1	BRASS	4	FERRULE	2
			1	BRASS	3	CONTACT I	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		4	1	QUANTITY PER ASSY		PARTS LIST	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN J.SANDWELL 25JAN06

CHK S.PARLOW 25JAN06

APVD F.WHEELER-KING 25JAN06

PRODUCT SPEC

APPLICATION SPEC

411-3247

WEIGHT -

CUSTOMER DRAWING

Tyco Electronics

Tyco Electronics Corporation
Kunshan,Jiangsu,RPC 215321

NAME

BNC ELBOW PLUG CRIMP 75 OHM
RG59B/U, 62A/U, 140/U, 210/U, URM90,
KX6A, KX25, KX52, KX53

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3





00779

C-1337525

SCALE NTS

SHEET 1 OF 1

REV D

RECOMMENDED
CENTRE CONTACT
A/F HEXRECOMMENDED
CRIMP SLEEVE
A/F HEXRECOMMENDED
CABLE STRIPPING DIM'SDIMENSIONS:
mm

MATERIAL

SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH

-