












REV.	DATE	DESCRIPTION
NC	04/20/99	INITIAL RELEASE
A	06/11/03	UPDATE DRAWING FORMAT/ADD MOUNTING HOLE DIMS.



RECOMMENDED
CABLE STRIPPING DIM'S



RECOMMENDED MOUNTING
HOLE DIMENSIONS



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex					
8						DRAWN	G.R.S.	06/11/03							
7	HEAT SHRINK					CHECKED									
6	FERRULE	COPPER	GOLD	1						PART DESCRIPTION					
5	HEX NUT	BRASS	GOLD	1						SMA REVERSE POLARIZED BULKHEAD CRIMP JACK (FOR RG-178B/U, 196A/U CABLE)					
4	BARREL	BRASS	GOLD	1						PART NO.					
3	CONTACT PIN	BER. COPPER	GOLD	1						132220RP					
2	INSULATOR	TEFLON	NATURAL	1											
1	HOUSING/BODY	BRASS	GOLD	1											
	DESCRIPTION	MATERIAL	FINISH	QTY				CAD FILE	DWG. NO.			REV.	SIZE	SCALE	
								C:/132/132220RP.DWG	132220RP.DWG			A	A	NA	