

ing / DESIGN
3





Technical drawing of a screwdriver tip. Dimension (a) indicates a minimum length of 7 units. Dimension (b) indicates the total length of the tip. A magnification scale of 5:1 is shown below the drawing.

Au: vergoldet
GOLD
(a) PIN: min. 0.8 μm Au ueber/OVER 1.0 μm - 2.2 μm Ni
(b) Kontaktkoerper/BODY: 0.8 μm - 2.0 μm Sn

NOTES
Bemerkungen

- 1 Datumcode (Woche/Jahr z.B. KW 38/Jahr 2009)
und TE-Revision (z.B. Rev. A)
DATE CODE (WEEK/YEAR E.G. WEEK NUMBER 38/YEAR 2009)
AND TE REVISION (E.G. Rev. A)
- 2 Passend zu Buchsenkontakt siehe Zeichnung 929454
SUITABLE FOR SOCKET CONTACT SEE DRAWING 929454
- 3 Einzelheiten der Ausfuehrung bleiben dem Hersteller ueberlassen
DETAILS OF DESIGN ARE LEFT TO MANUFACTURER
- 4 Nur fuer FLR-Leitung nach DIN 72551 Teil 6
FOR FLR-CONDUCTOR ACCORDING TO DIN 72551-6 ONLY
- 5 nicht fuer Neuanwendung
NOT FOR NEW APPLICATION
- 6 zugverstaerkte Leitung nach LV 112-4
REINFORCED WIRE ACCORDING LV 112-4
- 7 Bei doppelt fallenden Werkzeugen wird die erste Ueberfeder
mit einer Kennzeichnung "-" versehen
WITH DOUBLE OUT DIES THE FIRST SPRING WILL BE PROVIDED
WITH AN INDICATION "-"
- 8 Varianten von Design1 werden durch die entsprechenden
Versionen von Design2 ersetzt
VARIANTS OF DESIGN1 ARE SUPERSEDED BY CORRESPONDING
VERSIONS OF DESIGN2



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.Garcia 06JAN1999 CHK R.Jettler 06JAN1999 APVD M.Bleicher 13AUG2003		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 		NAME MQS Tabellenzeichnung Stiftkontakt TABLE PIN CONTACT	
MATERIAL -		FINISH -		SIZE A1	
WEIGHT -		APPLICATION SPEC 108-18030 114-18021 / -18025		CASE CODE 00779	
CUSTOMER DRAWING		DRAWING NO C=929453		RESTRICTED TO -	
		SCALE 10:1		SHEET 1 OF 1 REV	