

[→ Honeywell.com](#) [→ Automation & Control Solutions](#)[HOME](#)[ABOUT US](#)[KEY INDUSTRIES SERVED](#)[PRODUCTS & INFORMATION](#)[NEWS & EVENTS](#)[SALES & SUPPORT](#)[LOGIN](#)

Honeywell Sensing and Control

Search

**HOA6970-T55**
Optoschmitt Sensors (Transmissive)
(Home : Products)

narrow your search

Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1705)
- Sensors (6325)
- Switches (9763)
- Wireless (4)

Technology

- Electromechanical (9306)
- Magnetic (541)
- Microstructure (1577)
- Optical/Infrared (1056)
- Thick Film (1764)
- More...

white papers

Basic Switches Are Not Created Equal

Applying Precision Switches

Sensors for Medical Devices

New Ways to Measure Torque

Choosing Safety Switches

Specifying Hour Meters

SAW Torque Sensor Technology

white papers

Basic Switches Are Not Created Equal

Applying Precision Switches

Sensors for Medical Devices

New Ways to Measure Torque

Choosing Safety Switches

Specifying Hour Meters

SAW Torque Sensor Technology

Need help?

[Click here to contact us](#)

Actual product appearance may vary.

HOA096X/HOA097X Series IR Opaque Optoschmitt Sensor,
Transistor Output, Two Mounting Tabs, Plastic Package

[Sales & Service](#)[Distributor Inventory](#)[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

| | |
|--|--|
| Series Name | HOA696X/HOA697X |
| Product Type | IR Switch |
| Output | Totem-Pole |
| Output Logic | Buffer |
| Mounting Configuration | Two Mounting Tabs |
| Package Components | Plastic |
| Package Color | Black |
| Continuous Forward Current | 50 mA |
| Forward Voltage | 1.6 V |
| Reverse Breakdown Voltage | 3 V |
| Reverse Current | 10 µA |
| Maximum Trigger Current | 15 mA |
| Housing Material | Polysulfone, Opaque |
| Power Dissipation | 100 mW |
| Operating Temperature | -40 °C to 70 °C [-40 °F to 158 °F] |
| Hysteresis (H) | 0.05 |
| Operating Supply Voltage | 4.5 V to 7.0 V |
| Supply Voltage | 7.0 Vdc |
| High Level Output Voltage | 2.4 V minimum |
| High Level Supply Current | 15 mA |
| Low Level Output Voltage | 0.4 V maximum |
| Low Level Supply Current | 15 mA |
| Short Circuit Output Current | -20 mA to -100 mA |
| Output Rise Time | 70 ns |
| Output Fall Time | 70 ns |
| Propagation Delay&44; Low-High&44;High-Low | 5.0 µs |
| Duration of Output Short Vcc or Ground | 1.0 second |
| IRED Trigger Current | 15 mA |
| Comment | Output is LO when incident light intensity is above the turn-on threshold level. |
| Availability | Global |
| Sensor Aperture | 1,52 mm x 1,27 mm [0.060 in x 0.050 in] |
| Slot Width | 3,18 mm [0.125 in] |

contacts

Customer Service

Technical Support

Global Sales & Service

View Site Demo

Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.

Meet Dr. Larry



my links

[Login to iCOM](#)

[Login as Rep/AD](#)

[Login as Guest](#)

[Login to Digital University](#)

News Center

HONEYWELL EXPANDS
HAZARDOUS AREA LIMIT
SWITCH FAMILY TO FEATURE
A STAINLESS-STEEL SWITCH

HONEYWELL RELEASES
UNLIMITED POTENTIAL WITH
NEW LIMITLESS™ WIRELESS
SWITCHES

HONEYWELL'S XYR6000
WIRELESS POSITION SENSOR
ENABLES MONITORING IN
HAZARDOUS AREAS AND
REMOTE LOCATIONS

MICRO SWITCH
Anniversary site

[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)