









FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE TABLE



SECTION Y-Y



mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HEADERS	
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM	title	
L	V82054	EPK	11/12/98	angles	.XX±.01/.3		VRM 8 HEADER ASS'Y	
M	v82161	EPK	12/10/98	linear	.XXX±.005/.13	scale 1:1	dwg no	
N	V91079	EPK	5/10/99	0°±2'	.XXXX±.0020/.051		95798	
P	V01868	MDF	7/31/00	dr	M. CLOUSER	FCI	sheet 1 of 4	
R	V03-1222	PJ	11/18/03	enr	L. FYE		A3	
S	V04-0262	HTB	3/18/04	chr	L. FYE	type	Product Customer Drawing	
T	M06-0289	AGS	7/29/06	appd	L. FYE			
sheet index	revision	T	T	T	T			
	sheet	1	2	3	4			


form: A3

PDM: Rev:T


STATUS:Released

Printed: Jun 03, 2008

PRODUCT NUMBER
SEE TABLE



RECOMMENDED PCB HOLE LAYOUT
FOR HOUSING



RECOMMENDED PCB LAYOUT


NOTES:

- ① MOLDED MATERIAL: HIGH TEMP RESIN
PER UL 94 V-0
COLOR: PANTONE 4545 (OFF WHITE).
- ② PIN MATERIAL: 3/4 HARD PHOS BRONZE
UNS C51000.
- ③ PIN RETENTION TO BE 3 LB/1.36 KG
MIN IN EITHER DIRECTION.
- ④ SURFACE INDICATED MUST BE PARALLEL TO
DATUM -C- WITHIN $\pm 4^\circ$.
- ⑤ "R" FOLLOWING P/N INDICATES RETENTION
FEATURE.
- ⑥ PRESS FIT PINS 95798-5XX SERIES.
- ⑦ OPTIONAL POLARIZING FEATURE.
- ⑧ CRITICAL CONTACT AREA ON ALL FOUR SIDES.
- ⑩ PACKAGE IN PLASTIC TRAYS.
- ⑪ LUBRICATION - (ZIP-CHEM TO C-26)


mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HEADERS
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
T					angles	.XX±.01/.3	VRM 8 HEADER ASS'Y
					linear	.XXX±.005/.13	
					0°±2'	.XXXX±.0020/.051	
			dr	M. CLOUSER	6/12/95	scale 1:1	 dwg no 95798 sheet2 of 4 size A3
			enr	L. FYE	6/12/95		
			chr	L. FYE	6/12/95		
			appd	L. FYE	6/12/95		
sheet index	revision sheet						type Product Customer Drawing

PRODUCT NUMBER


SEE TABLE



DETAIL "G"
ROTATED 90°
SCALE 3:1
NOTE 5



DETAIL "H"
PRESS-FIT TAILS
ROTATED 90°
SCALE 3:1
NOTE 6



DETAIL "M"
SCALE 3:1
NOTE 7

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HEADERS				
ltr	ecn	no	dr	date	tolerances unless otherwise specified						title			
T					angles	linear	.XX±.01/.3		INCH/MM	VRM 8 HEADER ASS'Y				
					.XXX±.005/.13									
					0°±2'		.XXXX±.0020/.051		scale 1:1					
			dr	M. CLOUSER	6/12/95									
			enr	L. FYE	6/12/95									
			chr	L. FYE	6/12/95									
			appd	L. FYE	6/12/95									
sheet index		revision sheet								dwg no		sheet3 of 4		size
										95798				A3
										type		Product Customer		Drawing

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NUMBER	CONTACT PLATING	TAIL LENGTH	TAIL PLATING	POLARIZING PEG	LUBRICATION NOTE 11
95798-001			U N A V A I L A B L E		
-002	15u"/0.38 GXT OVER 50u"/1.27u Ni	.122/3.10	15μ"/0.38μ GXT OVER 50μ"/1.27μ Ni	NO	NO
-003			U N A V A I L A B L E		
-011			U N A V A I L A B L E		
-012			U N A V A I L A B L E		
-201			U N A V A I L A B L E		
-202			U N A V A I L A B L E		
-203			U N A V A I L A B L E		
-204			U N A V A I L A B L E		
-301			U N A V A I L A B L E		
95798-502			U N A V A I L A B L E		

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HEADERS			
ltr	ecn	no	dr	date	tolerances unless otherwise specified					title			
T					angles	linear	.XX±.01/.3 .XXX±.005/.13 .XXXX±.0020/.051	scale 1:1		VRM 8 HEADER ASS'Y			
					0°±2'								
			dr	M. CLOUSER	6/12/95			dwg no		sheet4 of 4		size	
			enr	L. FYE	6/12/95			95798		A3			
			chr	L. FYE	6/12/95								
			appd	L. FYE	6/12/95								
sheet index		revision sheet							type	Product	Customer	Drawing	

form: A3