

MR2535

AUTOMOTIVE TRANSIENT SUPPRESSORS


V_{BR} : 20 Volts
I_o : 35 Amperes

FEATURES :

- * Avalanche Voltage 24 to 32 Volts
- * High Power capability
- * Increased Capacity by Parallel Operation
- * Pb / RoHS Free

MECHANICAL DATA :

- * Case : Molded plastic
- * Epoxy : UL94V-O rate flame retardant
- * Polarity : Cathode polarity band
- * Mounting position : Any
- * Weight : 1.624 grams



Dimensions in inches and (millimeter)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating at 25 °C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

RATING	SYMBOL	VALUE	UNIT
Maximum DC Peak Repetitive Reverse Voltage	V _{RRM}	20	V
Maximum Working Peak Reverse Voltage	V _{RWM}	20	V
Maximum DC Blocking Voltage	V _R	20	V
Maximum Breakdown Voltage (I _R = 100 mA, T _c = 25°C) (1)	V _{BR(max)}	32	V
Minimum Breakdown Voltage (I _R = 100 mA, T _c = 25°C) (1)	V _{BR(min)}	24	V
Average Rectified Forward Current (Single Phase, Resistive Load, 60 Hz, T _c = 150 °C)	I _{F(AV)}	35	A
Maximum Repetitive Peak Reverse Surge Current (Time Constant = 10 ms, Duty Cycle ≤ 1%, T _c = 25 °C)	I _{RSM}	110	A
Maximum Non-Repetitive Peak Surge Current Surge Supplied at Rated Load Conditions, Halfwave, Single Phase	I _{FSM}	600	A
Maximum Instantaneous Forward Voltage (I _F = 100 A T _c = 25 °C) (1)	V _F	1.1	V
Maximum Reverse Current (V _R = 20 V, T _c = 25 °C)	I _R	200	nA
Typical Thermal Resistance Junction to Case	R _{θJC}	0.8	°C/W
Junction Temperature Range	T _J	- 65 to + 175	°C
Storage Temperature Range	T _{STG}	- 65 to + 175	°C

Note : (1) Pulse Test : Pulse Width ≤ 300μs, Duty Cycle ≤ 2%.