



New Innovation
New Impression
New Imagination

At NEC LCD Technologies, Ltd.,
the 3 New "I's inspire our mission
to create next-generation displays.

Environmental Initiatives

Our products are RoHS compliant.

In February 2003, the European Union (EU) issued the RoHS Directive*¹ aimed at restricting the use of certain hazardous substances. As a result, electrical and electronic equipment containing any of the six target substances (lead, mercury, cadmium, hexavalent chromium, PBB*² and PBDE*³) is restricted from the EU market, effective from July 1, 2006. Out of concern for the environment, NEC LCD Technologies began reducing the use of hazardous substances in our LCD modules prior to the RoHS directive. We have completely eliminated all of the six substances targeted in the RoHS directive so that our products are now RoHS compliant.

*1 RoHS: Restriction of the use of certain hazardous substances in electrical and electronic equipment

*2 PBB: Polybrominated biphenyls

*3 PBDE: Polybrominated diphenyl ethers

(Note)

*The maximum concentration level allowed by the RoHS is 1000ppm for lead, mercury, hexavalent chromium, PBB, PBDE, and 100ppm for cadmium. (Indicates the concentration level in each section/part [homogeneous material]) Moreover, the Amendment to the RoHS Directive indicates applications that are exempt from Directive requirements, such as the lead inside high-melting point solder of electrical appliance parts and mercury amounting to less than 5mg in small fluorescent tubes.

*The RoHS Directive does not apply to spare parts for electrical and electronic equipment put on the market before July 1, 2006. Therefore, the following products are exempt from the RoHS Directive

①Products with maintenance notification that were shipped before the end of March 2005.

②Repair and maintenance of products produced before March 2006 that were not Directive-compliant.

*Some products and repair parts may be exempt from the above. Please consult your sales personnel for details.

*The information appearing in LCD News Vol. 12 is valid as of October, 2008 and subject to change without notice. For details, please contact an NEC LCD Technologies sales representative.

*The Copyright to this document belongs to NEC LCD Technologies. No part of this document will be used, reproduced or copied without prior written consent of NEC LCD Technologies.

*All monitor screen images in this document are simulated pictures unless otherwise indicated.

*New Is is a registered trademark of NEC LCD Technologies in Japan, Australia, Austria, Belgium, Canada, Denmark, Finland, France, Germany, Hong Kong, Korea, Luxembourg, Mexico, Netherland, Norway, Singapore, Spain, Sweden, Switzerland, Taiwan and United Kingdom, and a trademark in China, Italy, United States and other countries.(As of September 2008)

*SA-SFT, UA-SFT, SR-NLT and ST-NLT are registered trademarks or trademarks of NEC LCD Technologies in Japan and other countries.(As of September 2008)

*SFT, NLT and VIT are abbreviations, respectively, for Super Fine TFT, Natural Light TFT and Value Integrated TFT.

*NEC LCD Technologies does and will not assume any liability for infringement of patents, copyrights or other intellectual property rights of any third party arising out of or in connection with application of the products described herein except for that directly attributable to mechanisms and workmanship thereof. No license, express or implied, is granted under any patent, copyright or other intellectual property right of NEC LCD Technologies.

*Some electronic parts/components would fail or malfunction at a certain rate. In spite of every effort to enhance reliability of products by NEC LCD Technologies, the possibility of failures and malfunction might not be avoided entirely. To prevent the risks of damage to death, human bodily injury or other property arising out thereof or in connection therewith, each customer is required to take sufficient measures in its safety designs and plans including, but not limited to, redundant system, fire-containment and anti-failure.

The products are classified into three quality grades: "Standard", "Special", and "Specific" of the highest grade of a quality assurance program at the choice of a customer. Each quality grade is designed for applications described below. Any customer who intends to use a product for application other than that of Standard quality grade is required to contact an NEC LCD Technologies sales representative in advance.

The **Standard quality grade** applies to the products developed, designed and manufactured in accordance with the NEC LCD Technologies standard quality assurance program, which are designed for such application as any failure or malfunction of the products (sets) or parts/components incorporated therein a customer uses are, directly or indirectly, free of any damage to death, human bodily injury or other property, like general electronic devices.

Examples: Computers, office automation equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment, industrial robots, etc.

The **Special quality grade** applies to the products developed, designed and manufactured in accordance with an NEC LCD Technologies quality assurance program stricter than the standard one, which are designed for such application as any failure or malfunction of the products (sets) or parts/components incorporated therein a customer uses might directly cause any damage to death, human bodily injury or other property, or such application under more severe condition than that defined in the Standard quality grade without such direct damage.

Examples: Control systems for transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, medical equipment not specifically designed for life support, safety equipment, etc.

The **Specific quality grade** applies to the products developed, designed and manufactured in accordance with the standards or quality assurance program designated by a customer who requires an extremely higher level of reliability and quality for such products.

Examples: Aircraft and air-control equipment, aerospace equipment, nuclear reactor control systems, medical equipment/devices/systems for life support, etc.

For purposes of NEC LCD Technologies catalogs, and data sheets and books, the Standard quality grade will apply to any product without indication of a quality grade.

(Note)

"NEC LCD Technologies" as used in this statement means NEC LCD Technologies, Ltd.

This pamphlet is produced using an environment-friendly printing method.

FSC-certified paper
for forest preservation



Soy Ink That's
Air- and Earth-Friendly



Waterless printing that
does not produce wastewater
containing harmful substances



Sales Offices

Taiwan Branch

7F, No.363 Fu Shing North Rd., Taipei, Taiwan, R.O.C.Tel: +886-2-2717-5775

NEC Electronics America, Inc.

2880 Scott Blvd., M/S SC 1800, Santa Clara, CA 95050 Tel: +1-408-588-6311
Web site: <http://www.am.necel.com/display/>

NEC Electronics(Europe)GmbH

Arcadiastrasse 10 D-40472 Duesseldorf, Germany Tel: +49-211-6503-01
Web site: <http://www.eu.necel.com/products/display/>

NEC LCD Technologies, Ltd.

1753 Shimonumabe, Nakahara-ku, Kawasaki, Kanagawa 211-8666 Japan

Tel: +81-44-435-1666

Web site: <http://www.nec-lcd.com/en/>

Oct. 2008 Vol.12
TFT-LCD Modules

Empowered by Innovation

NEC






Superior LCD solutions based upon NEC LCD Technologies' advanced core technologies

LCDs are gaining popularity as devices for displaying various types of information in many diverse environments. At the same time, customers are demanding greater sophistication and diversity from displays.

To meet the growing demand for higher image quality, smaller size, greater energy efficiency, higher added value, and improved environmental performance, NEC LCD Technologies offers various LCD products based on four core technologies: SFT Technology for outstanding image reproduction, NLT Technology for vivid images in any ambient light environment, VIT Technology for greater value, and integrated module technology called Adaptive Design Technology.

Based on our customer-oriented philosophy of seeing things from the customers' perspective, we strive to offer customers the best possible LCD solutions.



Four Core Technologies



Continual innovation toward higher image quality.

Image quality that specifications cannot adequately describe.

In LCD specifications the viewing angle refers to the maximum angle at which images can be viewed at an acceptable contrast ratio*1, such as 10:1. This angle is expressed as degrees (from the line perpendicular to the center of the screen). Since the contrast ratio is the only defining factor for image quality, an LCD can claim an 80-degree viewing angle even if the colors look completely different than when viewed from the front. Moreover, images on two LCD panels with the same maximum viewing angle but different LCD drivers can look very different when viewed from an angle.

An LCD varies the amount of light passing through the screen by applying voltage to liquid crystal molecules sandwiched between two polarizing plates and by changing the alignment and direction of the molecules. Many LCDs apply voltage in the vertical direction, which rotates the liquid crystal molecules vertically. But SFT displays apply voltage in the horizontal direction, which rotates the molecules horizontally. The amount of rotation depends on the voltage level and is used to vary the amount of light penetration. When the liquid crystal molecules are fully horizontal, their size appears identical regardless of the angle from which they are viewed. The difference in brightness and color at different viewing angles is therefore smaller with SFT displays than with conventional LCDs.

*1 The contrast ratio represents the contrast between the maximum brightness (white screen) and minimum brightness (black screen) in environments lacking any ambient light.



SFT Liquid Crystal Display



TN Liquid Crystal Display




* The above images are samples.


SFT technology also provides high-quality moving images.

Liquid crystal molecules tend to rotate more smoothly in the horizontal direction than the vertical direction. Since SFT LCDs enables display by rotating liquid crystal molecules horizontally, their response time is relatively fast, regardless of the magnitude of shift in gray scale. Moving images are also displayed very clearly because there is no sudden drop in response time between intermediate gray scales. There are no other technologies where liquid crystal molecules rotate vertically.

Response time of SA-SFT technology



Response time of TN technology



Spec Chart Response Time (sum of yellow-circled figures)

Although this is one indicator of LCD response time, it does not include the response time between intermediate gray scales.

Response Time Between Intermediate Gray Scales (shown by the orange circle)

Since most moving images consist primarily of changes between intermediate gray scales (even when the response time in the specifications is fast), if the response time between intermediate gray scales is slow, then the images may appear smeared.

High luminance and wide color gamut – for clear, vivid color.

High luminance and wide color gamut are both essential elements to achieve high LCD image quality. Until recently, however, one was possible only at the expense of the other.


Generally, LCD color representation is achieved through a combination of color filters and light source. An expansion in the color reproduction range (color gamut) can be attained by using color filters with thicker colored films. However, luminance declines if the color filter is combined with the backlight system, since LCD panel transmissivity decreases.

NEC LCD Technologies offers users both high luminance and wide color gamut in every LCD we produce — and the improved color performance that goes with them. The key breakthrough came as a result of the improved transmissivity achieved by our SFT technology.

The results are impressive. The transmissivity of SA-SFT*1 is approximately 1.4-fold that of A-SFT*2, while the transmissivity of UA-SFT*3 is approximately 1.2-fold that of SA-SFT. Thus, a wide color gamut exceeding 70% the color gamut of NTSC is possible, without sacrificing luminance, for products intended for applications requiring accurate color reproduction. The clear, vivid color reproduction stands up to the toughest professional standards in applications including broadcasting, graphics and medical use.

Note: In monochrome products and other products intended for fields not requiring a wide color gamut, improvements in transmissivity based on SFT technology are being applied to achieve higher luminance.


*1 SA-SFT:Super-Advanced SFT *2 A-SFT:Advanced SFT *3 UA-SFT:Ultra-Advanced SFT



High luminance and high definition – to satisfy even the most demanding professionals.

As the demand for LCDs spreads to new and different applications, user needs grow more diversified and sophisticated. In healthcare, for instance, a new generation of doctors is turning to IT in their efforts to make more informed, accurate diagnoses. With this new trend, the role of digital displays has become more pivotal than ever in medical applications — with increasing demand for higher image reproduction.

To realize the high 3 megapixel-plus definition and smooth, precise gray scale characteristics demanded by applications for reading chest X-rays and mammograms, a luminant dynamic range and gamma characteristics independent of viewing angle are absolute prerequisites. NEC LCD Technologies addresses the exacting demands of these and other medical applications by offering ultra-high definition without sacrificing high luminance, thanks to the clear visibility of SFT technology.



Products featuring SFT technology

For monitor use

| | | |
|-----------|---------------------|--|
| 22.5-inch | NL192120AC25-02 | UA-SFT |
| 21.3-inch | NL204153AC21-09 | UA-SFT |
| | NL204153AM21-07A | UA-SFT |
| | NL204153BM21-01/01A | UA-SFT |
| | NL160120AC27-22B | UA-SFT NEW |
| | NL160120BC27-14 | UA-SFT |
| | NL160120BC27-10 | UA-SFT |
| | NL160120BM27-03/03A | UA-SFT |
| 20.1-inch | NL256204AM15-03A | UA-SFT NEW |
| 19.0-inch | NL128102BC29-10 | UA-SFT |
| | NL128102BM29-05A | UA-SFT |

For industrial use

| | | |
|-----------|--------------------|--|
| 15.3-inch | NL12876BC26-25/26B | |
| 15.0-inch | NL10276BC30-17 | UA-SFT |
| 12.1-inch | NL8060BC31-20 | |
| 10.4-inch | NL8060BC26-28 | |
| | NL6448BC33-74 | |
| 9.0-inch | NL8048BC24-04 | UA-SFT NEW |
| 8.4-inch | NL10276BC16-01 | UA-SFT |
| | NL6448BC26-08D | UA-SFT |

SFT is an abbreviation for Super Fine TFT.

Clear images in any ambient light environment due to two NEC technologies : SR-NLT and ST-NLT.


SR-NLT guarantees high-visibility in any ambient light environment.



Adapts to changes in ambient light for bright, vivid displays with low power consumption!

NEC LCD Technologies' SR-NLT*1 is based on transreflective (semi-transmissive) technology that has both the transmissive mode and reflective mode characteristics. At night, or in weak light, the display operates in transmissive mode with backlight as light source to guarantee excellent visibility. In daylight, or in bright light, the display uses reflective mode with ambient light and features excellent visibility. Low energy consumption is possible since visibility can be secured in high ambient light even with the backlight OFF. LCDs based on SR-NLT technology are appropriate for use in battery operated PDA, PND (small GPS terminal), handheld terminal applications, used either indoors or outdoors.

*1 SR-NLT:Super-Reflective NLT



Primary Feature Low energy consumption is possible since visibility can be secured in high ambient light even with the backlight OFF.




We raised the brightness in the transmissive mode and the reflection ratio in the reflective mode.

Transreflective LCDs are comprised of a backlit transmissive field and a reflective field that utilizes ambient light. The distribution of pixels in the two zones largely determines the basic performance in the transmissive mode and the reflective mode. A larger transmissive field, for example, boosts brightness but reduces the reflection ratio due to a smaller reflective field. A larger reflective field, on the other hand, enhances visibility in bright environments while lowering the transmissive ratio due to a smaller transmissive field.

The SR-NLT solves this dilemma through a proprietary optical design that boosts the transmissive ratio of the transmissive field and the efficiency of the backlight. An exclusive reflective plate also enables far more efficient use of ambient light. Thus, brightness in the transmissive mode and the reflection ratio in the reflective mode are significantly increased without affecting backlight power usage. The balance between brightness and reflection ratio can also be optimized to suit different purposes and environments.

Sample Applications




ST-NLT achieves clear and bright displays even in sun light.



Unaffected by changes in outdoor light environments to ensure natural color anytime!

ST-NLT*1 is another innovative technology incorporating NEC LCD Technologies' proprietary optical design. It boosts the efficiency of the backlight's light utilization and minimizes the surface reflection of ambient light. It is a transmissive LCD that produces high-contrast (photopic contrast) images even in bright outdoor light found on sunny afternoons. It features a wider color reproduction range than reflective LCDs, making it the ideal choice for bright, vibrant color displays. NEC LCD Technologies' extensive lineup of ST-NLT products ranges in size from 5.5-inch QVGA to 15.0-inch XGA. Thanks to a new advanced optical technology, our ST-NLT LCDs are ideal for ATMs, measuring devices, vending machines, and other industrial devices subject to use in bright sunlight.

*1 ST-NLT:Super-Transmissive NLT





Primary Feature Guarantees clear, vivid color images even in high ambient light by using a backlight as a light source to minimize the surface reflection of outdoor light.

Products featuring SR-NLT technology

For mobile use

| | | |
|----------|--------------------------------|--------------------------------|
| 3.5-inch | NL4864HL11-01B | NL4864HL11-02A |
| | NL2432HC22-41B | NL2432HC22-40A |
| 2.7-inch | NL2432HC17-04B | NL2432HC17-04A |




Backlight energy efficiency is raised and surface reflection is reduced at the same time.

Transmissive LCDs vary image visibility by controlling the amount of backlight illumination passing through the panel at a pixel level. In ordinary transmissive LCDs, this visibility deteriorates in bright environments, such as when outdoors in the daytime. This is largely due to insufficient LCD brightness, in comparison with the ambient brightness, as well as reflection of ambient light on the panel surface, which reduces photopic contrast.

Since transmissive LCD brightness is determined by backlight output and transmissive ratio, the lack of brightness in bright environments can be overcome by simply boosting backlight output. But this raises LCD power consumption.

The proprietary optical design of the ST-NLT enhances both the transmissive efficiency of the LCD and the energy efficiency of the backlight. This makes it possible to boost brightness, without raising backlight output, and reduce the reflection of ambient light. As a result, image visibility is improved in bright environments without increasing power consumption.

Sample Applications



Products featuring ST-NLT technology

For industrial use

| | | |
|-----------|---|--------------------------------|
| 15.0-inch | NL10276BC30-18C | |
| 12.1-inch | NL10276BC24-13C | NL8060BC31-41C |
| 10.4-inch | NL8060BC26-30C <small>NEW</small> | NL6448BC33-63C |
| | NL6448BC33-64C | |
| 8.4-inch | NL8060BC21-03 | NL6448BC26-09C |
| 6.5-inch | NL10276BC13-01C | NL6448BC20-21C |
| | NL6448BC20-20 | |
| 5.5-inch | NL3224BC35-22 | |

NLT is an abbreviation for Natural Light TFT.

Customer needs drive our efforts to further enhance LCD quality and usability.


Module technology that makes LCDs more complete.

Unlike the LCDs used in consumer-oriented products such as household televisions and computer monitors, the LCDs built into various industrial equipment must adapt to a rapidly expanding list of specifications.

Adaptive design technology, the 4th core technology of NEC LCD Technologies, fulfills the requests of customers from various industries in a detailed manner by fusing the cutting-edge technologies with technological know-how accumulated over many years.

In contrast to SFT, NLT and VIT technologies as panel technologies designed to improve LCD panel performance, adaptive design technology is module technology that increases the completeness of LCDs as a total package by integrating backlight systems, peripheral circuits and mechanism design.

Adaptive design technology is applied to every product in the NEC LCD Technologies lineup.




Optimal solutions that meet customer needs.

The specifications sought in various industrial equipment LCDs relate to more than display performance. Industrial LCDs must meet a wide variety of detailed requirements in terms of module size, temperature attributes, interface, power consumption and other factors in accordance with various conditions, such as application, usage environment and other circumstances unique to the piece of equipment.

Take industrial equipment designed and built for long-term production as an example. In applications like these, NEC LCD Technologies facilitates smooth, ongoing performance by maintaining product interface and mounting compatibility — for quick, easy replacement and upgrading of our latest high-quality, high-performance LCDs.

On the other hand, for applications where a more compact and energy-saving design is required, progress has been made in developments related to lightweight, energy-saving products with a narrow frame and slim body. Recently, we have also been promoting a lineup of wide-format products to meet needs for displaying more information in a limited amount of space, as well as for displaying digital moving images. We are also in the process of expanding the operating temperature range so that our equipment can be used in more diverse environments.

The product lineup of NEC LCD Technologies provides "optimal" solutions that meet diverse customer needs.



A proposal for an optimal backlight system.

The backlight system plays an extremely important role among the elements in adaptive design technology. It can affect the specifications for luminance, color reproduction, module size, weight, power consumption and temperature attributes.

Common edge-light backlight systems for displays larger than 5 inches use CCFL*1 as a light source, while those smaller than 5 inches use white LED*2 as a light source. Products that require extremely high luminance, such as for medical diagnosis by radiograph interpretation, use several aligned CCFLs beneath the LCD panel.

In recent years, there has been a rapid increase in white LED backlight systems even for modules larger than 5 inches, as their resistance to vibration and shock has improved through lightweight designs with slim bodies and low energy consumption. These offer many advantages, such as the control of high-frequency noise and harmonic currents, as well as the elimination of mercury.

NEC LCD Technologies has developed a wide range of backlight systems and is making efforts to further increase their efficiency.

*1 CCFL (Cold Cathode Fluorescent Lamp) : A thin fluorescent tube that generates light by discharging electrons without requiring heat.

*2 LED (Light-Emitting Diode) : A semiconductor device that generates light when voltage is applied.



Products equipped with a high-intensity, direct backlight system

- For monitor use
- 21.3-inch NL204153AC21-09
- NL204153AM21-07A
- NL160120AC27-22B NEW
- NL160120AM27-13A

Color and gray-scale reproduction approaching "the original".

We believe that high LCD image quality means precise on-screen image reproduction of the original subject or object. To achieve precise image reproduction, the LCD module as a total package with optimally combined LCD panel, backlight system and peripheral circuitry is important.


Two absolute essentials in reproducing richly colored natural images are wide color reproduction range and smooth gray scale reproduction. Both are NEC LCD Technologies specialties — precisely why our LCDs feature the same wide color reproduction range as sRGB*1. The key is finding the optimum combination of color filters and backlight systems based on the kind of high transmissivity only our SFT technology can offer. We also feature products that support Adobe® RGB's*2 wide color gamut through the use of RGB3 primary color LEDs in the backlights.

A multi-bit driver, customizable internal LUT*3 and other advanced components are the keys to high color separation and smooth gray scale reproduction using this wide color gamut. Such cutting-edge quality ensures optimum reproduction of any and all images down to the finest details — from the delicate nuances of natural tones to the subtle gradation changes of medical imaging data.

*1 sRGB: International standards on color space established by IEC (International Electrotechnical Commission).

*2 "Adobe" is a registered trademark or trademark of Adobe Systems Incorporated.

*3 LUT: Look Up Table



*4 NL160120BC27-10 (SA-SFT+LED B/L), Color gamut: 103% of NTCS ratio, Luminance: 250cd/m²

*5 NL160120BC27-14 (SA-SFT+CCFL B/L), Color gamut: 72% of NTCS ratio, Luminance: 250cd/m²

21.3-inch LCD module equipped with a RGB3 LED backlight system




NL160120BC27-10
103%

22.5-inch LCD module equipped with 10 bit driver



NL192120AC25-02
10 bit
97%

For industrial use

12.1-inch
Long-life white LED backlight modelNL8060BC31-47D
(12.1-inch SVGA)

This model incorporates a newly-designed LED unit that achieves both long operating life* and low power consumption in its backlight system. This is a next-generation standard model for industrial use.

* 25°C : 70,000H, 70°C : 60,000H

10.4-inch ST-NLT
Ambient light adaptive modelNL8060BC26-30C
(10.4-inch SVGA)

ST-NLT technology enables high visibility, high luminance and vivid colors in the bright sunlight.

10.4-inch
Long-life white LED backlight modelNL6448BC33-71D
(10.4-inch VGA)

This model incorporates a newly-designed LED unit that achieves both long operating life* and low power consumption in its backlight system. This is a next-generation standard model for industrial use.

* 25°C : 70,000H, 70°C : 60,000H

9.0-inch UA-SFT
Ultra-wide viewing angle modelNL8048BC24-04
(9.0-inch WVGA)

UA-SFT technology enables ultra-wide viewing angle and high contrast ratio. This model supports a wide 800 x 480 pixel format.



White LED Backlight System

White LED backlight systems have been gaining acceptance in industrial display applications.

Some of the key characteristics of LED backlights are:

- ◆ low power consumption, slim package and lightweight design compared to cold-cathode fluorescent lamp (CCFL) backlight systems.
- ◆ high resistance to shock and vibration compared to CCFL backlight systems.
- ◆ reduced concern about peripheral equipment malfunctions and the integrity of measurement results that can be affected by harmonic currents and high-frequency noise.
- ◆ greater control of the backlight in response to ambient light makes it easier to modulate light and dimming range as compared with CCFL backlight systems.
- ◆ the influence of low temperatures are minimized so that luminance and start up performance are better than with CCFL backlights.
- ◆ LED backlights are completely mercury-free and therefore less harmful to the environment than CCFLs.

By leveraging the above LED characteristics, NEC LCD Technologies has been able to expand its diverse product line-up with high-reliability LCDs that achieve **long operating life**, **low power consumption** and **slim designs**. These products are ideally suited for a variety of portable industrial equipment applications. Through on-going product development we will continue to expand our white LED backlight product line-up.


Lineup of white LED backlight models for industrial use.

| | 15.0" | 12.1" | 10.4" | 9.0"W | 8.4" | 7.0"W | 6.5" | 5.7" |
|------------|-------|-------|-------|-------|------|-------|------|------|
| XGA | ○ | ○ | ○ | | | | ● | |
| SVGA | | ● | ○ | | ○ | | | |
| VGA / WVGA | | | ● | ● | ● | ● | ● | ● |

● : New Product ● : Mass Production ○ : Under Planning

Products equipped with white LED backlight system for industrial use

| | | | | | |
|--------------------------|---------------|-----|--------------------------|---------------|---------|
| 12.1-inch NL8060BC31-47D | 16.77M colors | NEW | 6.5-inch NL10276BC13-01C | 16.77M colors | 72% |
| 10.4-inch NL6448BC33-71D | 16.77M colors | NEW | NL10276BC13-01 | 900cd/m² | 1100:1 |
| 9.0-inch NL8048BC24-06 | 16.77M colors | NEW | NL6448BC20-21C | (h)176° | (v)176° |
| 8.4-inch NL6448BC26-26 | 16.77M colors | NEW | NL6448BC20-21D | | |
| 7.0-inch NL8048BC19-08 | 16.77M colors | NEW | NL6448BC18-01F | 850cd/m² | 600:1 |

9.0-inch
Long-life white LED backlight modelNL8048BC24-06
(9.0-inch WVGA)

This model incorporates a newly-designed LED unit that achieves both long operating life* and low power consumption in its backlight system and supports a wide 800 x 480 pixel format.

* 25°C : 70,000H, 70°C : 60,000H

8.4-inch
Long-life white LED backlight modelNL6448BC26-26
(8.4-inch VGA)

This model incorporates a newly-designed LED unit that achieves both long operating life* and low power consumption in its backlight system. This is a next-generation standard model for industrial use.

* 25°C : 70,000H, 70°C : 60,000H

7.0-inch
Long-life white LED backlight modelNL8048BC19-08
(7.0-inch WVGA)

This model incorporates a newly-designed LED unit that achieves both long operating life* and low power consumption in its backlight system and supports a wide 800 x 480 pixel format.

* 25°C : 70,000H, 70°C : 60,000H

5.7-inch
White LED backlight and high luminance modelNL6448BC18-01F
(5.7-inch VGA)

This model achieves a slim body and low power consumption due to the white LED backlight system and also enables high visibility with its high luminance and high contrast ratio.

5.7-inch
White LED backlight modelNL6448BC18-01
(5.7-inch VGA)

This model has a slim body and low power consumption due to the white LED backlight system.



For monitor use

21.3-inch UA-SFT
2M-pixel high luminance color modelNL160120AC27-22B
(21.3-inch UXGA)

Although this is a color model, it achieves ultra-high luminance and high contrast ratio of 1100:1 that can support medical diagnosis by radiograph interpretation, using UA-SFT technology with a high-intensity backlight system.

20.1-inch SA-SFT
5M-pixel monochrome modelNL256204AM15-03A
(20.1-inch QSXGA)

This model can support medical diagnosis of digital mammographic images due to its wide viewing angle with SA-SFT technology and 5 mega pixel of ultra-high density display.



*For product availability, please contact our sales offices or our agents.
◆ST-NLT : Super-Transmissive NLT, UA-SFT : Ultra-Advanced SFT, SA-SFT : Super-Advanced SFT

We provide the optimum solutions that meet diverse customer requirements.

Industrial Applications



High-End Professional Applications



Mobile Applications



Product Map

※All of LCD modules for mobile use are equipped with a timing controller and a DC/DC converter.

| | | | | | | |
|-------------------------|-------------------------------------|--|---|--|---|---|
| | |  |  |  |  |  |
| | | 4.3 inch Wide | 4.1 inch Wide | 3.5 inch | 2.7 inch Wide | 2.7 inch |
| | Viewing Direction | Landscape | Landscape | Portrait | Landscape | Portrait |
| QHD 960×540 | Transmissive Without touch panel | | | NL9654HL06-01J   70% 300cd/m ² | | |
| WVGA 800×480 | Transmissive With touch panel | | NL8048HL11-01B   70% 350cd/m ² | | | |
| VGA 480×640 | NLT With touch panel | | NL4864HL11-01B   200cd/m ² (transmissive mode) | | | |
| | Without touch panel | | NL4864HL11-02A   220cd/m ² (transmissive mode) | | | |
| WQVGA 480×272 | Transmissive With touch panel | NL4827HC19-05B  500cd/m ² | | | | |
| | Without touch panel | NL4827HC19-05A  600cd/m ² | | | | |
| NLT | With touch panel | | NL2432HC22-41B  200cd/m ² (transmissive mode) | NL2432HC17-04B  120cd/m ² (transmissive mode) | | |
| | Without touch panel | | NL2432HC22-40A  220cd/m ² (transmissive mode) | NL2432HC17-04A  140cd/m ² (transmissive mode) | | |
| QVGA 240×320 | With touch panel | | | NL2432HC17-07B 500cd/m ² | | |
| | Transmissive | | | NL2432HC17-07A 550cd/m ² | | |
| | Without touch panel | | | | | |

Product Specifications

...Wide color gamut
...Touch panel
...Wide

| Screen Size | 4.3 inch Wide (11cm diagonal) | 4.1 inch Wide (10.4cm diagonal) | 3.5 inch (8.9cm diagonal) | | | | |
|--------------------------------------|---|---|---|---|---|--|--|
| Viewing Direction | Landscape | Landscape | Portrait | | | | |
| Part Number | NL4827HC19-05B | NL4827HC19-05A | NL8048HL11-01B | NL4864HL11-01B | NL4864HL11-02A | NL2432HC22-41B | NL2432HC22-40A |
| Resolution | 480 × 272 | 480 × 272 | 800 × 480 | 480 × 640 | 480 × 640 | 240 × 320 | 240 × 320 |
| Display Area (mm) | 95.04 × 53.856 | 95.04 × 53.856 | 88.80 × 53.28 | 53.28 × 71.04 | 53.28 × 71.04 | 53.64 × 71.52 | 53.64 × 71.52 |
| Display Color | 16.77M colors | 16.77M colors | 16.77M colors | 262K colors | 262K colors | 262K colors | 262K colors |
| Pixel Pitch (mm) | 0.198 × 0.198 | 0.198 × 0.198 | 0.111 × 0.111 | 0.111 × 0.111 | 0.111 × 0.111 | 0.2235 × 0.2235 | 0.2235 × 0.2235 |
| Reflectivity | — | — | — | 7%(including touch panel) Type III | 7% Type III | 15%(including touch panel) Type IV | 15% Type IV |
| Luminance | 500cd/m ² ※at IL=20mA | 600cd/m ² ※at IL=20mA | 350cd/m ² ※at IL=14mA | 200cd/m ² ※at IL=20mA*2 | 220cd/m ² ※at IL=20mA*2 | 200cd/m ² ※at IL=20mA*2 | 220cd/m ² ※at IL=20mA*2 |
| Contrast Ratio | 500 : 1 | 500 : 1 | 400 : 1 | 180 : 1*2 | 180 : 1*2 | 150 : 1*2 | 150 : 1*2 |
| Viewing Angle (Up,Down,Left,Right) | 60°, 80°, 80°, 80° Contrast Ratio ≥ 10:1 | 60°, 80°, 80°, 80° Contrast Ratio ≥ 10:1 | 60°, 80°, 80°, 80° Contrast Ratio ≥ 10:1 | 30°, 35°, 30°, 30°*2 Contrast Ratio ≥ 5:1 | 30°, 35°, 30°, 30°*2 Contrast Ratio ≥ 5:1 | 30°, 35°, 30°, 30°*2 Contrast Ratio ≥ 5:1 | 35°, 35°, 35°, 35°*2 Contrast Ratio ≥ 5:1 |
| Response Time*1 | 33ms | 33ms | 25ms | 30ms | 30ms | 30ms | 30ms |
| Interface | CMOS(RGB 8 bits each) | CMOS(RGB 8 bits each) | CMOS(RGB 8 bits each) | CMOS(RGB 6 bits each) | CMOS(RGB 6 bits each) | CMOS(RGB 6 bits each) | CMOS(RGB 6 bits each) |
| Power Supply Voltage | VCC : 3.0V VDD : 5.0V | VCC : 3.0V VDD : 5.0V | VCC : 3.0V | VCC : 3.0V | VCC : 3.0V | VCC : 3.0V | VCC : 3.0V |
| Power Cons. LCD Panel+Driver | 87mW | 87mW | 165mW | 120mW | 120mW | 50mW | 50mW |
| | 512mW ※at IL=20mA | 512mW ※at IL=20mA | 604mW ※at IL=14mA | 512mW ※at IL=20mA | 512mW ※at IL=20mA | 384mW ※at IL=20mA | 384mW ※at IL=20mA |
| Operating Temperature | -20°C ~ +70°C | -20°C ~ +70°C | -20°C ~ +70°C | -20°C ~ +70°C | -20°C ~ +70°C | -20°C ~ +70°C | -20°C ~ +70°C |
| Storage Temperature | -30°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | -20°C ~ +70°C |
| Surface Condition | Antiglare | Clear | Clear | Clear | Clear | Clear | Clear |
| Module Size W × H × D mm (D : max*3) | 105.5 × 67.2 × 5.1 | 105.5 × 67.2 × 4.1 | 99.6 × 69.5 × 5.2 | 63.5 × 85.0 × 4.4 | 63.5 × 85.0 × (3.2) | 63.5 × 85.0 × 4.4 | 63.5 × 85.0 × 3.2 |
| Weight | 72g | 58g | 70g | 43g (25g) | 43g (25g) | 43g | 25g |
| Reverse Scan | — | — | ○*4 | ○*4 | ○*4 | — | — |
| Touch Panel | Equipment | None | Equipment | Equipment | None | Equipment | None |
| Controller | Installed | Installed | Installed | Installed | Installed | Installed | Installed |
| Remarks |   70% |  |   VIT SR-NLT |   VIT SR-NLT |   VIT SR-NLT |   SR-NLT |   SR-NLT |

| Screen Size | 2.7 inch Wide (6.8cm diagonal) | 2.7 inch (6.8cm diagonal) | | | | |
|--------------------------------------|---|--|--|--|--|--|
| Viewing Direction | Landscape | Portrait | | | | |
| Part Number | NL9654HL06-01J | NL2432HC17-04B | NL2432HC17-04A | NL2432HC17-07B | NL2432HC17-07A | |
| Resolution | 960 × 540 | 240 × 320 | 240 × 320 | 240 × 320 | 240 × 320 | |
| Display Area (mm) | 59.04 × 33.21 | 41.04 × 54.72 | 41.04 × 54.72 | 41.04 × 54.72 | 41.04 × 54.72 | |
| Display Color | 16.77M colors | 262K colors | 262K colors | 262K colors | 262K colors | |
| Pixel Pitch (mm) | 0.0615 × 0.0615 | 0.171 × 0.171 | 0.171 × 0.171 | 0.171 × 0.171 | 0.171 × 0.171 | |
| Reflectivity | — | 35%(including touch panel) Type II | 35% Type II | — | — | |
| Luminance | 300cd/m ² ※at IL=14mA | 120cd/m ² ※at IL=20mA*2 | 140cd/m ² ※at IL=20mA*2 | 500cd/m ² ※at IL=18mA | 550cd/m ² ※at IL=18mA | |
| Contrast Ratio | 400 : 1 | 150 : 1*2 | 150 : 1*2 | 400 : 1 | 400 : 1 | |
| Viewing Angle (Up,Down,Left,Right) | 60°, 60°, 80°, 80° Contrast Ratio ≥ 10:1 | 35°, 30°, 30°, 30°*2 Contrast Ratio ≥ 5:1 | 35°, 30°, 30°, 30°*2 Contrast Ratio ≥ 5:1 | 60°, 30°, 50°, 50° Contrast Ratio ≥ 5:1 | 60°, 30°, 50°, 50° Contrast Ratio ≥ 5:1 | |
| Response Time*1 | 25ms | 30ms | 30ms | 23ms | 23ms | |
| Interface | CMOS(RGB 8 bits each) | CMOS(RGB 6 bits each) | CMOS(RGB 6 bits each) | CMOS(RGB 6 bits each) | CMOS(RGB 6 bits each) | |
| Power Supply Voltage | VCC : (2.7V) VDD : (6.5V) | VCC : 3.0V | VCC : 3.0V | VCC : 3.0V | VCC : 3.0V | |
| Power Cons. LCD Panel+Driver | 235mW | 45mW | 45mW | 36mW | 36mW | |
| | 518mW ※at IL=20mA | 256mW ※at IL=20mA | 256mW ※at IL=20mA | 288mW ※at IL=18mA | 288mW ※at IL=18mA | |
| Operating Temperature | -20°C ~ +70°C | -20°C ~ +70°C | -20°C ~ +70°C | -20°C ~ +70°C | -20°C ~ +70°C | |
| Storage Temperature | -30°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | |
| Surface Condition | Clear | Clear | Clear | Clear | Clear | |
| Module Size W × H × D mm (D : max*3) | 69.0 × 50.8 × 3.6 | 50.54 × 68.62 × 4.32 | 50.54 × 68.62 × 3.2 | 50.54 × 68.62 × 3.75 | 50.54 × 68.62 × 2.8 | |
| Weight | 26g | 28g | | | | |

Product Map

* Mounting compatibility: Outer dimensions (except thickness), position of mounting holes and relative to screen center.
* Interface compatibility: Interface connector pin assignment.



15.3 inch Wide 15.0 inch 12.1 inch 10.4 inch 9.0 inch Wide 8.4 inch 7.0 inch Wide 6.5 inch 5.7 inch 5.5 inch

| WXGA 1280×768 | | | SFT | NL12876BC26-25/25B SA-SFT 470cd/m ² 100~70°C | WXGA Interface Compatibility (LVDS)*1 | | | | | | | | | | | |
|------------------|------|-------------------------|-------------------------|--|---|---|---|--|--|--|---|---|---|--|--|--|
| XGA 1024×768 | LVDS | SFT | | | | | | | | | | | | | | |
| | | SFT | | | XGA Interface Compatibility (LVDS)*1 NL10276BC30-17 UA-SFT 350cd/m ² 72% | XGA Interface Compatibility (LVDS)*2 NL10276BC30-18C ST-NLT 600cd/m ² 100~70°C | NL10276BC24-13C ST-NLT 400cd/m ² 100~70°C | NL10276BC24-13 400cd/m ² 100~70°C | NL10276BC20-04 300cd/m ² 100~70°C | NL10276BC16-01 UA-SFT 400cd/m ² 72% | | | NL10276BC13-01C ST-NLT 650cd/m ² LED 100~70°C | NL10276BC13-01 500cd/m ² LED 100~70°C | | |
| | | NLT | Wide viewing angle type | | NL10276BC30-18 500cd/m ² 100~70°C | NL10276BC30-33D 400cd/m ² 100~70°C | NL10276BC30-32D 250cd/m ² 100~70°C | | | | | | | | | |
| SVGA 800×600 | LVDS | SFT | | | SVGA Interface Compatibility (LVDS)*2 NL8060BC31-41C ST-NLT 550cd/m ² 100~70°C | NL8060BC26-28 SA-SFT 400cd/m ² 100~70°C | NL8060BC31-41C ST-NLT 550cd/m ² 100~70°C | NL8060BC31-47D (400cd/m ²) LED 100~70°C | NL8060BC26-30D 400cd/m ² 100~70°C | NL8060BC21-03 ST-NLT 650cd/m ² 100~70°C | NL8060BC21-06 650cd/m ² 100~70°C | NL8060BC21-02 400cd/m ² 100~70°C | | | | |
| | | NLT | Wide viewing angle type | | NL8060BC31-41D 400cd/m ² 100~70°C | | | | | | | | | | | |
| | CMOS | SFT | Wide viewing angle type | | SVGA Interface Compatibility (CMOS) NL8060BC31-20 A-SFT 250cd/m ² | NL8060BC26-27 SA-SFT 400cd/m ² 100~70°C | NL8060BC31-20 A-SFT 250cd/m ² | NL8060BC31-36 ³ 1100cd/m ² 100~70°C | NL8060BC26-30D 400cd/m ² 100~70°C | NL8060BC21-04 400cd/m ² 100~70°C | NL8048BC24-04 UA-SFT 350cd/m ² 100~70°C | NL8048BC24-06 (400cd/m ²) LED 100~70°C | NL8048BC19-08 400cd/m ² LED 100~70°C | | | |
| WVGA 800×480 | LVDS | SFT | Wide viewing angle type | | WVGA Interface Compatibility (LVDS)*2 NL8048BC24-01 400cd/m ² 100~70°C | NL8048BC24-04 UA-SFT 350cd/m ² 100~70°C | NL8048BC24-06 (400cd/m ²) LED 100~70°C | NL8048BC24-01 400cd/m ² 100~70°C | NL8048BC24-04 400cd/m ² 100~70°C | NL8048BC19-08 400cd/m ² LED 100~70°C | | | | | | |
| | LVDS | SFT | | | VGA Interface Compatibility (LVDS)*2 NL6448BC33-63C ST-NLT 450cd/m ² 100~70°C | NL6448BC26-08D UA-SFT 400cd/m ² 72% 100~70°C | NL6448BC33-63C ST-NLT 450cd/m ² 100~70°C | NL6448BC33-71D (450cd/m ²) LED 100~70°C | NL6448BC26-15 450cd/m ² 100~70°C | NL6448BC20-21C ST-NLT 800cd/m ² LED 100~70°C | NL6448BC20-21D 550cd/m ² LED 100~70°C | | | | | |
| | | NLT | Wide viewing angle type | | NL6448BC33-63D 450cd/m ² 100~70°C | | | | | | | | | | | |
| VGA 640×480 | CMOS | SFT | | | VGA Interface Compatibility (CMOS) NL6448BC33-74 SA-SFT 450cd/m ² 100~70°C | NL6448BC26-09C ST-NLT 750cd/m ² 100~70°C | NL6448BC33-74 SA-SFT 450cd/m ² 100~70°C | NL6448BC33-64C ST-NLT 450cd/m ² 100~70°C | NL6448BC26-09/09D 450cd/m ² 100~70°C | NL6448BC20-20 ST-NLT 650cd/m ² 100~70°C | NL6448BC20-18D 400cd/m ² 100~70°C | NL6448BC18-01F 800cd/m ² LED 100~70°C | NL6448BC18-01 400cd/m ² LED 100~70°C | VGA Interface Compatibility (CMOS) NL6448BC33-54 220cd/m ² 100~70°C | | |
| | | NLT | Wide viewing angle type | | NL6448BC33-64 450cd/m ² 100~70°C | | | | | | | | | | | |
| | CMOS | Standard type | | | NL6448BC33-54 220cd/m ² 100~70°C | | | | | | | | | | | |
| WQVGA 480×234 | CMOS | Wide viewing angle type | | | WQVGA (CMOS) | | | | | NL4823BC37-05 400cd/m ² 100~70°C | | | | | | |
| QVGA 320×240 | CMOS | NLT | Wide viewing angle type | | | | | | | | | | | QVGA Interface Compatibility (CMOS) NL3224BC35-22 ST-NLT 750cd/m ² 100~70°C | | |
| | | | | | | | | | | | | | | NL3224BC35-20 400cd/m ² 100~70°C | | |


*Please see the Data Sheet for detailed specifications. All values are typical values (excluding the width for module size). Values in brackets are tentative.

◆ A-SFT : Advanced SFT, SA-SFT : Super-Advanced SFT, UA-SFT : Ultra-Advanced SFT, ST-NLT : Super-Transmissive NLT

*1 The interface of 15.0-inch or larger LVDS models and 12.1-inch or smaller LVDS models are incompatible. *2 Connector types and connector pin alignments are compatible. Control signal is upwardly compatible.

*3 The position of the mounting holes with respect to the position of the display screen are interchangeable with other 12.1-inch models.

Product Specifications



| Screen Size | 15.3 inch Wide (39cm diagonal) | 15.0 inch (38cm diagonal) | | | | | | 12.1 inch (31cm diagonal) | | | | | | | |
|--|--------------------------------|------------------------------|------------------------------|------------------------------|-----------------------------|--------------------------------------|--------------------------------------|--------------------------------------|--------------------------------------|--------------------------------------|------------------------|------------------------|--------------------------------|--|--|
| Part Number | NL12876BC26-25/25B | NL10276BC30-17 | NL10276BC30-18C | NL10276BC30-18 | NL10276BC30-33D | NL10276BC30-32D | NL10276BC24-13C | NL10276BC24-13 | NL8060BC31-41C | NL8060BC31-47D | NL8060BC31-41D | NL8060BC31-20 | NL8060BC31-42/42D | | |
| Resolution | 1280 × 768 | 1024 × 768 | 1024 × 768 | 1024 × 768 | 1024 × 768 | 1024 × 768 | 1024 × 768 | 1024 × 768 | 800 × 600 | 800 × 600 | 800 × 600 | 800 × 600 | 800 × 600 | | |
| Display Area (mm) | 334.08 × 200.45 | 304.128 × 228.096 | 304.128 × 228.096 | 304.128 × 228.096 | 304.128 × 228.096 | 245.76 × 184.32 | 245.76 × 184.32 | 246.0 × 184.5 | 246.0 × 184.5 | 246.0 × 184.5 | 246.0 × 184.5 | 246.0 × 184.5 | 246.0 × 184.5 | | |
| Display Color | 16.77M colors | 16.77M colors | 16.77M colors | 16.77M colors | 16.77M colors | 16.77M colors / 262K colors | 16.77M colors / 262K colors | 16.77M colors / 262K colors | 16.77M colors / 262K colors | 16.77M colors / 262K colors | 262K colors | 262K colors | 262K colors | | |
| Pixel Pitch (mm) | 0.261 × 0.261 | 0.297 × 0.297 | 0.297 × 0.297 | 0.297 × 0.297 | 0.297 × 0.297 | 0.24 × 0.24 | 0.24 × 0.24 | 0.3075 × 0.3075 | 0.3075 × 0.3075 | 0.3075 × 0.3075 | 0.3075 × 0.3075 | 0.3075 × 0.3075 | 0.3075 × 0.3075 | | |
| Luminance | 470cd/m ² | 350cd/m ² | 600cd/m ² | 500cd/m ² | 400cd/m ² | 250cd/m ² | 400cd/m ² | 550cd/m ² | (400cd/m ²) | 400cd/m ² | 250cd/m ² | 400cd/m ² | 250cd/m ² | | |
| Contrast Ratio | 700 : 1 | 700 : 1 | 600 : 1 | 500 : 1 | 500 : 1 | 600 : 1 | 600 : 1 | 600 : 1 | 600 : 1 | 600 : 1 | 400 : 1 | 600 : 1 | 600 : 1 | | |
| Viewing Angle (Up,Down,Left,Right) Contrast Ratio ≥10:1 | 88°, 88°, 88°, 88° | 88°, 88°, 88°, 88° | 80°, 60°, 80°, 80° | 80°, 60°, 80°, 80° | 80°, 80°, 80°, 80° | 80°, 80°, 80°, 80° | 45°, 55°, 70°, 70° | 45°, 55°, 70°, 70° | 80°, 60°, 80°, 80° | 80°, 60°, 80°, 80° | 80°, 60°, 80°, 80° | 88°, 88°, 88°, 88° | 80°, 60°, 80°, 80° | | |
| Response Time* ¹ | 25ms | 25ms | 18ms | 18ms | 18ms | 18ms | 33ms | 33ms | 25ms | 25ms | 25ms | 80ms | 25ms | | |
| Interface | LVDS (RGB 8 bits each) | LVDS (RGB 8 bits each) | LVDS (RGB 8 bits each) | LVDS (RGB 8 bits each) | LVDS (RGB 8 bits each) | LVDS (RGB 8 bits each / 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | CMOS (RGB 6 bits each) | CMOS (RGB 6 bits each) | | | |
| Power Supply Voltage | 3.3V | 3.3V | 3.3V | 3.3V | 3.3V | 3.3V | 3.3V | 3.3V | 3.3V | 3.3V | 3.3V | 3.3V | 3.3V / 5.0V | | |
| Power Consumption | 18.0W* ² | 16.6W* ² | 15.7W* ² | 15.7W* ² | 10.0W* ² | 10.0W* ² | 7.0W* ² | 7.0W* ² | 6.8W* ² | (5.3W) | 6.8W* ² | 7.0W* ² | 6.9W* ² | | |
| Operating Temperature | -10°C ~ +70°C | 0°C ~ +55°C | -10°C ~ +70°C | -10°C ~ +70°C | -20°C ~ +70°C | -20°C ~ +70°C | -10°C ~ +70°C | -10°C ~ +70°C | -20°C ~ +70°C | -20°C ~ +70°C | -20°C ~ +70°C | 0°C ~ +55°C | -20°C ~ +70°C | | |
| Storage Temperature | -20°C ~ +80°C | -20°C ~ +60°C | -20°C ~ +80°C | -20°C ~ +80°C | -20°C ~ +80°C | -20°C ~ +80°C | -20°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | -20°C ~ +60°C | -30°C ~ +80°C | | |
| Polarizer Surface | -25 : Antiglare / -25B : Clear | Antiglare | Clear + Antireflection | Antiglare | Antiglare | Antiglare | Clear + Antireflection | Clear | Clear + Antireflection | Antiglare | Antiglare | Clear | -42 : Clear / -42D : Antiglare | | |
| Module Size W × H × D mm (D : max) | 358.0 × 226.0 × 16.8 | 326.5 × 253.5 × 17.0 | 326.5 × 253.5 × 17.0 | 326.5 × 253.5 × 17.0 | 326.5 × 253.5 × 12.0 | 326.5 × 253.5 × 12.0 | 280.0 × 210.0 × 13.7 | 280.0 × 210.0 × 13.7 | 280.0 × 210.0 × 11.5 | 280.0 × 210.0 × 11.5 | 280.0 × 210.0 × 13.7 | 280.0 × 210.0 × 11.5 | 280.0 × 210.0 × 13.7 | | |
| Weight | 1270g | 1300g | 1300g | 1300g | 970g | 970g | 755g | 750g | 670g | (670g) | 670g | 760g | 670g | | |
| Reverse Scan | — | — | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | | |
| Backlight | Top and bottom, 2 CCFLs each | Top and bottom, 2 CCFLs each | Top and bottom, 2 CCFLs each | Top and bottom, 2 CCFLs each | Top and bottom, 1 CCFL each | Top and bottom, 1 CCFL each | One side, 2 CCFLs | One side, 2 CCFLs | One side, 2 CCFLs | White LED | One side, 2 CCFLs | One side, 2 CCFLs | One side, 2 CCFLs | | |
| Recommended Inverter | — | 150PW231 | 150PW231 | 150PW231 | 150PW331 | 150PW331 | 121PW181 | 121PW181 | 121PW181 | — | 121PW181 | 121PW181 | 121PW181 | | |
| Remarks | | | | — | — | — | | — | | | — | | — | | |

| Screen Size | 12.1 inch (31cm diagonal) | 10.4 inch (26cm diagonal) | | | | | | | | | | | |
|--|---------------------------|---------------------------|--------------------------------------|--------------------------------------|--------------------------------------|------------------------|--------------------------------------|--------------------------------------|------------------------|------------------------|------------------------|----------------------|---------------|
| Part Number | NL8060BC31-36 | NL10276BC20-04 | NL8060BC26-28 | NL8060BC26-30C | NL8060BC26-30D | NL8060BC26-27 | NL6448BC33-63C | NL6448BC33-71D | NL6448BC33-63D | NL6448BC33-74 | NL6448BC33-64C | NL6448BC33-64 | NL6448BC33-54 |
| Resolution | 800 × 600 | 1024 × 768 | 800 × 600 | 800 × 600 | 800 × 600 | 640 × 480 | 640 × 480 | 640 × 480 | 640 × 480 | 640 × 480 | 640 × 480 | 640 × 480 | |
| Display Area (mm) | 246.0 × 184.5 | 210.4 × 157.8 | 211.2 × 158.4 | 211.2 × 158.4 | 211.2 × 158.4 | 211.2 × 158.4 | 211.2 × 158.4 | 211.2 × 158.4 | 211.2 × 158.4 | 211.2 × 158.4 | 211.2 × 158.4 | 211.2 × 158.4 | |
| Display Color | 262K colors | 262K colors | 16.77M colors / 262K colors | 16.77M colors / 262K colors | 16.77M colors / 262K colors | 262K colors | 16.77M colors / 262K colors | 16.77M colors / 262K colors | 262K colors | 262K colors | 262K colors | 262K colors | |
| Pixel Pitch (mm) | 0.3075 × 0.3075 | 0.2055 × 0.2055 | 0.264 × 0.264 | 0.264 × 0.264 | 0.264 × 0.264 | 0.264 × 0.264 | 0.33 × 0.33 | 0.33 × 0.33 | 0.33 × 0.33 | 0.33 × 0.33 | 0.33 × 0.33 | 0.33 × 0.33 | |
| Luminance | 1100cd/m ² | 300cd/m ² | 400cd/m ² | 550cd/m ² | 400cd/m ² | 400cd/m ² | 450cd/m ² | (450cd/m ²) | 450cd/m ² | 450cd/m ² | 450cd/m ² | 450cd/m ² | |
| Contrast Ratio | 600 : 1 | 300 : 1 | 700 : 1 | 900 : 1 | 1000 : 1 | 700 : 1 | 600 : 1 | 600 : 1 | 600 : 1 | 800 : 1 | 600 : 1 | 350 : 1 | |
| Viewing Angle (Up,Down,Left,Right) Contrast Ratio ≥10:1 | 45°, 55°, 70°, 70° | 45°, 60°, 60°, 60° | 88°, 88°, 88°, 88° | 80°, 80°, 80°, 80° | 80°, 80°, 80°, 80° | 88°, 88°, 88°, 88° | 80°, 60°, 80°, 80° | 80°, 60°, 80°, 80° | 80°, 60°, 80°, 80° | 88°, 88°, 88°, 88° | 80°, 60°, 80°, 80° | 30°, 20°, 45°, 45° | |
| Response Time* ¹ | 33ms | 55ms | 50ms | 18ms | 18ms | 50ms | 25ms | 25ms | 30ms | 25ms | 25ms | 38ms | |
| Interface | CMOS (RGB 6 bits each) | LVDS (RGB 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | CMOS (RGB 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | CMOS (RGB 6 bits each) | CMOS (RGB 6 bits each) | CMOS (RGB 6 bits each) | | |
| Power Supply Voltage | 3.3V / 5.0V | 3.3V | 3.3V | 3.3V | 3.3V | 3.3V / 5.0V | 3.3V | 3.3V | 3.3V / 5.0V | 3.3V / 5.0V | 3.3V / 5.0V | 3.3V / 5.0V | |
| Power Consumption | 13.7W* ² | 6.2W* ² | 6.5W* ² | 6.6W* ² | 6.6W* ² | 6.6W* ² | 6.2W* ² | (4.6W) | 6.2W* ² | 6.6W* ² | 6.2W* ² | 5.8W* ² | |
| Operating Temperature | -10°C ~ +70°C | 0°C ~ +60°C | -10°C ~ +70°C | -20°C ~ +70°C | -20°C ~ +70°C | -10°C ~ +70°C | -20°C ~ +70°C | -20°C ~ +70°C | -20°C ~ +70°C | -20°C ~ +70°C | -20°C ~ +70°C | -10°C ~ +70°C | |
| Storage Temperature | -20°C ~ +80°C | -20°C ~ +70°C | -20°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | -20°C ~ +80°C | -30°C ~ +80°C | -30°C ~ | | | | | |

Product Specifications



| Screen Size | 9.0 inch Wide (23cm diagonal) | | | | 8.4 inch (21cm diagonal) | | | | | | | | |
|---------------------------------------|---|---|---|--|--|---|---|---|---|---|---|---|---|
| Part Number | NL8048BC24-04  | NL8048BC24-06  | NL8048BC24-01 | NL10276BC16-01 | NL8060BC21-03 | NL8060BC21-06 | NL8060BC21-02 | NL8060BC21-04 | NL6448BC26-08D | NL6448BC26-15 | NL6448BC26-09C | NL6448BC26-26  | NL6448BC26-09/09D |
| Resolution | 800 × 480 | 800 × 480 | 800 × 480 | 1024 × 768 | 800 × 600 | 800 × 600 | 800 × 600 | 800 × 600 | 640 × 480 | 640 × 480 | 640 × 480 | 640 × 480 | 640 × 480 |
| Display Area (mm) | 196.8 × 118.08 | 196.8 × 118.08 | 196.8 × 118.08 | 170.496 × 127.872 | 170.4 × 127.8 | 170.4 × 127.8 | 170.4 × 127.8 | 170.4 × 127.8 | 170.88 × 128.16 | 170.88 × 128.16 | 170.88 × 128.16 | 170.88 × 128.16 | 170.88 × 128.16 |
| Display Color | 16.77M colors / 262K colors | 16.77M colors / 262K colors | 16.77M colors / 262K colors | 16.77M colors / 262K colors | 16.77M colors / 262K colors | 16.77M colors / 262K colors | 16.77M colors / 262K colors | 262K colors | 16.77M colors / 262K colors | 16.77M colors / 262K colors | 262K colors | 262K colors | 262K colors |
| Pixel Pitch (mm) | 0.246 × 0.246 | 0.246 × 0.246 | 0.246 × 0.246 | 0.1665 × 0.1665 | 0.213 × 0.213 | 0.213 × 0.213 | 0.213 × 0.213 | 0.213 × 0.213 | 0.267 × 0.267 | 0.267 × 0.267 | 0.267 × 0.267 | 0.267 × 0.267 | 0.267 × 0.267 |
| Luminance | 350cd/m ² | (400cd/m ²) | 400cd/m ² | 400cd/m ² | 650cd/m ² | 650cd/m ² | 400cd/m ² | 400cd/m ² | 400cd/m ² | 450cd/m ² | 750cd/m ² | (450cd/m ²) | 450cd/m ² |
| Contrast Ratio | 800 : 1 | 600 : 1 | 600 : 1 | 400 : 1 | 600 : 1 | 600 : 1 | 600 : 1 | 600 : 1 | 800 : 1 | 600 : 1 | 600 : 1 | 600 : 1 | 600 : 1 |
| Viewing Angle (Up,Down,Left,Right) | 88°, 88°, 88°, 88° | 80°, 60°, 80°, 80° | 80°, 60°, 80°, 80° | 88°, 88°, 88°, 88° | 80°, 60°, 80°, 80° | 80°, 60°, 80°, 80° | 80°, 60°, 80°, 80° | 80°, 60°, 80°, 80° | 88°, 88°, 88°, 88° | 80°, 60°, 80°, 80° | 80°, 60°, 80°, 80° | 80°, 60°, 80°, 80° | 80°, 60°, 80°, 80° |
| Contrast Ratio ≥10:1 | | | | | | | | | | | | | |
| Response Time* ¹ | 25ms | 25ms | 25ms | 25ms | 25ms | 25ms | 25ms | 25ms | 20ms | 25ms | 25ms | 25ms | 25ms |
| Interface | LVDS (RGB 8 bits each / 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | CMOS (RGB 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | CMOS (RGB 6 bits each) | CMOS (RGB 6 bits each) | CMOS (RGB 6 bits each) |
| Power Supply Voltage | 3.3V | 3.3V | 3.3V | 3.3V | 3.3V | 3.3V | 3.3V | 3.3V / 5.0V | 3.3V | 3.3V | 3.3V / 5.0V | 3.3V / 5.0V | 3.3V / 5.0V |
| Power Consumption | 5.8W* ² | (4.6W) | 5.8W* ² | 9.8W* ² | 5.5W* ² | 5.5W* ² | 5.5W* ² | 5.5W* ² | 5.4W* ² | 5.3W* ² | 5.3W* ² | (3.5W) | 5.3W* ² |
| Operating Temperature | −20°C ~ +70°C  | −20°C ~ +70°C  | −20°C ~ +70°C  | 0°C ~ +55°C | −20°C ~ +70°C  | −20°C ~ +70°C  | −20°C ~ +70°C  | −20°C ~ +70°C  | −10°C ~ +70°C  | −20°C ~ +70°C  | −20°C ~ +70°C  | −20°C ~ +70°C  | −20°C ~ +70°C  |
| Storage Temperature | −30°C ~ +80°C | −30°C ~ +80°C | −30°C ~ +80°C | −20°C ~ +60°C | −30°C ~ +80°C | −30°C ~ +80°C | −30°C ~ +80°C | −30°C ~ +80°C | −20°C ~ +80°C | −30°C ~ +80°C | −30°C ~ +80°C | −30°C ~ +80°C | −30°C ~ +80°C |
| Polarizer Surface | Clear | Clear | Clear | Antiglare | Clear + Antireflection | Clear | Clear | Clear | Antiglare | Clear | Clear + Antireflection | Clear | −09 : Clear / −09D : Antiglare |
| Module Size W × H × D mm (D : max) | 220.5 × 136.5 × 11.0 | 220.5 × 136.5 × 11.0 | 220.5 × 136.5 × 11.0 | 200.0 × 152.0 × 17.0 | 200.0 × 152.0 × 11.0 | 200.0 × 152.0 × 11.0 | 200.0 × 152.0 × 11.0 | 200.0 × 152.0 × 11.0 | 200.0 × 152.0 × 11.0 | 200.0 × 152.0 × 11.0 | 200.0 × 152.0 × 11.0 | 200.0 × 152.0 × 11.0 | 200.0 × 152.0 × 11.0 |
| Weight | 365g | (365g) | 365g | 465g | 330g | 330g | 330g | 330g | 330g | 330g | 330g | (330g) | 330g |
| Reverse Scan | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ |
| Backlight | One side, 2 CCFLs | White LED | One side, 2 CCFLs | Top and bottom, 2 CCFLs each | One side, 2 CCFLs | One side, 2 CCFLs | One side, 2 CCFLs | One side, 2 CCFLs | One side, 2 CCFLs | One side, 2 CCFLs | One side, 2 CCFLs | White LED | One side, 2 CCFLs |
| Recommended Inverter | 104PW201 | — | 104PW201 | 84PW021 | 84PW031 / 84PW041 | 84PW031 / 84PW041 | 84PW031 / 84PW041 | 84PW031 / 84PW041 | 84PW031 / 84PW041 | 84PW031 / 84PW041 | 84PW031 / 84PW041 | 84PW031 / 84PW041 | 84PW031 / 84PW041 |
| Remarks | UA-SFT  | LED  | WIDE | UA-SFT  | ST-NLT  | — | — | — | UA-SFT  | — | ST-NLT  | — | LED  |

| Screen Size | 7.0 inch Wide (18cm diagonal) | | 6.5 inch (17cm diagonal) | | | | | | 5.7 inch (15cm diagonal) | | 5.5 inch (14cm diagonal) | | |
|---|---|---|---|--|---|---|---|---|--|---|---|---|---|
| Part Number | NL8048BC19-08  | NL4823BC37-05 | NL10276BC13-01C | NL10276BC13-01 | NL6448BC20-21C | NL6448BC20-21D | NL6448BC20-20 | NL6448BC20-18D | NL6448BC18-01F  | NL6448BC18-01  | NL3224BC35-22 | NL3224BC35-20 | |
| Resolution | 800 × 480 | 480 × 234 | 1024 × 768 | 1024 × 768 | 640 × 480 | 640 × 480 | 640 × 480 | 640 × 480 | 640 × 480 | 640 × 480 | 320 × 240 | 320 × 240 | |
| Display Area (mm) | 152.4 × 91.44 | 154.08 × 87.048 | 132.096 × 99.072 | 132.096 × 99.072 | 132.48 × 99.36 | 132.48 × 99.36 | 132.48 × 99.36 | 132.48 × 99.36 | 116.16 × 87.12 | 116.16 × 87.12 | 111.36 × 83.52 | 111.36 × 83.52 | |
| Display Color | 16.77M colors / 262K colors | 262K colors | 16.77M colors / 262K colors | 16.77M colors / 262K colors | 16.77M colors / 262K colors | 16.77M colors / 262K colors | 262K colors | 262K colors | 262K colors | 262K colors | 262K colors | 262K colors | |
| Pixel Pitch (mm) | 0.1905 × 0.1905 | 0.321 × 0.372 | 0.129 × 0.129 | 0.129 × 0.129 | 0.207 × 0.207 | 0.207 × 0.207 | 0.207 × 0.207 | 0.207 × 0.207 | 0.1815 × 0.1815 | 0.1815 × 0.1815 | 0.348 × 0.348 | 0.348 × 0.348 | |
| Luminance | 400cd/m ² | 400cd/m ² | 650cd/m ² | 500cd/m ² | 800cd/m ² | 550cd/m ² | 650cd/m ² | 400cd/m ² | 800cd/m ² | 400cd/m ² | 750cd/m ² | 400cd/m ² | |
| Contrast Ratio | 1000 : 1 | 600 : 1 | 500 : 1 | 500 : 1 | 600 : 1 | 600 : 1 | 600 : 1 | 600 : 1 | 1000 : 1 | 1000 : 1 | 500 : 1 | 400 : 1 | |
| Viewing Angle (Up,Down,Left,Right) Contrast Ratio ≥ 10:1 | 80°, 80°, 80°, 80° | 60°, 80°, 80°, 80° | 80°, 60°, 80°, 80° | 80°, 60°, 80°, 80° | 80°, 60°, 80°, 80° | 80°, 60°, 80°, 80° | 80°, 60°, 80°, 80° | 80°, 60°, 80°, 80° | 80°, 80°, 80°, 80° | 80°, 80°, 80°, 80° | 50°, 40°, 55°, 55° | 50°, 40°, 55°, 55° | |
| Response Time* ¹ | 18ms | 25ms | 25ms | 25ms | 25ms | 25ms | 25ms | 25ms | 18ms | 18ms | 30ms | 30ms | |
| Interface | LVDS (RGB 8 bits each / 6 bits each) | CMOS (RGB 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | LVDS (RGB 8 bits each / 6 bits each) | CMOS (RGB 6 bits each) | CMOS (RGB 6 bits each) | CMOS (RGB 6 bits each) | CMOS (RGB 6 bits each) | CMOS (RGB 6 bits each) | CMOS (RGB 6 bits each) | |
| Power Supply Voltage | 3.3V | 3.3V | 3.3V | 3.3V | 3.3V | 3.3V | 3.3V / 5.0V | 3.3V / 5.0V | 3.3V | 3.3V | 3.3V / 5.0V | 3.3V / 5.0V | |
| Power Consumption | (3.8W) | 2.7W* ² | 3.9W | 3.9W | 2.4W | 2.4W | 4.4W* ² | 4.4W* ² | 3.3W | 1.8W | 3.8W* ² | 3.8W* ² | |
| Operating Temperature | -20°C ~ +70°C  | -20°C ~ +70°C  | -20°C ~ +70°C  | -20°C ~ +70°C  | -20°C ~ +70°C  | -20°C ~ +70°C  | -10°C ~ +70°C  | -10°C ~ +70°C  | -20°C ~ +70°C  | -20°C ~ +70°C  | -10°C ~ +70°C  | -10°C ~ +70°C  | |
| Storage Temperature | -30°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | -20°C ~ +80°C | -20°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | -30°C ~ +80°C | |
| Polarizer Surface | Clear | Clear | Clear + Antireflection | Clear | Clear + Antireflection | Antiglare | Clear + Antireflection | Antiglare | Clear | Clear | Clear + Antireflection | Antiglare | |
| Module Size W X H X D mm (D : max) | 170.0 × 111.0 × 9.0 | 174.5 × 105.5 × 11.0 | 153.0 × 118.0 × 9.5 | 153.0 × 118.0 × 9.5 | 153.0 × 118.0 × 9.5 | 153.0 × 118.0 × 9.5 | 153.0 × 118.0 × 11.0 | 153.0 × 118.0 × 11.0 | 135.0 × 104.6 × 11.0 | 135.0 × 104.6 × 11.0 | 134.0 × 104.5 × 13.0 | 134.0 × 104.5 × 13.0 | |
| Weight | 170g | 205g | 170g | 170g | 170g | 165g | 205g | 205g | 165g | 160g | 215g | 210g | |
| Reverse Scan | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○* ³ | ○* ³ | ○* ³ | ○* ³ | |
| Backlight | White LED | One side, 1 CCFL | White LED | White LED | White LED | White LED | One side, 2 CCFLs | One side, 2 CCFLs | White LED | White LED | Top and bottom, 1 CCFL each | Top and bottom, 1 CCFL each | |
| Recommended Inverter | — | 70PW021 | — | — | — | — | 65PW061 | 65PW061 | — | — | 55PW131 | 55PW131 | |
| Remarks |   |  |   |   |   |   |   |   | — |  |  |   | — |

*Please see the Data Sheet for detailed specifications. All values are typical values (excluding the width for module size). Values in brackets are tentative. *1 Values equal $T_{on} + T_{off}$ (10% → 90%). *2 Values do not include inverter power dissipation. *3 Both horizontal and vertical scan direction can be selected independently. ♦UA-SFT: Ultra-Advanced SFT, ST-NLT: Super-Transmissive NLT

Product Map

※ Mounting compatibility: Outer dimensions (except thickness), position of mounting holes and relative to screen center.
※ Interface compatibility: Interface connector pin assignment.



22.5 inch Wide 21.3 inch 20.1 inch 19.0 inch

| | | | | |
|-----------------------------------|---------------------|--|---|---|
| QSXGA 2560×2048 (5M pixels) | Monochrome model | | NL256204AM15-03A   850cd/m², 600:1, 30ms | |
| | | | | |
| QXGA 2048×1536 (3M pixels) | Color model | | NL204153AC21-09   800cd/m², 750:1, 24ms | |
| | | | NL204153BC21-02   235cd/m², 450:1, 23ms | |
| QXGA 2048×1536 (3M pixels) | Monochrome model | | NL204153AM21-07A   1450cd/m², 900:1, 27ms | |
| | | | NL204153BM21-01/01A   800cd/m², 700:1, 35ms | |
| WUXGA 1920×1200 | Color model | | NL192120AC25-02   (420cd/m²), (800:1), (12ms) | |
| | | | | |
| UXGA 1600×1200 (2M pixels) | Color model | | NEW NL160120AC27-22B   (900cd/m²), (1100:1), (35ms) | |
| | | | NL160120BC27-14   250cd/m², 550:1, 20ms | NL160120BC27-10   250cd/m², 430:1, 20ms |
| UXGA 1600×1200 (2M pixels) | Monochrome model | | NL160120AM27-13A   1650cd/m², 850:1, 23ms | |
| | | | NL160120BM27-03/03A   1000cd/m², 700:1, 35ms | |
| SXGA 1280×1024 (1M pixels) | Color model | | NL128102BC29-10   (300cd/m²), (800:1), 20ms | |
| | | | | |
| SXGA 1280×1024 (1M pixels) | Monochrome model | | NL128102BM29-05A   1000cd/m², 900:1, 35ms | |
| | | | | |

Mounting Compatibility

Won the 12th Advanced Display of the Year 2007 (ADY) award in the Display Module category.

Mounting Compatibility

Product Specifications

Wide color gamut  NTSC ratio  Monochrome model  High intensity backlight  Refresh rate 

| Screen Size | 22.5 inch Wide (57cm diagonal) | 21.3 inch (54cm diagonal) | | | | | |
|--|---|--|--|---|--|--|--|
| Part Number | NL192120AC25-02 | NL204153AC21-09 | NL204153BC21-02 | NL204153AM21-07A | NL204153BM21-01/01A | NL160120AC27-22B  | NL160120BC27-14 |
| Resolution | 1920 × 1200 | 2048 × 1536 | 2048 × 1536 | 2048 × 1536 | 2048 × 1536 | 1600 × 1200 | 1600 × 1200 |
| Display Area (mm) | 483.84 × 302.4 | 433.152 × 324.864 | 433.152 × 324.864 | 433.152 × 324.864 | 433.152 × 324.864 | 432.0 × 324.0 | 432.0 × 324.0 |
| Display Color | 1073M colors | 16.77M colors | 16.77M colors | 256 gray scales / 1sub-pixel 766 gray scales / 1pixel | 256 gray scales / 1sub-pixel 766 gray scales / 1pixel | 16.77M colors | 16.77M colors |
| Pixel Pitch (mm) | 0.252 × 0.252 | 0.2115 × 0.2115 | 0.2115 × 0.2115 | 0.2115 × 0.2115 | 0.2115 × 0.2115 | 0.27 × 0.27 | 0.27 × 0.27 |
| Luminance | (420cd/m²) | 800cd/m² | 235cd/m² | 1450cd/m² | 800cd/m² | (900cd/m²) | 250cd/m² |
| Contrast Ratio | (800 : 1) | 750 : 1 | 450 : 1 | 900 : 1 | 700 : 1 | (1100 : 1) | 550 : 1 |
| Viewing Angle (Up,Down,Left,Right) Contrast Ratio ≥10:1 | 88°, 88°, 88°, 88° | 88°, 88°, 88°, 88° | 88°, 88°, 88°, 88° | 88°, 88°, 88°, 88° | 88°, 88°, 88°, 88° | 88°, 88°, 88°, 88° | 88°, 88°, 88°, 88° |
| Response Time* ¹ | (12ms) | 24ms | 23ms | 27ms | 35ms | (35ms) | 20ms |
| Interface | 4 port LVDS (RGB 10 bits each) | 4port LVDS (RGB 8 bits each) | 4port LVDS (RGB 8 bits each) | 4port LVDS (LCR 8 bits each) | 4port LVDS (LCR 8 bits each) | 2port LVDS (RGB 8 bits each) | 2port LVDS (RGB 8 bits each) |
| Power Supply Voltage | 12.0V (Inverter : 12.0V) | 12.0V (Inverter : 24.0V) | 12.0V | 12.0V (Inverter : 12.0V) | 12.0V | (12.0V) (Inverter : (24.0V)) | 12.0V |
| Power Consumption | (67.0W) | 73.2W | 32.5W* ² | 68.4W | 34.2W* ² | (72.0W) | 30.7W* ² |
| Operating Temperature | 0°C ~ +50°C | 0°C ~ +55°C | 0°C ~ +55°C | 0°C ~ +55°C | 0°C ~ +55°C | 0°C ~ +55°C | 0°C ~ +55°C |
| Storage Temperature | -20°C ~ +60°C | -20°C ~ +60°C | -20°C ~ +60°C | -20°C ~ +60°C | -20°C ~ +60°C | -20°C ~ +60°C | -20°C ~ +60°C |
| Polarizer Surface | Antiglare | Antiglare | Antiglare | Antiglare | Antiglare | Antiglare | Antiglare |
| Module Size W × H × D mm (D: max) | 542.0 × 362.0 × 55.5 | 457.0 × 350.0 × 37.0 | 457.0 × 350.0 × 25.5 | 457.0 × 350.0 × 37.0 | 457.0 × 350.0 × 25.5 | 457.0 × 350.0 × 37.0 | 457.0 × 350.0 × 25.5 |
| Weight | 3450g | 2700g | 3800g | 3000g | 3800g | 2600g | 3750g |
| Backlight | 12 CCFLs | 16 CCFLs | Top and bottom, 3 CCFLs each | 16 CCFLs | Top and bottom, 3 CCFLs each | 16 CCFLs | Top and bottom, 3 CCFLs each |
| Inverter | Built in | Built in | Not provided | Built in | Not provided | Built in | Not provided |
| Remarks |   97% |   72% |   72% |   Clear base |   {01: Blue base 01A: Clear base |   72% |   72% |

| Screen Size | 21.3 inch (54cm diagonal) | 20.1 inch (51cm diagonal) | 19.0 inch (48cm diagonal) |
|--|---|--|---------------------------------|
| Part Number | NL160120BC27-10 | NL160120AM27-13A | NL160120BM27-03/03A |
| Resolution | 1600 × 1200 | 1600 × 1200 | 1600 × 1200 |
| Display Area (mm) | 432.0 × 324.0 | 432.0 × 324.0 | 399.36 × 319.488 |
| Display Color | 16.77M colors | 256 gray scales/1sub-pixel 766 gray scales/1pixel | 16.77M colors |
| Pixel Pitch (mm) | 0.27 × 0.27 | 0.27 × 0.27 | 0.156 × 0.156 |
| Luminance | 250cd/m² | 1650cd/m² | 850cd/m² (300cd/m²) |
| Contrast Ratio | 430 : 1 | 850 : 1 | 600 : 1 (800 : 1) |
| Viewing Angle (Up,Down,Left,Right) Contrast Ratio ≥10:1 | 88°, 88°, 88°, 88° | 88°, 88°, 88°, 88° | 88°, 88°, 88°, 88° |
| Response Time* ¹ | 20ms | 23ms | 30ms |
| Interface | 2port LVDS (RGB 8 bits each) | 2port LVDS (LCR 8 bits each) | 4port LVDS (LCR 8 bits each) |
| Power Supply Voltage | 12.0V | 12.0V (Inverter : 12.0V) | 12.0V (Inverter : 12.0V) |
| Power Consumption | 72.0W (At 6,500K) | 63.7W | 49.2W (25.9W* ²) |
| Operating Temperature | 0°C ~ +55°C | 0°C ~ +55°C | 0°C ~ +55°C |
| Storage Temperature | -20°C ~ +60°C | -20°C ~ +60°C | -20°C ~ +60°C |
| Polarizer Surface | Antiglare | Antiglare | Antiglare |
| Module Size W × H × D mm (D: max) | 457.0 × 355.0 × 47.4 ³ | 457.0 × 350.0 × 37.0 | 457.0 × 350.0 × 25.5 |
| Weight | TBD | 2900g | 2440g (2700g) |
| Backlight | RGB (3 primary colors) LED array | 16 CCFLs | 12 CCFLs |
| Inverter | Unnecessary | Built in | Built in |
| Remarks |  <img alt="LED logo" data-bbox="325 845 | | |