


PRODUCT NO.

94898

PRODUCT NO.	STAND OFF	SOLDER TAIL	DIM "P" (mm)	DIM "Q" (mm)	FOR LOWER DECK OR UPPER DECK	③ HOLD DOWN	SHEET NO.	MOUNTING STYLE TO PCB
94898-XXXX	DIM "M" (mm)							
000	0	R/A	2.8	—	LOWER	NONE	NO.2	TOP MOUNT 94898-0XXX
000LF	0	R/A	2.8	—	LOWER	NONE		
000MLF	0	R/A	2.8	—	LOWER	NONE		
000H	0	R/A	2.8	—	LOWER	YES		
000HLF	0	R/A	2.8	—	LOWER	YES		
001	0	SMT STAGGERED	—	—	LOWER	NONE		
001LF	0	SMT STAGGERED	—	—	LOWER	NONE		
001H	0	SMT STAGGERED	—	—	LOWER	YES		
001HLF	0	SMT STAGGERED	—	—	LOWER	YES		
002	0	SMT IN LINE	—	—	LOWER	NONE		
002LF	0	SMT IN LINE	—	—	LOWER	NONE	NO.3	BLACK COLOR 
002H	0	SMT IN LINE	—	—	LOWER	YES		
002HLF	0	SMT IN LINE	—	—	LOWER	YES		
010	4	R/A	2.8	—	LOWER	NONE		
010LF	4	R/A	2.8	—	LOWER	NONE		
020	5	R/A	2.8	—	LOWER	NONE		
020LF	5	R/A	2.8	—	LOWER	NONE		
020MLF	5	R/A	2.8	—	LOWER	NONE		
021MLF	5	R/A	2.8	—	LOWER	NONE		
040	2	R/A	2.5	—	LOWER	NONE	NO.4	
040MLF	2	R/A	2.5	—	LOWER	NONE		
040LF	2	R/A	2.5	—	LOWER	NONE		
005	FDR 0	R/A	2.8	8.6	UPPER	NONE		
005LF	FDR 0	R/A	2.8	8.6	UPPER	NONE		
045	FDR 2	R/A	2.5	10.3	UPPER	NONE		
045MLF	FDR 2	R/A	2.5	10.3	UPPER	NONE		
045LF	FDR 2	R/A	2.5	10.3	UPPER	NONE		
500	0	R/A	2.8	—	LOWER	NONE	NO.5	BOTTOM MOUNT 94898-5XXX
500LF	0	R/A	2.8	—	LOWER	NONE		
500H	0	R/A	2.8	—	LOWER	YES		
500HLF	0	R/A	2.8	—	LOWER	YES		
501	0	SMT STAGGERED	—	—	LOWER	NONE		
501LF	0	SMT STAGGERED	—	—	LOWER	NONE		
501H	0	SMT STAGGERED	—	—	LOWER	YES		
501HLF	0	SMT STAGGERED	—	—	LOWER	YES		
502	0	SMT IN LINE	—	—	LOWER	NONE		
502J	0	SMT IN LINE	—	—	LOWER	NONE	NO.6	NATURAL (WHITE) COLOR 
502LF	0	SMT IN LINE	—	—	LOWER	NONE		
502H	0	SMT IN LINE	—	—	LOWER	YES		
502HLF	0	SMT IN LINE	—	—	LOWER	YES		
510	4	R/A	2.8	—	LOWER	NONE		
510LF	4	R/A	2.8	—	LOWER	NONE		
520	5	R/A	2.8	—	LOWER	NONE		
520LF	5	R/A	2.8	—	LOWER	NONE		
530	2	R/A	1.48	—	LOWER	NONE	NO.7	
530LF	2	R/A	1.48	—	LOWER	NONE		
540	2	R/A	2.5	—	LOWER	NONE		
540LF	2	R/A	2.5	—	LOWER	NONE		
505	FDR 0	R/A	2.8	8.6	UPPER	NONE		
505LF	FDR 0	R/A	2.8	8.6	UPPER	NONE		
535	FDR 2	R/A	1.48	9.28	UPPER	NONE		
535LF	FDR 2	R/A	1.48	9.28	UPPER	NONE		
545	FDR 2	R/A	2.5	10.3	UPPER	NONE		
545LF	FDR 2	R/A	2.5	10.3	UPPER	NONE		

NOTES

1. PRODUCT SPEC:110-263

94898-X X X X X

OPTIONAL LEED FREE

NONE : N □

LF : YES

OPTIONAL HOLD DOWN

NONE : N □

H : YES (SEE FIGURE OF -xxxH)

LOW COST VERSION

NONE : N □

M : YES (DETAIL AS COMPONENT)

SOLDER TAIL

0 : R/A (FOR LOWER & SINGLE)

1 : SMT STAGGERED (FOR LOWER ONLY)

2 : SMT IN LINE (FOR LOWER ONLY)

5 : R/A (FOR UPPER ONLY)

STAND OFF

0 : 0mm

1 : 4mm

2 : 5mm



3 : 2mm (SPECIAL TAIL LENGTH)

4 : 2mm

MOUNTING STYLE

0 : TOP MOUNTING

5 : BOTTOM MOUNTING



SECTION "W"—"W"

94898-xxxH
(OPTIONAL HOLD DOWN)

mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		PCMCIA
l	tr	ec	n	dr	date	tolerances unless other	wise specified
J	N06-0065	M.Z			04/02/06	angles	
K	N07-0219	M.Z			12/07/07	linear	
L	N08-0041	M.Z			03/10/08	±2°	
M	N08-0219	M.Z			10/10/08	dr	
N	N09-0045	SH			05/25/09	engn	
P	ELX-N-007954	ZK			11/01/11	chr	
R	ELX-N-011436	ZK			04/23/12	appd	
sheet	revision	R	R	R	R	R	R
index	sheet	1	2	3	4	5	6



dwg no 94898 sheet 1 of 7 size A4

type CUSTOMER Drawing

PRODUCT NO.

94898-000

94898-000LF

94898-000H

94898-000HLF

94898-000MLF

94898-001

94898-001LF

94898-001H



94898-001HLF

94898-002

94898-002LF

94898-002H

94898-002HLF






NOTES

- TRUE POSITION IS A FREE GRID TO PIN PATTERN ITSELF.
- SEE TA-946 FOR PCB LAYOUT.
- MATERIAL
HOUSING : HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
PIN : COPPER ALLOY.
HOLD-DOWN : BRASS
- FINISH
PIN
UNDER PLATING : 0.5µm MIN. Ni.
CONTACT AREA : 0.076 µm MIN. GOLD

SOLDER AREA : 2.5µm MIN. Sn-Pb.
OR 2.5µm MIN. PURE Sn.(FOR -XXXLF)
HOLD-DOWN : 2.5µm MIN. PURE Sn.
- RECOMMENDED PCB HOLE (OPTIONAL HOLD-DOWN) : 2.3±0.1
- SEQUENCE PIN ASSIGNMENT

	DIM "I"		
	4.25±0.1	3.5±0.1	5.0±0.1
PIN No.	OTHERS	36.67	1.77, 34, 35, 51, 68

- GENERAL TOLERANCE : ±0.3
- SEE SHEET 1 REGARDING COMPONENTS.
- IF LEAD FREE P/N, THE HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
- LEAD FREE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCRIBLED IN GS-22-008
- IF LEAD FREE P/N, PACKAGE MEETS GS-14-920 SPECIFICATION



mat'l. code		surface		tolerance		projection		product family	
ISO 1302		ISO 406		ISO 1101		ISO 1101		PCMCIA	
ltr ecn nodr date		tolerances unless otherwise specified		title		title		title	
R		angles		linear		MM		68 POS EJECTOR HEADER ASSY FOR LOW VOLTAGE	
		±2°		0.X±0.3		scale 1:1		dwg no	
		dr M.Hasegawa 2/24/05		0.XX±0.13				94898	
		engr M.Hasegawa 2/24/05		0.XXX±0.05				sheet 2 of 7	
		chr						A4	
		appd						type CUSTOMER	
sheet index		revision sheet						Drawing	

PRODUCT NO.

94898-010

94898-010LF

94898-020/020M




94898-020LF/020MLF

94898-021MLF

94898-040

94898-040LF/040MLF

STAND OFF HEIGHT




SECTION "Z"- "Z" (5/1)


- ① TRUE POSITION IS A FREE GRID TO PIN PATTERN ITSELF.
2. SEE TA-946 FOR PCB LAYOUT.
③ MATERIAL
HOUSING : HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
PIN : COPPER ALLOY.
HOLD-DOWN : BRASS
④ FINISH
PIN
UNDER PLATING : 0.5μm MIN. Ni.
CONTACT AREA : 0.076 μm MIN. GOLD
SOLDER AREA : 2.5μm MIN. Sn-Pb.
OR 2.5μm MIN. PURE Sn.(FOR -XXXLF)
HOLD-DOWN : 2.5μm MIN. PURE Sn.
5. RECOMMENDED PCB HOLE (OPTIONAL HOLD-DOWN) : 2.3±0.1
6. SEQUENCE PIN ASSIGNMENT

PIN No.	DIM "L"		
	4.25±0.1	3.5±0.1	5.0±0.1
OTHERS	36.67	1.17.34	35.51.68

7. GENERAL TOLERANCE : ±0.3
8. SEE SHEET 1 REGARDING COMPONENTS.
9. IF LEAD FREE P/N, THE HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
10. LEAD FREE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCRIBLED IN GS-22-008
11. IF LEAD FREE P/N, PACKAGE MEETS GS-14-920 SPECIFICATION
12. "M" SHOWS IT IS LOW COST VERSION, IT IS OPTIONAL AND IN FIRST OF LETTER OF PART NO., SUCH AS 94898-020MLF IS LOW COST VERSION 94898-020LF IS NOT LOW COST VERSION.





DETAIL "Y" (5/1)

DETAIL "X" (20/1)
TYP(68)

mat'l. code		surface	tolerance	projection	product family
ISD 1302		ISD 406	ISD 1101		PCMCIA
l'tecn naddr date		tolerances unless otherwise specified			title
R		angles	linear	MM	68 POS EJECTOR HEADER ASSY FOR LOW VOLTAGE
		±2°	0.X±0.3		
			0.XX±0.13		
			0.XXX±0.05	scale 1:1	
		dr M.Hasegawa 2/24/05			dwg no 94898 sheet 3 of 7 size A4
		engr M.Hasegawa 2/24/05			
		chr			
		appd			
sheet index	revision sheet				type CUSTOMER Drawing

PRODUCT NO.
94898-005
94898-005LF
94898-045
94898-045LF




NOTES

- TRUE POSITION IS A FREE GRID TO PIN PATTERN ITSELF.
- SEE TA-946 FOR PCB LAYOUT.
- MATERIAL
HOUSING : HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
PIN : COPPER ALLOY.
HOLD-DOWN : BRASS
- FINISH
PIN
UNDER PLATING : 0.5μm MIN. NI.
CONTACT AREA : 0.076 μm MIN. GOLD



SOLDER AREA : 2.5μm MIN. Sn-Pb.
OR 2.5μm MIN. PURE Sn.(FOR -XXXLF)
HOLD-DOWN : 2.5μm MIN. PURE Sn.
- RECOMMENDED PCB HOLE (OPTIONAL HOLD-DOWN) : 2.3±0.1
- SEQUENCE PIN ASSIGNMENT

	DIM "L"		
	4.25±0.1	3.5±0.1	5.0±0.1
PIN No.	OTHERS	36.67	1.17.34 35.51.68

- GENERAL TOLERANCE : ±0.3
- SEE SHEET 1 REGARDING COMPONENTS.
- IF LEAD FREE P/N, THE HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
- LEAD FREE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCRIBLED IN GS-22-008
- IF LEAD FREE P/N, PACKAGE MEETS GS-14-920 SPECIFICATION



SECTION "Z-Z" (5/1)



DETAIL "X" (20/1)
TYP(68)

DETAIL "Y" (5/1)

mat'l. code		surface	tolerance	projection	product family
		ISO 1302	ISO 406 ISO 1101		PCMCIA
l	tr	ec	n	o	d
r					
date		tolerances unless otherwise specified		title	
R		angles	linear	MM	68 POS EJECTOR HEADER ASSY FOR LOW VOLTAGE
		±2°	0.X±0.3 0.XX±0.13 0.XXX±0.05	scale 1:1	
		dr	M.Hasegawa	2/24/05	
		eng	M.Hasegawa	2/24/05	
		chr			
		app			
sheet	revision				
index	sheet				

PRODUCT NO.
94898-500
94898-500LF
94898-500H
94898-500HLF
94898-501
94898-501LF
94898-501H
94898-501HLF
94898-502
94898-502J
94898-502LF
94898-502H
94898-502HLF

-SEE NOTE 12



NOTES


1. TRUE POSITION IS A FREE GRID TO PIN PATTERN ITSELF.
2. SEE TA-946 FOR PCB LAYOUT.
3. MATERIAL
HOUSING : HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
PIN : COPPER ALLOY.
HOLD-DOWN : BRASS
4. FINISH
PIN
UNDER PLATING : 0.5μm MIN. Ni.
CONTACT AREA : 0.076 μm MIN. GOLD
SOLDER AREA : 2.5μm MIN. Sn-Pb.
OR 2.5μm MIN. PURE Sn.(FOR -XXXLF)
HOLD-DOWN : 2.5μm MIN. PURE Sn.

5. RECOMMENDED PCB HOLE (OPTIONAL HOLD-DOWN) : 2.3±0.1


6. SEQUENCE PIN ASSIGNMENT

PIN No.	OTHERS	DIM "L"	
		4.25±0.1	5.0±0.1
		36.67	117.94
			35.51±0.08


7. GENERAL TOLERANCE : ±0.3
8. SEE SHEET 1 REGARDING COMPONENTS.
9. IF LEAD FREE P/N, THE HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
10. LEAD FREE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCRIBED IN GS-22-008
11. IF LEAD FREE P/N, PACKAGE MEETS GS-14-920 SPECIFICATION
12. THE P/N 94898-502J HAS SPECIAL TRAY, IT IS 10084720-001.



R/A (94898-500X)





SMT STAGGERED (94898-501X)



SMT IN LINE (94898-502X)

mat'l. code		surface		tolerance		projection		product family	
ISO 1302		ISO 406		ISO 1101		ISO 1101		PCMCIA	
ltr ecn nldr date		tolerances unless otherwise specified		title		title		title	
R		angles		linear		MM		68 POS EJECTOR HEADER ASSY FOR LOW VOLTAGE	
		±2°		0.X±0.3		scale 1:1		dwg no	
		dr M.Hasegawa 2/24/05		0.XX±0.13				94898	
		engr M.Hasegawa 2/24/05		0.XXX±0.05				sheet 5 of 7	
		chr						A4	
		appd						type CUSTOMER	
sheet index		revision sheet						Drawing	

PRODUCT NO.	
94898-510	94898-510LF
94898-520	94898-520LF
94898-530	94898-530LF
94898-540	94898-540LF







NOTES

- TRUE POSITION IS A FREE GRID TO PIN PATTERN ITSELF.
- SEE TA-946 FOR PCB LAYOUT.
- MATERIAL
HOUSING : HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
PIN : COPPER ALLOY.
HOLD-DOWN : BRASS
- FINISH
PIN
UNDER PLATING : 0.5µm MIN. Ni.
CONTACT AREA : 0.076 µm MIN. GOLD

SOLDER AREA : 2.5µm MIN. Sn-Pb.
OR 2.5µm MIN. PURE Sn.(FOR -XXLF)
HOLD-DOWN : 2.5µm MIN. PURE Sn.
- RECOMMENDED PCB HOLE (OPTIONAL HOLD-DOWN) : 2.3±0.1
- SEQUENCE PIN ASSIGNMENT



PIN No.	DIM "L"	
	4.25±0.1	3.5±0.1
OTHERS	36.67	5.0±0.1

- GENERAL TOLERANCE : ±0.3
- SEE SHEET 1 REGARDING COMPONENTS.
- IF LEAD FREE P/N, THE HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
- LEAD FREE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCRIBLED IN GS-22-008
- IF LEAD FREE P/N, PACKAGE MEETS GS-14-920 SPECIFICATION



mat'l. code		surface	tolerance	projection	product family
ISO 1302		ISO 406	ISO 1101		PCMCIA
l	tr	ec	n	o	d
date		tolerances unless otherwise specified			title
R		angles	linear	MM	68 POS EJECTOR HEADER ASSY FOR LOW VOLTAGE
		±2°	0.X±0.3	scale 1:1	
			0.XX±0.13		
			0.XXX±0.05		
		dr	M.Hasegawa	2/24/05	dwg no
		engr	M.Hasegawa	2/24/05	94898
		chr			sheet 6 of 7
		appd			size A4
sheet	revision	type CUSTOMER Drawing			
index	sheet				

PRODUCT NO.
94898-505
94898-505LF
94898-535
94898-535LF
94898-545
94898-545LF






NOTES

- TRUE POSITION IS A FREE GRID TO PIN PATTERN ITSELF.
- SEE TA-946 FOR PCB LAYOUT.
- MATERIAL
 - HOUSING : HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK
 - PIN : COPPER ALLOY.
 - HOLD-DOWN : BRASS
- FINISH
 - PIN
 - UNDER PLATING : 0.5μm MIN. Ni.
 - CONTACT AREA : 0.076 μm MIN. GOLD
 - SOLDER AREA : 2.5μm MIN. Sn-Pb.
OR 2.5μm MIN. PURE Sn.(FOR -XXXLF)
 - HOLD-DOWN : 2.5μm MIN. PURE Sn.
- RECOMMENDED PCB HOLE (OPTIONAL HOLD-DOWN) : 2.3±0.1
- SEQUENCE PIN ASSIGNMENT

	DIM "L"		
PIN No.	4.25±0.1	3.5±0.1	5.0±0.1
OTHERS	36.67	117.34	35.51±0.08

- GENERAL TOLERANCE : ±0.3
- SEE SHEET 1 REGARDING COMPONENTS.
- IF LEAD FREE P/N, THE HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
- LEAD FREE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCIBLED IN GS-22-008
- IF LEAD FREE P/N, PACKAGE MEETS GS-14-920 SPECIFICATION



mat'l. code	surface	tolerance	projection	product family
	ISO 1302	ISO 406 ISO 1101		PCMCIA
ltr ecn nodr date	tolerances unless otherwise specified			title
R	angles	linear	MM	68 POS EJECTOR HEADER ASSY FOR LOW VOLTAGE
	±2°	0.X±0.3 0.XX±0.13 0.XXX±0.05	scale 1:1	
	dr	M.Hasegawa 2/24/05	FCI	dwg no
	engr	M.Hasegawa 2/24/05		94898
	chr			sheet 7 of 7
	appd			A4
sheet index	revision sheet			type CUSTOMER Drawing