

# PRODUCT SPECIFICATION

**Carl  
Kammerling**  
International

|                         |                  |
|-------------------------|------------------|
| <b>Brand</b>            | C.K              |
| <b>Product Range</b>    | Multistep Drills |
| <b>Catalogue number</b> | 3008, 3009, 3010 |
| <b>Date</b>             | 03/11/2008       |

|                                                                                                                                                                                                                                                                                                                                                  |                                                                                                                    |                                                                                      |                |            |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|----------------|------------|
| <b>Range Description</b><br>Multistep Drills                                                                                                                                                                                                                                                                                                     |                                                                                                                    |  |                |            |
| <b>Features</b> <ul style="list-style-type: none"><li>Centres, drill and de burrs sheet metal in one operation</li><li>HSS construction</li><li>Self starting tip</li><li>Dual flute construction for less drilling pressure, faster drilling and longer tool life</li><li>Three flats on drive shaft for secure drive in drill chucks</li></ul> |                                                                                                                    |                                                                                      |                |            |
| Item Number                                                                                                                                                                                                                                                                                                                                      | Item Description                                                                                                   | EAN No                                                                               | Commodity code | Carton Qty |
| T3008                                                                                                                                                                                                                                                                                                                                            | HSS-Multistepdrill 6, 9, 12.5, 15.2, 18.6, 20.4, 22.5, 25.5, 28.3 & 30.5mm (PG7, PG9, PG11, PG13, PG16, M25, PG21) | 5013969985283                                                                        | 82075060       | 1          |
| T3009                                                                                                                                                                                                                                                                                                                                            | HSS-Multistepdrill 4, 5, 6, 7, 8, 9, 10, 11 & 12mm Diameters                                                       | 5013969985290                                                                        | 82075060       | 1          |
| T3010 1                                                                                                                                                                                                                                                                                                                                          | HSS-Multistepdrill 4, 6, 8, 10, 12, 14, 16, 18 & 20mm Diameters                                                    | 5013969985313                                                                        | 82075060       | 1          |
| T3010 2                                                                                                                                                                                                                                                                                                                                          | HSS-Multistepdrill 6, 8, 10, 12, 14, 16, 18, 20, 22, 24, 26, 28 & 30mm Diameters                                   | 5013969985320                                                                        | 82075060       | 1          |

|                                    |                                                                                                                                                        |
|------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Technical product information      |                                                                                                                                                        |
| Standards compliance               | None applicable                                                                                                                                        |
| User health and safety information | None applicable                                                                                                                                        |
| RoHS/WEEE compliance               | This product range does not fall within the scope of RoHS or WEEE regulations                                                                          |
| Material safety data               | None applicable                                                                                                                                        |
| Warranty                           | C.K Tools are guaranteed for life against imperfect materials or workmanship<br>Normal wear and tear or damage caused through inappropriate use is not |

|                   |         |
|-------------------|---------|
|                   | covered |
| Country of origin | Germany |

## Dimensional details

|         | Product only |          |           |              | Product on primary packaging |          |           |                |
|---------|--------------|----------|-----------|--------------|------------------------------|----------|-----------|----------------|
| Item    | Width mm     | Depth mm | Height mm | Net weight g | Width mm                     | Depth mm | Height mm | Gross weight g |
| T3008   | 31           | 31       | 95        | 146          | 35                           | 35       | 115       | 164            |
| T3009   | 12           | 12       | 65        | 18           | 25                           | 25       | 105       | 30             |
| T3010 1 | 20           | 20       | 70        | 50           | 25                           | 25       | 105       | 62             |
| T3010 2 | 30           | 30       | 95        | 146          | 35                           | 35       | 115       | 164            |

|         | Shelf box (secondary packaging) |          |           |                | Euro Pallet data<br>Wi x Hi |                     |
|---------|---------------------------------|----------|-----------|----------------|-----------------------------|---------------------|
| Item    | Width mm                        | Depth mm | Height mm | Gross weight g | No of cartons on base       | Number of rows high |
| T3008   | -                               | -        | -         | -              |                             |                     |
| T3009   | -                               | -        | -         | -              |                             |                     |
| T3010 1 | -                               | -        | -         | -              |                             |                     |
| T3010 2 | -                               | -        | -         | -              |                             |                     |

## Packaging waste details

|         | Primary Packaging |     |        |     | Secondary packaging |     |        |     |
|---------|-------------------|-----|--------|-----|---------------------|-----|--------|-----|
| Item    | Plastic g         | Use | Card g | Use | Plastic g           | Use | Card g | Use |
| T3008   | 18                | Box |        |     | -                   | -   | -      | -   |
| T3009   | 10                | Box |        |     | -                   | -   | -      | -   |
| T3010 1 | 12                | Box |        |     | -                   | -   | -      | -   |
| T3010 2 | 18                | Box |        |     | -                   | -   | -      | -   |