



RIA **US**


Headers

to Type 351

Type 335 page 133

 Type 336 page 140

Accessories

for Type 351

coding set

700025 page 206

Type 351

Screw type terminal block, pluggable, centerline 5 mm / 0.197 inches, wire entry parallel to plug direction, lift system, contact system with integrated wire protection, with mounting flange

Technical Data

RIA **US** V / A / AWG 300 / 16 / 28 - 12

 0.08 - 2.5 mm² 250 V / 4 kV / 12 A

Insulation co-ordination according to EN 60664-1

Clearance and creepage distances min. 3.6 mm

Insulating material class CTI 600

Overvoltage category III III II

Pollution degree 3 2 2

Rated voltage 250 630 630

Rated test voltage 2.5 6 4

Protection category according to IEC 529 IP20

Tightening torque UL 4.4 lb-in max.


Min. insul. strip length 8 mm

Pole size 2 - 24

Color black

Dimensions in mm

1 mm = 0.0394 in.


 $L = (\text{pole size} - 1) \times \text{centerline} + 14.6 \text{ mm} / 0.575 \text{ inches}$

Part numbers (P/N)

(information: page 56)

Complete the part number by adding the pole size.

Type 351

centerline 5 mm / 0.197 inches

P/N 313511

	02	03	04	05	06	07	08
09	10	11	12	13	14	15	16
17	18	19	20	21	22	23	24

Type 351

centerline 10 mm / 0.394 inches

P/N 313512

	02	03	04	05	06	07	08
09	10	11	12				

Standard pole sizes

Available on demand. Minimum order quantity 5000 pieces per item.