

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


ALL RIGHTS RESERVED.

© COPYRIGHT - By -



LOC AF DIST 50

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	AL	REVISED PER ECR-12-013445	09NOV12	KH	PD




- 1 CONTINUOUS STRIP ON REELS.
- 2 WIRE SIZE IS [#24-#22] AWG.
- 3 INSULATION RANGE IS 1.52 [.060]MAX
- 4 ACCEPTS 0.58-0.41 [.023-.016] THK TAB.
- 5 SAME AS 41355 EXCEPT REVERSE REEL FOR ARTOS MACHINE.



SECTION B-B



SECTION C-C



SECTION A-A

42765-1  
PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 12OCT99	<b>STE</b> TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK S HEADER 12OCT99				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S HEADER 12OCT99	NAME RECEPTACLE, TAPER TAB, 2.0 [.078] SERIES			
0 PLC ± -		PRODUCT SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
1 PLC ± -		APPLICATION SPEC	A3 00779		C-42765	-
2 PLC ± 0.38 [.015]		WEIGHT	CUSTOMER DRAWING		SCALE 8:1	SHEET 1 OF 1
3 PLC ± -					REV AL	
4 PLC ± -						
ANGLES ± -						
MATERIAL BRASS		FINISH 0.002032 [.000080] MIN TIN				