

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200870004

Status:


Active

Overview:

Brad Nano-Change (M8) Products

Description:

Nano-Change (M8) to Micro-Change (M12) Double-Ended Cordset, 3 Poles, Female (Straight) to Male (Straight), 24 AWG, PUR Cable, 2.0m (6.56') Length



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
CSA	LR6837
UL	E152210
General	
Product Family	Industrial Cordsets
Series	120087
Connector End A	Nano-Change (M8)
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Nano-Change (M8) Products
Product Name	Micro-Change (M12), Nano-Change (M8)
Protocol	N/A
Region	America
Type	Double Ended
UPC	78678838170
Physical	
Cable Diameter	4.32mm (.170")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Female-Male
Keyway	None
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	TPE
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	3
Temperature Range - Operating	-25°C to +80°C
Wire Size AWG	24
Wire/Cable Type	E152210
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC
Material Info	
Engineering Number	483030B09M020
Reference - Drawing Numbers	
Sales Drawing	SD-120087-017

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

120087 Series

This document was generated on 02/19/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION