














Insulating clamping parts for power transistors

Plastic insulating clamping parts for mounting transistors in cases TO 220, TO 218 and TO 247 for enhanced dielectric strengths

- electrically insulating assembly of the transistor by means of a plastic clamping part
- pin reaching into the hole of the transistor plate
- fastening of clamping part onto the mounting plate by screws, no electroinsulating connection to the transistor
- dielectric strength only determined by the insulating washer between transistor and mounting surface
- no insulating bush necessary, thus no dielectric breakdown

art. no. ISP 220				
art. no. ISP 220 V				
art. no. ISP 218				
art. no. ISP 247				
material: dielectric strength: heat distortion: dielectric constant: dielectric loss factor: specific volume resistance: colour: class of flammability:		polyamide 6, GF reinforced <27 kV/mm 205°C (1.8 MPa); 135°C (8 MPa) 8 [100 Hz]/4.5 [1 MHz] 1300 [100 Hz] 450 [1 MHz] > 10 ¹³ Ω·cm black UL 94 V-0		