

T2250 Serial Matrix Printer

Zero Tear-Off, Zero Skewing And Zero Jams



- Low cost/high performance – 750 cps at 15 cpi (430 pages per hour)!
- Load up to three forms at once; autoswitch between forms without intervention.
- Straight paper path for up to 6-part forms on front tractors.
- Auto-switching parallel and serial interfaces.
- Fully automatic gap adjustment, quick-tear, paper load, and paper parking.
- 15 Industry standard bar codes resident including POSTNET.
- 8 resident fonts.

Make an Impact on the Bottom Line

Printing invoices, shipping bills, bar code labels and reports can impact the bottom line. At 750 cps and with workloads of up to 26,000 pages per month the T2250 is ideal for tough, transaction printing.

The T2250 can be configured optionally with three input tractors. A standard front push tractor and straight paper path load up to 6-part forms with zero tear-off for zero waste, zero skewing and zero jams. A second front tractor and a rear tractor may be added.

The 136-column capacity of the T2250 their rugged design and quiet 53dB(A) operation equip them for the warehouse, the shipping dock or the front desk. Back-room durability combined with front-office 24-wire print quality and a variety of automated performance features make the T2250 a serious solution for demand document printing.

Ideal for Many Markets & Applications

Federal, State & Local Government - Print tax forms, payroll checks, expense reports, inventory reports, invoices.

Manufacturing, Transportation, & Distribution - Print pick lists, shipping labels and freight bills. Excellent readability on all industry standard bar codes, including POSTNET.

Healthcare - Handles a wide variety of media including bar code labels for patient charts, prescription labels, pre-printed forms for billing departments.

Available Configuration:

T2250 - 750 CPS, 24 Wire, 136 Column, Parallel + Serial

Print Speed	At 10, 12, 15 cpi: Draft: 500, 600, 750; NLQ: 180, 220, 135; LQ: 90, 110, 135
Print Method	Serial Impact, Bi-directional
Resolution	360 x 360 DPI
Character Density	5, 6, 7.5, 8.6, 10, 12, 15, 17.1, 20 cpi
Line Density	2, 3, 6, 8, 12 lpi
Character Line Density	136 at 10 cpi, 163 at 12 cpi, 204 at 15 cpi, 232 at 17.1 cpi, 272 at 20 cpi
Character Sets	256 characters, 20 international sets, IBM PC® and Epson®
Printhead Life	500 Million Characters
Printhead Type	24 wire
Memory	128kB
Standard Connectivity	Dual Parallel/Serial (Auto-Switching); 64K buffer
Optional Connectivity	Ethernet 10/100 (External); 9 to 25 pin Serial Adapter
Standard Emulation	MTPL (including 15 resident bar codes and LCP), IBM® Proprinter XL24, Epson® LQ-2550
Optional Emulation	LA75
Fonts	Std: Draft, Copy Draft; NLQ and LQ: Courier, Roman, San Serif, Cyrillic, OCR A/B. Scaleable LCP font (Accepts downloadable fonts in Epson® and IBM® XL24 format). Bar Codes: Code 2/5, Code EAN 8, Code EAN 13, Code UPCA, Code UPCE, Code Delta-Distance; Code 39, Codabar, Code BCD matrix, Code 11, Code MSI/modified Plessey, Code 128, & Code 128 EAN, POSTNET, LCP
Consumables	5.0 million characters
STD Paper Handling	Friction and push tractor, front feed (straight path for continuous forms and labels), auto paper load, auto quick tear, auto view, full paper parking, auto-gap adjustment (for forms thickness)
Opt'l Paper Handling	Supplemental push tractors (front and/or rear), single-bin automatic sheet feeder front, single-bin automatic sheet feeder rear
Number of Copies	Orig. +5 (front push tractors) without jamming; 3 forms at once and autoswitch between forms without operator intervention
Paper Type	Continuous paper, cut sheets (optional feeder)
Paper Weight	NA
Paper Size	3" - 16" width; 3" - 22" length
Parameter Selection	Front panel menu (32 character LCD) and host programmable (3 separate menu configurations can be stored for access through the interface)
Physical Weight	35 lbs
Physical Size	23.6" x 11.8" x 15.7"
Power Voltage	AC 120V or 220-240V
Power Frequency	60/50 Hz
Power Consumption	40 watts (operating); 15 watts (standby)
Compliance	Energy Star compliant, Ozone-free, RoHS, Microsoft, ISO-compliant
Workload	Up to 26,000 pages per month
Reliability MTBF	10,000 hours @ 25% duty cycle
Drivers	Windows 95/98, NT 4.0, 2000, XP, 2003; SAP
Temperature	NA
Humidity	NA
Acoustic	53 dB (A)
Warranty	One Year Return To Depot
Option 1	supplemental push tractors; auto sheet feeder front; auto sheet feeder rear
Option 2	printer stand; paper basket; castors
Option 3	Ethernet 10/100
Options 4	RS-422 I/O



Tally and TallyGenicom are registered trademarks of TallyGenicom, L.P. All other company and product names are trademarks or registered trademarks of their respective owner. Specifications are subject to change without notice. Copyright © 2009 TallyGenicom, L.P.

Printed Date: 05/18/2009



4500 Daly Drive, Suite 100
Chantilly, VA 20151
T 800.436.4266
www.tallygenicom.com