



Spec No.: DS-22-99-0226 Effective Date: 07/30/2010

Revision: I

LITE-ON DCC

RELEASE

BNS-OD-FC001/A4




Property of Lite-On Only

Features

- * Meet ROHS, Green Product.
- * Package In 8mm Tape On 7" Diameter Reels.
- * Compatible With Automatic Placement Equipment.
- * Compatible With Infrared And Vapor Phase Reflow Solder Process.
- * EIA STD package.
- * I.C. compatible.

Package Dimensions



Part No.		Lens	Source Color			
	LTST-C170TBKT	Water Clear	InGaN Blue			

Notes:

- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is $\pm~0.10$ mm (.004") unless otherwise noted.

Part No.: LTST-C170TBKT Page: 1 of 11



Property of Lite-On Only

Absolute Maximum Ratings At Ta=25°C

Parameter	LTST-C170TBKT	Unit	
Power Dissipation	76	mW	
Peak Forward Current (1/10 Duty Cycle, 0.1ms Pulse Width)	100	mA	
DC Forward Current	20	mA	
Derating Linear From 25°C	0.25	mA/°C	
Reverse Voltage Note A	5	V	
Operating Temperature Range	-20°C to + 80°C		
Storage Temperature Range	-30°C to + 100°C		
Wave Soldering Condition	260°C For 5 Seconds		
Infrared Soldering Condition	260°C For 5 Seconds		
Vapor Phase Soldering Condition	215°C For 3 Minutes		

Note A: Reverse Voltage can't be continued operating


Part No.: LTST-C170TBKT Page: 2 of 11




Property of Lite-On Only

Suggestion Profile:

(1) Suggestion IR Reflow Profile For Normal Process



(2) Suggestion IR Reflow Profile For Pb Free Process



Part No.: LTST-C170TBKT Page: 3 of 11



Property of Lite-On Only

Electrical Optical Characteristics At Ta=25°C

Parameter	Symbol	Part No. LTST-	Min.	Тур.	Max.	Unit	Test Condition
Luminous Intensity	IV	С170ТВКТ	28.0	1	180	mcd	IF = 20mA Note 1
Viewing Angle	2 θ 1/2	2 C170TBKT 130 deg		deg	Note 2 (Fig.6)		
Peak Emission Wavelength	ission Wavelength λP C170TBKT			468		nm	Measurement @Peak (Fig.1)
Dominant Wavelength	λd	С170ТВКТ	465.0	-	475.0	nm	IF = 20mA Note 3
Spectral Line Half-Width	Δλ	С170ТВКТ		25		nm	
Forward Voltage	VF	С170ТВКТ	2.80	-	3.80	V	IF = 20mA
Reverse Current	IR	С170ТВКТ			10	μ A	VR = 5V

Notes: 1. Luminous intensity is measured with a light sensor and filter combination that approximates the CIE eye-response curve.

- 2. θ 1/2 is the off-axis angle at which the luminous intensity is half the axial luminous intensity.
- 3. The dominant wavelength, λ d is derived from the CIE chromaticity diagram and represents the single wavelength which defines the color of the device.
- 4. Caution in ESD:

Static Electricity and surge damages the LED. It is recommend to use a wrist band or anti-electrostatic glove when handling the LED. All devices, equipment and machinery must be properly grounded.

Part No.: LTST-C170TBKT Page: 4 of 11



LITEON LITE-ON TECHNOLOGY CORPORATION

Property of Lite-On Only

Bin Code List

Forward Voltage		Unit: V @20mA		
Bin Code	Min.	Max.		
D7	2.80	3.00		
D8	3.00	3.20		
D9	3.20	3.40		
D10	3.40	3.60		
D11	3.60	3.80		

Tolerance on each Forward Voltage bin is +/-0.1 volt

Luminous Intensity Unit		: mcd @20mA
Bin Code	Min.	Max.
N	28.0	45.0
P	45.0	71.0
Q	71.0	112.0
R	112.0	180.0

Tolerance on each Intensity bin is +/-15%


Dominant Wavelength		Unit: nm @20mA		
Bin Code Min.		Max.		
AC	465.0	470.0		
AD	470.0	475.0		

Tolerance for each Dominate Wavelength bin is +/- 1nm

Part No.: LTST-C170TBKT Page: 5 of 11



Property of Lite-On Only



(25 °C Ambient Temperature Unless Otherwise Noted)








Fig.1 Relative Intensity vs. Wavelength












Fig.5 Luminous Intensity vs.

Ambient Temperature

Fig.6 Spatial Distribution

Part No.: LTST-C170TBKT Page: 6 of 11




Property of Lite-On Only

Cleaning


Do not use unspecified chemical liquid to clean LED they could harm the package.

If clean is necessary, immerse the LED in ethyl alcohol or in isopropyl alcohol at normal temperature for less one minute.

Suggest Soldering Pad Dimensions



Package Dimensions Of Tape And Reel



Notes:


1. All dimensions are in millimeters (inches).

Part No.: LTST-C170TBKT Page: 7 of 11



LITEON LITE-ON TECHNOLOGY CORPORATION

Property of Lite-On Only



Notes:

- 1. Empty component pockets sealed with top cover tape.
- 2. 7 inch reel-3000 pieces per reel.
- 3. Minimum packing quantity is 500 pcs for remainders.
- 4. The maximum number of consecutive missing lamps is two.
- 5. In accordance with ANSI/EIA 481-1-A-1994 specifications.

No.: LTST-C170TBKT 11 Page: of



Property of Lite-On Only

CAUTIONS

1. Application

The LEDs described here are intended to be used for ordinary electronic equipment (such as office equipment, communication equipment and household applications). Consult Liteon's Sales in advance for information on applications in which exceptional reliability is required, particularly when the failure or malfunction of the LEDs may directly jeopardize life or health (such as in aviation, transportation, traffic control equipment, medical and life support systems and safety devices).

2. Storage

The storage ambient for the LEDs should not exceed 30°C temperature or 70% relative humidity. It is recommended that LEDs out of their original packaging are IR-reflowed within one week. For extended storage out of their original packaging, it is recommended that the LEDs be stored in a sealed container with appropriate desiccant, or in a desiccators with nitrogen ambient. LEDs stored out of their original packaging for more than a week should be baked at about 60 deg C for at least 24 hours before solder assembly.

3. Cleaning

Use alcohol-based cleaning solvents such as isopropyl alcohol to clean the LED if necessary.

4. Soldering

Recommended soldering conditions:

Reflow so	oldering	Wave So	ldering	Soldering iron		
		Pre-heat	100°C Max.	Temperature	300°C Max.	
Pre-heat time				Soldering time	3 sec. Max.	
Peak temperature Soldering time			260°C Max. 10 sec. Max.		(one time only)	
Soldering time	10 sec. Max.	Soldering time	TO sec. Max.			

5. Drive Method

An LED is a current-operated device. In order to ensure intensity uniformity on multiple LEDs connected in parallel in an application, it is recommended that a current limiting resistor be incorporated in the drive circuit, in series with each LED as shown in Circuit A below.



- (A) Recommended circuit.
- (B) The brightness of each LED might appear different due to the differences in the I-V characteristics of those LEDs.

6. ESD (Electrostatic Discharge)

Static Electricity or power surge will damage the LED.

Suggestions to prevent ESD damage:

- Use of a conductive wrist band or anti-electrostatic glove when handling these LEDs.
- All devices, equipment, and machinery must be properly grounded.
- Work tables, storage racks, etc. should be properly grounded.
- Use ion blower to neutralize the static charge which might have built up on surface of the LED's plastic lens as a result of friction between LEDs during storage and handling.

Part No.: LTST-C170TBKT	Page: 9 of 11
-------------------------	---------------



Property of Lite-On Only

ESD-damaged LEDs will exhibit abnormal characteristics such as high reverse leakage current, low forward voltage, or "no lightup" at low currents.

To verify for ESD damage, check for "lightup" and Vf of the suspect LEDs at low currents.

The Vf of "good" LEDs should be >2.0V@0.1mA for InGaN product and >1.4V@0.1mA for AlInGaP product.

7. Reliability Test

Classification	Test Item	Test Condition	Reference Standard
	Operation Life	Ta= Under Room Temperature As Per Data Sheet Maximum Rating *Test Time= 1000HRS (-24HRS,+72HRS)	MIL-STD-750D:1026 (1995) MIL-STD-883D:1005 (1991) JIS C 7021:B-1 (1982)
Endurance Test	High Temperature High Humidity Storage	IR-Reflow In-Board, 2 Times Ta= 65±5°C,RH= 90∼95% *Test Time= 240HRS±2HRS	MIL-STD-202F:103B(1980) JIS C 7021:B-11(1982)
1000	High Temperature Storage	Ta= 105±5°C *Test Time= 1000HRS (-24HRS,+72HRS)	MIL-STD-883D:1008 (1991) JIS C 7021:B-10 (1982)
	Low Temperature Storage	Ta= -55±5°C *Test Time=1000HRS (-24HRS,+72H RS)	JIS C 7021:B-12 (1982)
	Temperature Cycling	105°C ~ 25°C ~ -55°C ~ 25°C 30mins 5mins 30mins 5mins 10 Cycles	MIL-STD-202F:107D (1980) MIL-STD-750D:1051(1995) MIL-STD-883D:1010 (1991) JIS C 7021:A-4(1982)
	Thermal Shock	IR-Reflow In-Board, 2 Times $85 \pm 5^{\circ}$ C $\sim -40^{\circ}$ C $\pm 5^{\circ}$ C ~ 10 mins 10 Cycles	MIL-STD-202F:107D(1980) MIL-STD-750D:1051(1995) MIL-STD-883D:1011 (1991)
	Solder Resistance	T.sol= $260 \pm 5^{\circ}$ C Dwell Time= 10 ± 1 secs	MIL-STD-202F:210A(1980) MIL-STD-750D:2031(1995) JIS C 7021:A-1(1982)
Environmental Test	IR-Reflow Normal Process	Ramp-up rate($183^{\circ}\mathbb{C}$ to Peak) $+3^{\circ}\mathbb{C}$ / second max Temp. maintain at $125(\pm 25)^{\circ}\mathbb{C}$ 120 seconds max Temp. maintain above $183^{\circ}\mathbb{C}$ 60-150 seconds Peak temperature range $235^{\circ}\mathbb{C} + 5/-0^{\circ}\mathbb{C}$ Time within $5^{\circ}\mathbb{C}$ of actual Peak Temperature (tp) 10-30 seconds Ramp-down rate $+6^{\circ}\mathbb{C}$ /second max	MIL-STD-750D:2031.2(1995) J-STD-020(1999)
	IR-Reflow Pb Free Process	Ramp-up rate($217^{\circ}\mathbb{C}$ to Peak) $+3^{\circ}\mathbb{C}$ / second max Temp. maintain at $175(\pm 25)^{\circ}\mathbb{C}$ 180 seconds max Temp. maintain above $217^{\circ}\mathbb{C}$ 60-150 seconds Peak temperature range $260^{\circ}\mathbb{C} + 0/-5^{\circ}\mathbb{C}$ Time within $5^{\circ}\mathbb{C}$ of actual Peak Temperature (tp) 20-40 seconds Ramp-down rate $+6^{\circ}\mathbb{C}$ /second max	MIL-STD-750D:2031.2(1995) J-STD-020(1999)
	Solderability	T.sol= $235 \pm 5^{\circ}$ C Immersion time 2 ± 0.5 sec Immersion rate 25 ± 2.5 mm/sec Coverage $\geq 95\%$ of the dipped surface	MIL-STD-202F:208D(1980) MIL-STD-750D:2026(1995) MIL-STD-883D:2003(1991) IEC 68 Part 2-20 JIS C 7021:A-2(1982)

8. Others

The appearance and specifications of the product may be modified for improvement without prior notice.

Part No.: LTST-C170TBKT	Page:	10	of	11	
-------------------------	-------	----	----	----	--



Property of Lite-On Only

9. Suggested Checking List

Training and Certification

- 1. Everyone working in a static-safe area is ESD-certified?
- 2. Training records kept and re-certification dates monitored?

Static-Safe Workstation & Work Areas

- 1. Static-safe workstation or work-areas have ESD signs?
- 2. All surfaces and objects at all static-safe workstation and within 1 ft measure less than 100V?
- 3. All ionizer activated, positioned towards the units?
- 4. Each work surface mats grounding is good?

Personnel Grounding

- 1. Every person (including visitors) handling ESD sensitive (ESDS) items wears wrist strap, heel strap or conductive shoes with conductive flooring?
- 2. If conductive footwear used, conductive flooring also present where operator stand or walk?
- 3. Garments, hairs or anything closer than 1 ft to ESD items measure less than 100V*?
- 4. Every wrist strap or heel strap/conductive shoes checked daily and result recorded for all DLs?
- 5. All wrist strap or heel strap checkers calibration up to date? Note: *50V for Blue LED.

Device Handling

- 1. Every ESDS items identified by EIA-471 labels on item or packaging?
- 2. All ESDS items completely inside properly closed static-shielding containers when not at static-safe workstation?
- 3. No static charge generators (e.g. plastics) inside shielding containers with ESDS items?
- 4. All flexible conductive and dissipative package materials inspected before reuse or recycles?

Others

- 1. Audit result reported to entity ESD control coordinator?
- 2. Corrective action from previous audits completed?
- 3. Are audit records complete and on file?

Part No.: LTST-C170TBKT Page: 11 of 11