




BXT BAS (920 300)


Four-pole version for universal use with all types of protection modules
The modules can be plugged in and removed without signal interruption
Universal design without protection elements



Figure without obligation



Basic circuit diagram with and without plugged-in module



Dimension drawing BXT BAS

The BLITZDUCTOR XT base part is a very space-saving four-pole universal feed-through terminal for the insertion of a protection module without signal interruption. The snap-in mechanism at the supporting foot of the base part allows the protection module to be safely earthed via the DIN rail. As no components of the protective circuit are situated in the base part, maintenance operation is only required for the protection modules.

Type	BXT BAS
Part No.	920 300
Operating temperature range	-40°C...+80°C
Degree of protection	IP 20
For mounting on	35 mm DIN rails acc. to EN 60715
Connection (input / output)	screw / screw
Cross-sectional area, solid	0.08 - 4 mm ²
Cross-sectional area, flexible	0.08 - 2.5 mm ²
Tightening torque (terminals)	0.4 Nm
Earthing via	35 mm DIN rail acc. to EN 60715
Enclosure material	polyamide PA 6.6
Colour	yellow
ATEX approvals	DEKRA 11ATEX0089 X: II 3 G Ex nA IIC T4 Gc ^{*)}
IECEx approvals	DEK 11.0032X: Ex nA IIC T4 Gc ^{*)}
Approvals	CSA, VdS, UL, GOST
Weight	45 g
Customs tariff number	85369010
GTIN	4013364109179
PU	1 pc(s)

^{*)} only in connection with an approved protection module

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.