


	10	9	8	7	6	5	4	3	2	19430
	MATERIAL NUMBER	ENGINEERING NUMBER	COLOR INSERT	SOLID WIRE RANGE AWG	PORTS	DIM A	DIM B	DIM C		
F	194300001	PC2-RED	RED	12-22	2	.37/9.5	.41/10.5	.77/19.5		F
	194300002	PC3-ORANGE	ORANGE	12-22	3	.37/9.5	.53/13.5	.78/19.7		
	194300003	PC4-YELLOW	YELLOW	12-22	4	.37/9.5	.68/17.2	.78/19.7		
	194300004	PC5-GRAY	GRAY	12-22	5	.37/9.5	.83/21.1	.78/19.7		
	194300005	PC8-BLACK	BLACK	12-22	8	.66/16.8	.69/17.5	.75/19.0		



PORTS 8

PORTS 2,3,4,5

REF NOTES:

- 1.) CURRENT: 24A(VDE)
- 2.) VOLTAGE: UL-600V, VDE-450V
- 3.) WORKING TEMP: -30°C TO 105°C
- 4.) HOUSING MATERIAL: UL 94V-2
FLAME RETARDANT THERMOPLASTIC
- 5.) WIRE STRIP LENGTH: APPROX. .45/11.0
- 6.) UL FILE NO. E32244 (B1)
- 7.) INTERNATIONAL APPROVALS: CE, VDE, FIMKO, KEMA, CEBEC

UL, ENG NUMBERS EC NO: WNA2012-0128 DRWN:ETHRODAH012/03/15 CHKD:JMACNEIL 2012/03/15 APPR: JMACNEIL 2012/03/20 B1	DESCRIPTION REV	QUALITY SYMBOLS - 0 C - 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE 1:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	REVISE ON CAD ONLY		
					DIMENSION STYLE			TITLE		
					IN/MM			PUSH-IN WIRE CONNECTOR 12-22AWG		
			4 PLACES ± --- ± ---		DRAWN BY	DATE				
			3 PLACES ± --- ± ---		B.RUPERT	11/13/03				
			2 PLACES ± --- ± .020		CHECKED BY	DATE				
			1 PLACE ± 0.51 ± .020		J.PAWLIC	11/13/03		MOLEX MOLEX INCORPORATED		
			ANGULAR ± ---°		APPROVED BY	DATE		MATERIAL NO.	DOCUMENT NO.	SHEET NO.
			DRAFT WHERE APPLICABLE		R.DEROSS	11/13/03		SEE CHART	SD-19430-001	1 OF 1
			MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					B