






Copyright FCI,

PRODUCT NO.  
SEE TABLE




| mat'l. code |                |     |            | tolerances unless otherwise specified |            |           |          | CUSTOMER COPY                                                                                       |                                                   | FCI<br><br>www.fciconnect.com |  |  |
|-------------|----------------|-----|------------|---------------------------------------|------------|-----------|----------|-----------------------------------------------------------------------------------------------------|---------------------------------------------------|-------------------------------|--|--|
| ltr         | ecn no         | dr  | date       | linear                                | .X ± 0.10  |           |          | projection<br> | title<br>DUAL POLARIZED<br>QUICKIE II LOW PROFILE |                               |  |  |
| J           | V22169         | MSC | 1992-05-21 |                                       | .XX ± 0.05 |           |          |                                                                                                     |                                                   |                               |  |  |
| K           | N05-0368       | GUL | 2005-12-27 |                                       | .XXX ±     |           |          |                                                                                                     |                                                   |                               |  |  |
| L           | N09-0400       | AZH | 2010-01-18 | angles                                | ± 2        |           |          |                | product family QUICKIE<br>size dwg no<br>A4 66432 |                               |  |  |
|             |                |     |            | dr                                    | GuLing     | 12/27/05  |          |                                                                                                     |                                                   |                               |  |  |
|             |                |     |            | enr                                   | TaoDeniel  | 12/27/05  |          |                                                                                                     |                                                   |                               |  |  |
|             |                |     |            |                                       | chr        | TaoDeniel | 12/27/05 | scale<br>1:1                                                                                        | sheet<br>1 of 2                                   |                               |  |  |
|             |                |     |            | appd                                  | Jason Zhou | 12/27/05  |          |                                                                                                     |                                                   |                               |  |  |
| sheet index | revision sheet | L   | 1-2        |                                       |            |           |          |                                                                                                     |                                                   |                               |  |  |



Copyright FCI.

| 1               |      |       |       |       | 2 | 3       |                   |            | 4                      | 5 |               | 6 |
|-----------------|------|-------|-------|-------|---|---------|-------------------|------------|------------------------|---|---------------|---|
| PRODUCT NO.     | SIZE | DIM L | DIM S | DIM C |   | DASH NO | COVER ORIENTATION |            | POLARIZATION           |   | STRAIN RELIEF |   |
| 66432-X10/X10LF | 2X5  | 17.27 | 13.21 | 10.16 |   | -0XX    | THRU              | DUAL ENTRY | DUAL POL.              |   | YES           |   |
| -X14/X14LF      | 2X7  | 22.35 | 18.29 | 15.24 |   | -1XX    | THRU              | DUAL ENTRY | CENTER KEY & DUAL POL. |   | YES           |   |
| -X16/X16LF      | 2X8  | 24.89 | 20.83 | 17.78 |   | -2XX    | BLIND             | RIGHT      | DUAL                   |   | YES           |   |
| -X20/X20LF      | 2X10 | 29.97 | 25.91 | 22.86 |   | -3XX    | BLIND             | RIGHT      | CENTER KEY & DUAL POL. |   | YES           |   |
| -X24/X24LF      | 2X12 | 35.05 | 30.99 | 27.94 |   | -4XX    | BLIND             | LEFT       | DUAL POL.              |   | YES           |   |
| -X26/X26LF      | 2X13 | 37.59 | 33.53 | 30.48 |   | -5XX    | BLIND             | LEFT       | CENTER KEY & DUAL POL. |   | YES           |   |
| -X30/X30LF      | 2X15 | 42.67 | 38.61 | 35.56 |   | -6XX    | BLIND             | RIGHT      | CENTER KEY & DUAL POL. |   | NO            |   |
| -X34/X34LF      | 2X17 | 47.75 | 43.69 | 40.64 |   | -7XX    | BLIND             | LEFT       | CENTER KEY & DUAL POL. |   | NO            |   |
| -X40/X40LF      | 2X20 | 55.37 | 51.31 | 48.26 |   | -8XX    | DISCONTINUED      |            |                        |   |               |   |
| -X44/X44LF      | 2X22 | 60.45 | 56.39 | 53.34 |   | -9XX    | DISCONTINUED      |            |                        |   |               |   |
| -X50/X50LF      | 2X25 | 68.07 | 64.01 | 60.96 |   |         |                   |            |                        |   |               |   |
| 66432-X60/X60LF | 2X30 | 80.77 | 76.71 | 73.66 |   |         |                   |            |                        |   |               |   |



#### NOTES:

1. TERMINAL MATERIAL: FULL HARD PHOS. BRONZE ALLOY. UNS-C51000.
2. TERMINAL PLATING: 50u"/1.27um MIN Ni UNDERPLATE OVER ENTIRE TERMINAL AND 30u"/0.76um MIN Au OR GXT IN CONTACT AREA ONLY;
3. MOLDING MATERIAL: BASE & COVER-GLASS FILLED POLYESTER. FLAME RETARDANT PER UL94V-0. COLOR-BLUE.
4. CONNECTOR ASSEMBL ES PACKAGED IN TUBES.
5. THE FIRST TWO CAVITY POSITIONS AND THE LAST TWO. ARE IDENTIFIED BY NUMBER.
6. POLARIZING FEATURES ARE DESCRIBED IN TABLE.
7. MOLDING MATERIAL: STRAIN RELIEF-POLYSULFONE. FLAME RETARDANT PER UL 94V-0,COLOR-NATURAL.
8. THE POLARIZING FEATURE ON THIS END IS NON-EXISTANT ON 2X5 AND 2X7 POSITION CONNECTORS.
9. 2X5 POSITION NOT AVAILABLE WITH POLARIZATION SLOT ON CENTER KEY STYLE.
10. PRODUCT NUMBER 66432-XXX LF LEAD FREE OPTION
11. WITH "LF" MARK, TERMINAL PLATING: 50u"/1.27um Ni UNDERPLATE OVER ENTIRE TERMINAL AND 30u"/0.76um MIN AU OR GXT IN CONTACT AREA ONLY.
12. FOR LEAD FREE P/N, THE PRODUCT MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
13. FOR LEAD FREE P/N, THE PLASTIC PART WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.
14. PRODUCT SPEC. BUS-12-082
15. PLATING OPTIONS: MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

|                                          |            |          |                                                                                                     |                                                   |                                                                                              |  |                    |        |
|------------------------------------------|------------|----------|-----------------------------------------------------------------------------------------------------|---------------------------------------------------|----------------------------------------------------------------------------------------------|--|--------------------|--------|
| tolerances unless<br>otherwise specified |            |          | CUSTOMER<br>COPY                                                                                    |                                                   | FCI<br> |  | www.fciconnect.com |        |
| linear                                   | .X ± 0.1   |          | projection<br> | title<br>DUAL POLARIZED<br>QUICKIE II LOW PROFILE |                                                                                              |  |                    |        |
|                                          | .XX ± 0.05 |          |                                                                                                     |                                                   |                                                                                              |  |                    |        |
|                                          | .XXX ±     |          |                                                                                                     |                                                   |                                                                                              |  |                    |        |
| angles                                   | ±2         |          |                                                                                                     |                                                   |                                                                                              |  |                    |        |
| dr                                       | GuLing     | 12/27/05 | INCH/MM<br>    |                                                   | product family QUICKIE                                                                       |  |                    | code   |
| engr                                     | TaoDeniel  | 12/27/05 | scale<br>1:1                                                                                        |                                                   | size dwg no                                                                                  |  | NT                 |        |
| chr                                      | TaoDeniel  | 12/27/05 |                                                                                                     |                                                   | A4                                                                                           |  | 66432              | sheet  |
| appd                                     | Jason Zhou | 12/27/05 |                                                                                                     |                                                   |                                                                                              |  |                    | 2 of 2 |