


ST02D-82

OUTLINE DIMENSIONS



RATINGS

●Absolute Maximum Ratings (TI=25°C)


Item	Symbol	Conditions	ZD	Di	Unit
Storage Temperature	T _{stg}		-40~150	-40~150	°C
Junction Temperature	T _j		150	150	°C
Peak Surge Reverse Power	P _{RSM}	10/1000 μ s, Non-repetitive	200	-	W
Peak Surge Reverse Current	I _{RSM}	10/1000 μ s, Non-repetitive	1.7	-	A
Maximum Reverse Voltage	V _{RM}		67	600	V

●Electrical Characteristics (TI=25°C)

Item	Symbol	Conditions	ZD	Di	Unit
Movement Start Voltage	V _{BR}	I _R = 1mA	MIN 74 TYP 82 MAX 90	-	V
Restriction Voltage	V _{GL}	I _{PP} = 1.7A	MAX 118	-	V
Leak Current	I _R	V _R = V _{RM}	MAX 5	MAX 5	μ A
Reverse Recovery Time	trr	I _F /I _R =0.1A/0.3A	-	MAX 500	ns
Thermal Resistance	θ jL	Junction to lead	MAX 17	MAX 17	°C/W


ST02D-82

Breakdown Voltage




ST02D-82

Reverse Current




ST02D-82

Reverse Current




ST02D-82

Peak Surge Reverse Power




ST02D-82

Junction Capacitance




ST02D-82

Junction Capacitance



ST02D-82

Junction Capacitance



ST02D-82

Junction Capacitance

