

PIN	A	B	C
04	8.50	1.50	2.60
05	9.00	2.00	3.10
06	9.50	2.50	3.60
07	10.00	3.00	4.10
08	10.50	3.50	4.60
09	11.00	4.00	5.10
10	11.50	4.50	5.60
11	12.00	5.00	6.10
12	12.50	5.50	6.60
13	13.00	6.00	7.10
14	13.50	6.50	7.60
15	14.00	7.00	8.10
16	14.50	7.50	8.60
17	15.00	8.00	9.10
18	15.50	8.50	9.60
19	16.00	9.00	10.10
20	16.50	9.50	10.60
21	17.00	10.00	11.10
22	17.50	10.50	11.60
23	18.00	11.00	12.10
24	18.50	11.50	12.60
25	19.00	12.00	13.10
26	19.50	12.50	13.60
27	20.00	13.00	14.10
28	20.50	13.50	14.60
29	21.00	14.00	15.10
30	21.50	14.50	15.60

PIN	A	B	C
31	22.00	15.00	16.10
32	22.50	15.50	16.60
33	23.00	16.00	17.10
34	23.50	16.50	17.60
35	24.00	17.00	18.10
36	24.50	17.50	18.60
37	25.00	18.00	19.10
38	25.50	18.50	19.60
39	26.00	19.00	20.10
40	26.50	19.50	20.60
41	27.00	20.00	21.10
42	27.50	20.50	21.60
43	28.00	21.00	22.10
44	28.50	21.50	22.60
45	29.00	22.00	23.10
46	29.50	22.50	23.60
47	30.00	23.00	24.10
48	30.50	23.50	24.60
49	31.00	24.00	25.10
50	31.50	24.50	25.60
51	32.00	25.00	26.10
52	32.50	25.50	26.60
53	33.00	26.00	27.10
54	33.50	26.50	27.60
55	34.00	27.00	28.10
56	34.50	27.50	28.60
57	35.00	28.00	29.10
58	35.50	28.50	29.60
59	36.00	29.00	30.10
60	36.50	29.50	30.60

SPECIFICATIONS:

MATERIAL:-

HOUSING: HIGH-TEMP THERMOSPLASTIC UL94V-0

COLOUR: BLACK

ACTUATOR: HIGH-TEMP THERMOSPLASTIC UL94V-0

COLOUR: WHITE

CONTACT: COPPER ALLOY, T=0.2mm

FITTING NAIL: COPPER ALLOY, T=0.2mm

FINISH:-

CONTACT AREA: TIN PLATED

SOLDER AREA: TIN PLATED

FITTING NAIL: TIN PLATED

TOLERANCES




X.X = $\pm 0.30\text{mm}$ X.XX = $\pm 0.20\text{mm}$ ANGLE = $\pm 0^\circ 30'$

NOTES: ALL DIMENSIONS AND NOTES

MARKED * ARE CRITICAL AND




MUST BE CHECKED IN ACCORDANCE

WITH QUALITY INSTRUCTION Q1-02A



RECOMMENDED P.C.B BOARD PATTERN DIM. (REF)

OBSOLETE

RECOMMENDED APPLICABLE
FPC LAYOUT (THICKNESS: 0.30 ± 0.03)

SECTION A-A

Allan	6	02.09.09	A232
Allan	5	15.09.08	A161
Allan	4	18.12.07	A099
Allan	3	26.07.07	A063
Allan	2	06.07.07	A058
Allan	1	01.08.06	-

NAME	ISS.	DATE	C/NOTE
------	------	------	--------

APPROVED: _____

CHECKED: *Ben*

DRAWN: Allan

CUSTOMER REF.:

ASSEMBLY DRG:

*PLEASE CONTACT TECHNICAL SALES
FOR WAYS WITH * FOR AVAILABILITY

ORDER CODE

F05E- XX 3146R

NO. OF WAYS PER ROW

HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.comHARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.ukHARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sgTHIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.TOLERANCES
X. = $\pm 1\text{mm}$
X.X = $\pm 0.25\text{mm}$
X.XX = $\pm 0.10\text{mm}$
X.XXX = $\pm 0.01\text{mm}$
ANGLES = $\pm 5^\circ$
UNLESS STATED

MATERIAL:

SEE NOTES

FINISH:

SEE NOTES

S/AREA:

mm²

TITLE:

0.5 ZIF FPC SMT V/T

DRAWING NUMBER:

F05E- XX 3146R

SHT
1
OF

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Harwin:

F05E-303146	F05E-433146R	F05E-233146R	F05E-133146R	F05E-533146R	F05E-333146R	F05E-503146
F05E-283146R	F05E-483146R	F05E-083146R	F05E-383146R	F05E-183146R	F05E-103146	F05E-373146R
F05E-173146R	F05E-073146R	F05E-473146R	F05E-273146R	F05E-343146R	F05E-543146R	F05E-143146R
F05E-043146R	F05E-443146R	F05E-243146R	F05E-393146R	F05E-193146R	F05E-093146R	F05E-493146R
F05E-293146R	F05E-053146	F05E-403146R	F05E-203146R	F05E-103146R	F05E-503146R	F05E-303146R
F05E-453146R	F05E-053146R	F05E-253146R	F05E-153146R	F05E-553146R	F05E-353146R	F05E-203146
F05E-223146R	F05E-423146R	F05E-323146R	F05E-523146R	F05E-123146R	F05E-403146	F05E-513146R
F05E-113146R	F05E-313146R	F05E-213146R	F05E-413146R	F05E-263146R	F05E-463146R	F05E-063146R
F05E-363146R	F05E-163146R	F05E-563146R				