

## High-current terminal block - PTPOWER 95-3L-F - 3260121

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



High-current terminal block, Blocked, Connection method: Push-in connection, Number of positions: 3, Cross section: 25 mm<sup>2</sup> - 95 mm<sup>2</sup>, AWG: 4 - 3/0, Width: 75 mm, Height: 99.8 mm, Color: gray, Mounting type: ct screw connection

### Product Features

- ✓ Quick and easy connection is now also possible for large conductors with the high-current terminal block
- ✓ The Push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors
- ✓ The compact design enables wiring in a confined space
- ✓ In addition to using the existing test connection, pick-off terminal blocks can be connected, each of which can also accommodate two test cables



### Key commercial data

|                                      |           |
|--------------------------------------|-----------|
| Packing unit                         | 1 pc      |
| Minimum order quantity               | 3 pc      |
| Weight per Piece (excluding packing) | 620.0 GRM |
| Custom tariff number                 | 85369010  |
| Country of origin                    | Poland    |

### Technical data

#### General

|                                         |                                                         |
|-----------------------------------------|---------------------------------------------------------|
| Number of levels                        | 1                                                       |
| Number of connections                   | 2                                                       |
| Color                                   | gray                                                    |
| Insulating material                     | PA                                                      |
| Inflammability class according to UL 94 | V0                                                      |
| Maximum load current                    | 232 A (with 95 mm <sup>2</sup> conductor cross section) |
| Rated surge voltage                     | 8 kV                                                    |
| Pollution degree                        | 3                                                       |
| Surge voltage category                  | III                                                     |

# High-current terminal block - PTPOWER 95-3L-F - 3260121

## Technical data

### General

|                                  |                                                         |
|----------------------------------|---------------------------------------------------------|
| Insulating material group        | I                                                       |
| Connection in acc. with standard | IEC 60947-7-1                                           |
| Maximum load current             | 232 A (with 95 mm <sup>2</sup> conductor cross section) |
| Nominal current I <sub>N</sub>   | 232 A                                                   |
| Nominal voltage U <sub>N</sub>   | 1500 V                                                  |
| Maximum load current             | 232 A (with 95 mm <sup>2</sup> conductor cross section) |
| Open side panel                  | nein                                                    |
| Number of positions              | 3                                                       |

### Dimensions

|                    |           |
|--------------------|-----------|
| Width              | 75 mm     |
| Length             | 139.1 mm  |
| Height             | 99.8 mm   |
| Hole diameter      | 8 mm      |
| Drill hole spacing | 126.40 mm |

### Connection data

|                                                                            |                    |
|----------------------------------------------------------------------------|--------------------|
| Connection in acc. with standard                                           | IEC 60947-7-1      |
| Connection method                                                          | Push-in connection |
| Conductor cross section solid min.                                         | 25 mm <sup>2</sup> |
| Conductor cross section solid max.                                         | 95 mm <sup>2</sup> |
| Conductor cross section AWG/kcmil min.                                     | 4                  |
| Conductor cross section AWG/kcmil max.                                     | 3/0                |
| Conductor cross section stranded min.                                      | 25 mm <sup>2</sup> |
| Conductor cross section stranded max.                                      | 95 mm <sup>2</sup> |
| Min. AWG conductor cross section, stranded                                 | 4                  |
| Max. AWG conductor cross section, stranded                                 | 4/0                |
| Conductor cross section stranded, with ferrule without plastic sleeve min. | 25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule without plastic sleeve max. | 95 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule with plastic sleeve min.    | 25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule with plastic sleeve max.    | 95 mm <sup>2</sup> |
| Cross section with insertion bridge, solid max.                            | 95 mm <sup>2</sup> |
| Cross section with insertion bridge, stranded max.                         | 70 mm <sup>2</sup> |
| Cross section with insertion bridge, solid max.                            | 95 mm <sup>2</sup> |
| Cross section with insertion bridge, stranded max.                         | 70 mm <sup>2</sup> |
| Stripping length                                                           | 40 mm              |

## High-current terminal block - PTPOWER 95-3L-F - 3260121

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27141120 |
| eCl@ss 4.1 | 27141120 |
| eCl@ss 5.0 | 27141120 |
| eCl@ss 5.1 | 27141120 |
| eCl@ss 6.0 | 27141120 |
| eCl@ss 7.0 | 27141120 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000897 |
| ETIM 4.0 | EC000897 |
| ETIM 5.0 | EC000897 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |

### Approvals

#### Approvals

---

##### Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

---

##### Ex Approvals

---

##### Approvals submitted

---

##### Approval details

# High-current terminal block - PTPOWER 95-3L-F - 3260121

## Approvals

|                                                                                                 |        |
|-------------------------------------------------------------------------------------------------|--------|
| UL Recognized  |        |
| mm²/AWG/kcmil                                                                                   | 4-4/0  |
| Nominal current I <sub>N</sub>                                                                  | 230 A  |
| Nominal voltage U <sub>N</sub>                                                                  | 1000 V |

|                                                                                                  |        |
|--------------------------------------------------------------------------------------------------|--------|
| cUL Recognized  |        |
|                                                                                                  | C      |
| mm²/AWG/kcmil                                                                                    | 4-4/0  |
| Nominal current I <sub>N</sub>                                                                   | 230 A  |
| Nominal voltage U <sub>N</sub>                                                                   | 1000 V |

|     |
|-----|
| EAC |
|-----|

|                                                                                                      |
|------------------------------------------------------------------------------------------------------|
| cULus Recognized  |
|------------------------------------------------------------------------------------------------------|

## Drawings

Circuit diagram



Dimensioned drawing

