



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO. SPC-FD05 * Effective: 12/21/98 * DCP No. 860			
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD
170	A	RELEASED	HYO	1/19/00	JJC	1/28/00	DJC

SPECIFICATIONS:

- 1.INSULATOR: POLYAMIDE (NYLON)
- 2. CONTACT: BRASS, NICKEL PLATED
- 3. VOLTAGE: 1000V CATIII P2 (IEC61010-1)
- 4. CURRENT: 36A MAX.
- 5. RESISTANCE: < 5 milliohms
- 6. TEMPERATURE: -20°C TO +80°C
- 7. COLOR: RED

MOUNTING HOLE



DISCLAIMER
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

**SPC TECHNOLOGY**

DRAWING TITLE:				DRAWING TITLE:			
PUSH-IN SAFETY SOCKET, W/M4 STUD				PUSH-IN SAFETY SOCKET, W/M4 STUD			
Tolerances Unless Otherwise Specified		DRAWN BY:		DATE:		SIZE	
Decimals		HISHAM ODISH		1/19/00		DWG. NO.	
.XX ± .02		CHECKED BY:		DATE:		SPC4858	
.XXX ± .005		JOHN COLE		1/28/00		ELECTRONIC FILE	
		APPROVED BY:		DATE:		50N069.DWG	
		DANIEL CAREY		4/5/00		REV	
						A	