






MATERIAL LIST:

NO.	PARTS NAME	SPECIFICATION DESCRIPTION
①	CABLE	UL20276 7*(1P*30AWG+AL+D+JZD)+1P*30AWG+3C*30AWG +AL+D+B (60%) OD:7.5±0.2mm COLOR:BLACK
②	DVI CONNECTOR	DVI 24+1 MALE INSULATOR BLACK SOLDER TYPE PIN GOLD PLATED 1u" GOLD PLATED SHELL
③	SCREW	Ø4*47mm NICKEL PLATED
④	MOLDING PVC	MOLDING PVC 063 45P COLOR:BLACK
⑤	MOLDING PVC	MOLDING PVC 063 30P COLOR:BLACK

Marking: Maxxtro C AWM E200765 STYLE 20276 80°C 30V FT2



ITEM NO	LENGTH	PVC COLOR	PACKING
103072	1800±50mm	BLACK 0020	BLISTER CARD



ELECTRONIC TEST:

- A.OPEN/SHORT/INTERMITTENCE: 100%.
- B.HI-POT: 300V DC/sec
- C.INSULATION RESISTANCE: 10M ohm (MIN)
- D.CONDUCTIVE RESISTANCE: 5ohm (MAX)

PIN OUT



REMARK	NO	CHA.NO	SIGNATURE	DATE	SIGN	REV.	SCALE
DRAWN BY		Renzhi					
CHECKED BY							
AUDITED BY			APPROVED BY	Qingho		A	
CRAFT			DATE	2010.11.04	PAGE	OF	

