



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS in.				
		A $\pm .03$	W $\pm .01$	C $\pm .02$	M $\pm .03$	H $\pm .01$
PN22-4F	#4	.67 (17.02)	.20 (5.08)	.21 (5.33)	.57 (14.49)	.12 (3.05)
PN22-6F	#6	.77 (19.56)	.25 (6.35)	.26 (6.60)	.63 (16.00)	.15 (3.81)

NOTES:

- USED FOR:
 - #26-22 AWG SOLID OR STRANDED COPPER WIRE
 - 221° [105°C] MAX. TEMP. RATING
 - 300V MAX. VOLTAGE RATING
- INSTALLATION TOOLS: CT-520
- WIRE STRIP LENGTH: 3/16 $^{+1/32}_{-0}$ [4,8 $^{+0,8}_{-0}$]
- MATERIAL:
 - STAMPING: .02" [0,5] THK COPPER, TIN PLATED
 - HOUSING: NYLON, YELLOW
 - SLEEVE: BRASS, TIN PLATED
- SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT.



							TITLE FORK TERMINALS, NYLON INSULATED #26-22 CUSTOMER DRAWING					
							ITEM REVISION NAME N41235BA/07		PANDUIT MATERIAL: SEE NOTES			
							DATASET FILE NAME N41235BA_DC/07A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .1 [2.54] .XXX ± .005 [.127] .XX ± .01 [.25] ANGLES ± 5 °  — THIRD ANGLE PROJECTION					
07	04-26-13	JBN	RTFI	RTFI	UPDATED DRAWING BORDER & TITLE BLOCK	A41235	DRAWING NUMBER: A41235					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY DAW	DATE -	CHK -	SCALE NONE	SHT 1 OF 1	SIZE A