


DESCRIPTION : ABOVE PCB, DECK AND PUSH ROD LOCATION ARE AS VIEW BY USER.

PRODUCT NO.	PUSH ROD LOCATION		STAND-OFF HEIGHT		CLOSEST TO PCB	FARTHEST FROM PCB	MATING RECEPTACLE	P.C.B SIDE	RECOMMENDED P.C.B LAYOUT	MOUNT STYLE TO PCB AND PUSH ROD SIDE
	DECK CLOSEST TO PCB	DECK FARTHEST TO PCB	DECK CLOSEST TO PCB	DECK FARTHEST TO PCB	EJ HDR ASS'Y	EJ HDR ASS'Y				
Ⓐ 10114582-xxxxxxx					Ⓑ	Ⓒ	Ⓓ			
8501CALF	LEFT	LEFT	5.0	0.5	61125-650CALF	10114583-615CALF	RECEPTACLE PART NO. 91931-31169LF	BELOW	(SEE PAGE 2)	

PART NUMBER DESCRIPTION :

10114582-□□□□□□□

LEAD FREE OPTION: LF

BUTTON COLOR
A: BLACK

C: 13.0 mm

STAND-OFF (LOWER-UPPER DESK)
0: 0.0mm
1: 0.5mmSTAND-OFF (LOWER DESK-PCB)
00: 0.0 mm
06: 0.6 mm
20: 2.0 mm
22: 2.2 mm
40: 4.0 mm
43: 4.3 mm
50: 5.0 mm

PUSH ROD

TOP MOUNT	BOTTOM MOUNT
0: RIGHT-LEFT	5: RIGHT-LEFT
1: LEFT-RIGHT	6: LEFT-RIGHT
2: RIGHT-RIGHT	7: RIGHT-RIGHT
3: LEFT-LEFT	8: LEFT-LEFT

NOTES:

- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
- THE PRODUCTS FOR SUFFIX " LF " MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008 OTHER PRODUCTS ARE COMPLIANT EXCEPT FOR Pb.
- LEAD FREE P/N PACKAGING MEETS GS-14-920 SPECIFICATION
- FINISH (PIN)
UNDER PLATING: 1.27 μ m MIN. Ni
CONTACT AREA: 0.076 μ m MIN. GOLD
SOLDER TAIL: 2.5 μ m MIN. MATTE PURE Sn
- PRODUCT SPEC 110-263
- PACKAGE SPEC GS-14-341

www.fciconnect.com			surface 6.4 ISO 1302	tolerance std ISO 406 ISO 1101	projection 	MM 
Dr	SH MIAO	2011-05-05	ANGULAR LINEAR	0.X	±0.3	size A4
Eng	SH MIAO	2011-05-05		0.XX	±0.15	
Chr	RICK BIAN	2011-05-05		0.XXX	±0.05	
Appr	JOSEPH HSIA	2011-05-05	Product family		10114582	Spec ref
FCI			title			Rev.
			EJECTOR HEADER ASS'Y 3.3V SMT, TYPE 1/2/3			B
			catalog no			sheet 1 of 2

rev	ecn no	dr	date
1	-	-	-
2	-	SH	2010-12-21
A	N11-0095	SH	2011-05-05
B	ELX-N-011457	ZK	2012-04-02
-	-	-	-
-	-	-	-
-	-	-	-

