

DATA SHEET

SKY13299-321LF: GaAs SPDT 7 W Switch **100 MHz–4 GHz**

Features


- Positive voltage control (0/3 to 0/5 V)
- Low insertion loss 0.5 dB typical at 3.5 GHz
- High isolation >35 dB at 3.5 GHz
- High $P_{-0.1\text{ dB}}$ of 38.5 dBm at 3.3 V
- Low gate lag process for fast settling time applications
- Available lead (Pb)-free and RoHS-compliant MSL-1 @ 260 °C per JEDEC J-STD-020

Description

The SKY13299-321LF is a pHEMT GaAs FET IC high power switch packaged in a 12-lead exposed pad plastic package for low-cost commercial applications. This switch is an ideal choice for WiMax and WLAN applications where low loss, high isolation and excellent linearity are key requirements.

NEW

Skyworks offers lead (Pb)-free, RoHS (Restriction of Hazardous Substances)-compliant packaging.


Functional Diagram

Electrical Specifications at 25°C

$V_{CTL} = 0\text{ V/3 V}$, $T = 25\text{ °C}$, $P_{INPUT} = 0\text{ dBm}$, $Z_0 = 50\text{ }\Omega$, unless otherwise noted

Parameter	Frequency	Min.	Typ.	Max.	Unit
Insertion loss	0.1–1.0 GHz		0.30	0.50	dB
	1.0–2.0 GHz		0.40	0.60	dB
	2.0–3.0 GHz		0.45	0.65	dB
	3.0–4.0 GHz		0.65	0.85	dB
Isolation	0.1–1.0 GHz	26	29		dB
	1.0–2.0 GHz	26	29		dB
	2.0–3.0 GHz	26	29		dB
	3.0–4.0 GHz	27	30		dB
Return loss (Insertion loss state) Lower frequency return loss is dependent on DC blocks	0.1–1.0 GHz		20		dB
	1.0–2.0 GHz		17		dB
	2.0–3.0 GHz		20		dB
	3.0–4.0 GHz		17		dB


Innovation to Go™

Now available for purchase online.





Operating Characteristics at 25°C

$V_{CTL} = 0\text{ V}/3\text{ V}$, $T = 25\text{ °C}$, $P_{INPUT} = 0\text{ dBm}$, $Z_0 = 50\text{ }\Omega$, unless otherwise noted


Parameter	Condition	Frequency	Min.	Typ.	Max.	Unit
Switching characteristics						
Rise/fall time	10/90% or 90/10% RF			200		ns
On/off time	50% V_{CTL} to 90/10% RF			300		ns
Settling time	50% CTL to 0.1 dB final value			2		μ s
Harmonics H2, H3	$P_{IN} = 34\text{ dBm CW}$	$F_0 = 900\text{ MHz}$		-80		dBc
Input power for 0.1 dB compression		0.7–4 GHz		38.5		dBm
Control voltages	$V_{CTL\text{ LOW}}$ $V_{CTL\text{ HIGH}}$		0 2.75		0.2 5	V V
Supply currents	$V_{CTL\text{ LOW}}$ $V_{CTL\text{ HIGH}}$ @ 3.3 V and < 30 dBm input $V_{CTL\text{ HIGH}}$ @ 3.3 V and 30–37 dBm input $V_{CTL\text{ HIGH}}$ @ 3.3 V and 37–38 dBm input			5 50 100 200		μ A μ A μ A μ A

Typical Performance Data


$V_{CTL} = 0\text{ V}/3\text{ V}$, $T = 25\text{ °C}$, $P_{INPUT} = 0\text{ dBm}$, $Z_0 = 50\text{ }\Omega$, unless otherwise noted



Frequency = 900 MHz, $P_{IN} = 34\text{ dBm CW}$



Typical Loss vs. Input Power
2500 MHz $V_{CTL} = 3.3$ V




Typical Settling Time

Pin Descriptions

Pin #	Pin Name	Description
1	V_{CTL1}	DC control voltage
2	Gnd	Ground
3	J_1	RF port must be DC blocked
4	Gnd	Ground
5	Gnd	Ground
6	Gnd	Ground
7	J_2	RF port must be DC blocked
8	Gnd	Ground
9	V_{CTL2}	DC control voltage
10	Gnd	Ground
11	RFc	RF common port must be DC blocked
12	Gnd	Ground
Paddle	Paddle	Exposed paddle must be grounded

Pin Out (Top View)

X-ray of pads on bottom of package



Truth Table

V_{CTL1}	V_{CTL2}	RFc to J_1	RFc to J_2
1	0	Insertion loss	Isolation
0	1	Isolation	Insertion loss
1	1	undefined	undefined
0	0	undefined	undefined

0 = 0 to 0.2 V.
1 = 2.75 to 5 V.


Absolute Maximum Ratings

Characteristic	Value
V_{CTL} voltage range	$2.75 \leq V_{CTL} \leq 7$ V
RF input power @ 3.3V	39.5 dBm, $f > 700$ MHz
Operating temperature	-40 °C to +85 °C
Storage temperature	-65 °C to +150 °C


Performance is guaranteed only under the conditions listed in the specifications table and is not guaranteed under the full range(s) described by the Absolute Maximum specifications. Exceeding any of the absolute maximum/minimum specifications may result in permanent damage to the device and will void the warranty.

CAUTION: Although this device is designed to be as robust as possible, ESD (Electrostatic Discharge) can damage this device. This device must be protected at all times from ESD. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection. Industry-standard ESD precautions must be employed at all times.

QFN-12



Part Marking



Recommended Solder Reflow Profiles

Refer to the [“Recommended Solder Reflow Profile”](#) Application Note.

Tape and Reel Information

Refer to the [“Discrete Devices and IC Switch/Attenuators Tape and Reel Package Orientation”](#) Application Note.

Copyright © 2002, 2003, 2004, 2005, 2006, 2007, Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks, the Skyworks symbol, and "Breakthrough Simplicity" are trademarks or registered trademarks of Skyworks Solutions, Inc., in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.