

High Pulse Load MELF Resistors



CMB 0207 specialty MELF resistors with advanced pulse load capability are the perfect choice for the protection of circuitry with signal and mains input lines from surge pulses. The resistors are also suitable for circuits exposed to high levels of electromagnetic interference or electro-static discharge. The applications are in all fields of automotive, telecommunication, industrial and medical equipment.

FEATURES

- Approved to the safety requirements of IEC 60065, 14.1.a* (= VDE 0860, 14.1.a) VDE-REG.-Nr. B583
- AEC-Q200 qualified
- Special carbon film technology
- Up to 10 kV or 17 kW single pulse capability
- Up to tbf. continuous pulse load capability
- ESD capability: 16 kV, human body model
- Compliant to RoHS directive 2002/95/EC
- Find out more about Vishay's Automotive Grade Product requirements at: www.vishay.com/applications


RoHS
COMPLIANT

GREEN
[5-2008]**

APPLICATIONS

- Automotive
- Telecommunication
- Industrial
- Medical equipment

METRIC SIZE

DIN	0207
CECC	RC 6123M

TECHNICAL SPECIFICATIONS


DESCRIPTION	CMB 0207	
CECC size	RC 6123M	
Resistance range	2.2 Ω to 1.5 M Ω	
Resistance tolerance	$\pm 5\%$; $\pm 2\%$; $\pm 1\%$	
Temperature coefficient	see TCR graph	
Operation mode	Standard	Power
Climatic category (LCT/UCT/days)	55/125/56	55/155/56
Rated dissipation, P_{70} ⁽¹⁾	0.4 W	1.0 W ⁽²⁾
Operating voltage, U_{max} , AC/DC	500 V	
Film temperature ⁽³⁾	125 $^{\circ}\text{C}$	155 $^{\circ}\text{C}$
Max. resistance change at P_{70} for resistance range, $\Delta R/R$ after:	2.2 Ω to 10 k Ω	
1000 h	$\leq 0.5\%$	$\leq 1\%$
8000 h	$\leq 1\%$	$\leq 2\%$
225 000 h	t.b.f	-
Permissible voltage against ambient (insulation):	750 V	
1 min; U_{ins}	75 V	
Continuous	$\leq 0.1 \times 10^{-9}/\text{h}$	
Failure rate: FIT _{observed}	$\leq 0.1 \times 10^{-9}/\text{h}$	

Notes

- These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime.
- ⁽¹⁾ The power dissipation on the resistor generates a temperature rise against the local ambient, depending on the heatflow support of the printed-circuit board (thermal resistance). The rated dissipation applies only if the permitted film temperature is not exceeded. Furthermore, a high level of ambient temperature or of power dissipation may raise the temperature of the solder joint, hence special solder alloys or board materials may be required to maintain the reliability of the assembly.
- ⁽²⁾ Specified power rating requires dedicated heat-sink pads.
- ⁽³⁾ Film temperatures above the specified range may be permissible, e.g. 175 $^{\circ}\text{C}$. Please contact the factory for details.

** Please see document "Vishay Material Category Policy": www.vishay.com/doc?99902

DIMENSIONS




DIMENSIONS AND MASS

TYPE	L (mm)	D (mm)	L ₁ min. (mm)	D ₁ (mm)	K (mm)	MASS (mg)
CMB 0207	5.8 + 0/- 0.15	2.2 + 0/- 0.2	3.2	D + 0/- 0.2	1.15 ± 0.1	79

Note

- Color code marking is applied according to IEC 60062 ⁽³⁾ in four bands. Each color band appears as a single solid line, voids are permissible if at least $\frac{2}{3}$ of the band is visible from each radial angle of view. The last color band for tolerance is approximately 50 % wider than the other bands. An interrupted band between the 2nd and 3rd full band indicates the special carbon film type.

PATTERN STYLES FOR MELF RESISTORS



RECOMMENDED SOLDER PAD DIMENSIONS

TYPE	WAVE SOLDERING				REFLOW SOLDERING			
	G (mm)	Y (mm)	X (mm)	Z (mm)	G (mm)	Y (mm)	X (mm)	Z (mm)
CMB 0207	2.8	2.1	2.6	7.0	3.2	1.7	2.4	6.6

Note

- The given solder pad dimensions reflect the considerations for board design and assembly as outlined e.g. in standards IEC 61188-5-x, or in publication IPC-7351. They do not guarantee any supposed thermal properties, however, they will be found adequate for most general applications.

**PART NUMBER AND PRODUCT DESCRIPTION**

Part Number: CMB02070X4701GB200

C	M	B	0	2	0	7	0	X	4	7	0	1	G	B	2	0	0
MODEL/SIZE CMB0207	SPECIAL CHARACTER 0 = Neutral		TCR X = No indication		VALUE 3 digit value 1 digit multiplier Multiplier 8 = *10 ⁻² 9 = *10 ⁻¹ 0 = *10 ⁰ 1 = *10 ¹ 2 = *10 ² 3 = *10 ³ 4 = *10 ⁴					TOLERANCE J = ± 5 % G = ± 2 % F = ± 1 %		PACKAGING B2 B7		SPECIAL Up to 2 digits 00 = Standard			
Product Description: CMB 0207 2 % B2 4K7																	
CMB		0207			2 %					B2		4K7					
MODEL		SIZE			TOLERANCE					PACKAGING		RESISTANCE VALUE					
CMB		0207			± 5 % ± 2 % ± 1 %					B2 B7		100R = 100 Ω 4K7 = 4.7 kΩ					

Note

- Products can be ordered using either the PART NUMBER or the PRODUCT DISCRIPTION.

PACKAGING

MODEL	BLISTER TAPE ON REEL ACC. IEC 60286-3		
	DIAMETER	PIECES/REEL	CODE
CMB 0207	180 mm/7"	2000	B2
	330 mm/13"	7000	B7

TOLERANCE AND RESISTANCE RANGE

DESCRIPTION	RESISTANCE VALUE ⁽¹⁾
TOLERANCE	CMB 0207
± 5 %	2.2 Ω to 15 Ω
± 2 %	16 Ω to 1.5 MΩ
± 1 %	16 Ω to 1 MΩ

Note

- ⁽¹⁾ Please select resistance values for ± 5 % and ± 2 % tolerance from the E24 series.

DESCRIPTION

Production of the CMB 0207 specialty MELF resistor is strictly controlled and follows an extensive set of instructions established for reproducibility. A homogeneous and dense carbon film is deposited on a high grade ceramic body (Al_2O_3). Nickel plated steel termination caps are firmly pressed on the coated rods. Products with a resistance of $15\ \Omega$ or lower are made without trimming, whereas a special laser is used to achieve a target value of $16\ \Omega$ or above by smoothly cutting a helical groove in the resistive layer without damaging the ceramics. The resistor elements are covered by a protective coating designed for electrical, mechanical and climatic protection. The terminations receive a final pure tin on nickel plating. Four color code rings designate the resistance value and tolerance in accordance with **IEC 60 062** ⁽³⁾.

The result of the determined production is verified by an extensive testing procedure performed on 100 % of the individual resistors. Only accepted products are laid directly into the blister tape in accordance with **IEC 60 286-3** ⁽³⁾.

ASSEMBLY

The resistors are suitable for processing on automatic SMD assembly systems. They are suitable for automatic soldering using wave, reflow or vapour phase as shown in **IEC 61760-1** ⁽³⁾. The encapsulation is resistant to all cleaning solvents commonly used in the electronics industry, including alcohols, esters and aqueous solutions. The suitability of conformal coatings, if applied, shall be qualified by appropriate means to ensure the long-term stability of the whole system. The resistors are RoHS compliant, the pure tin plating provides compatibility with lead (Pb)-free and lead containing soldering processes. The immunity of the plating against tin whisker growth has been proven under extensive testing.

All products comply with the **GADSL** ⁽¹⁾ and the **CEPIC-EECA-EICTA** ⁽²⁾ list of legal restrictions on hazardous substances. This includes full compliance with the following directives:

- 2000/53/EC End of Vehicle life Directive (ELV) and Annex II (ELV II)
- 2002/95/EC Restriction of the use of Hazardous Substances Directive (RoHS)
- 2002/96/EC Waste Electrical and Electronic Equipment Directive (WEEE)

Solderability is specified for 2 years after production or requalification. The permitted storage time is 20 years.

Notes

⁽¹⁾ Global Automotive Declarable Substance List, see www.gadsl.org.




⁽²⁾ CEPIC (European Chemical Industry Council), EECA (European Electronic Component Manufacturers Association), EICTA (European trade organisation representing the information and communications technology and consumer electronics), see www.eicta.org/index.php?id=995 → issues → environment policy → chemicals → chemicals for electronics.



⁽³⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents.

APPROVALS

Where applicable the resistors are tested in accordance with **EN 140401-803** which refers to **EN 60115-1**, **EN 140400** and the variety of environmental test procedures of the **IEC 60068** ⁽³⁾ series.

Vishay BEYSCHLAG has achieved “**Approval of Manufacturer**” in accordance with **IEC QC 001002-3, clause 2**. The release certificate for “**Technology Approval Schedule**” in accordance with **CECC 240001** based on **IEC QC 001002-3, clause 6** is granted for the Vishay BEYSCHLAG manufacturing process.

FUNCTIONAL PERFORMANCE

Derating

1.2/50 Pulse

10/700 Pulse



HISTORICAL 12NC INFORMATION

- The resistors have a 12-digit numeric code starting with 2312.
- The subsequent 4 digits indicate the resistor type, specification and packaging; see the 12NC table.
- The remaining 4 digits indicate the resistance value:
 - The first 3 digits indicate the resistance value.
 - The last digit indicates the resistance decade in accordance with the 12NC Indicating Resistance Decade table.

Last Digit of 12NC Indicating Resistance Decade

RESISTANCE DECADE	LAST DIGIT
1 Ω to 9.99 Ω	8
10 Ω to 99.9 Ω	9
100 Ω to 999 Ω	1
1 k Ω to 9.99 k Ω	2
10 k Ω to 99.9 k Ω	3
100 k Ω to 999 k Ω	4
1 M Ω to 9.99 M Ω	5

Historical 12NC Example

The 12NC of a CMB 0207 resistor, value 47 k Ω with $\pm 2\%$ tolerance, supplied in blister tape of 2000 units per reel was: 2312 199 24703.

HISTORICAL 12NC - Resistor type and packaging

DESCRIPTION		CODE 2312	
		BLISTER TAPE ON REEL	
TYPE	TOL.	B2 2000 UNITS	B7 7000 UNITS
CMB 0207	$\pm 5\%$	... 199 3....	... 189 3....
	$\pm 2\%$	... 199 2....	... 189 2....
	$\pm 1\%$	... 199 1....	... 189 1....



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.