




C.S. IMQ



Features

Single pole interlocking barrier terminals block. Base moulded in self extinguishing white polyamide 6 to CEI 23-20, UL 94 V₂ and IEC 695-2-1 to 850°C. Inserts are ultrasonically welded into position. Each pole snap-fits to the next pole enabling required number of poles to be built up to suit individual applications. End plate PA 81 must be used for final end. Suitable for chassis or 15 DIN 46277 rail mounting.

Caratteristiche

Morsettiera faston unipolare componibile. Sul supporto plastico PA 80 realizzato in nylon 6 bianco autoestinguente secondo CEI 23-20, UL 94 V₂ e IEC 695-C-2-1 a 850°C, vengono inseriti contatti metallici in Fe zincato di 3 tipi, sotto specificati, rivettati a ultrasuoni. I singoli blocchetti, vengono successivamente uniti tra di loro ad incastro, utilizzando all'estremità il blocchetto PA 81. Per un elevato numero di poli è possibile montare i blocchetti su un binario 15 DIN 46277.

Technical data

poles as required
rating 16A - 380V
temp. rating 125°C
metal parts screws and tabs in Zinc passivated steel

types

PA 80 VF/F screw/tab to 4 tabs
PA 80 V/F screw to 3 tabs
PA 80 F/F 3 tabs to 3 tabs
PA 81 end plate

Dati tecnici

n° poli senza limite
portata 16A/380V
temp. es. 125°C
ins. met. viti e faston in acciaio zincato passivato

tipi

PA80 VF/F vite - faston / 4 faston
PA80 V/F vite / 3 faston
PA80 F/F 3 faston / 3 faston
PA81 parete terminali

dimensions/dimensioni

A	B	C
29	38	11