

- 1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED
FLAME RETARDANT PER UL 94 V-O.
LOW TEMPERATURE: COLOR BLUE.
HIGH TEMPERATURE: COLOR GREY OR BLACK.
- 2 - TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 - 2 UP TO 4 POSITIONS PRODUCT PACKED IN PLASTIC BOX.
5 UP TO 50 POSITIONS PRODUCT PACKED IN TUBE.
- 4 - TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS

6 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS

"LF" MEANS THE PRODUCT IS LEAD-FREE
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.

b – MANUFACTURING PROCESS COMPATIBILITY



- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.

C – LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004


7 - PRINTING & HOLE PATTERN SEE NEXT SHEET.



PDS: Rev :AG STATUS:Released Printed: Oct 29, 2014

A

A



B

B





FCIconnect.com

C

C

Copyright FCI

mat'l. code SEE SHEET 1				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family DUBOX											
ltr	ecn no	dr	date	tolerances unless		otherwise specified				title BtB RECEPT. VERT SR TMT											
A	F04-0347	DLE	04.09.23	angles linear	±0.3		scale N/A														
B	F05-0230	DLE	05.08.08																		
C	F06-0204	DLE	06.06.20		±2'																
D	F07-0109	DLE	07.01.16	dr	D.LEGRAND		04.09.23		dwg no 75915 size A4												
				engr	P.NIZZI		04.09.23														
				chr	D.LEGRAND		04.09.23														
				appd	P.NIZZI		04.09.23														
sheet index		revision sheet																			

D

D