

CONNETTORE TIPO A (CON MOLLA DI RITEGNO ESTERNA)
CONNECTOR TYPE A (WITH EXTERNAL SPRING)


SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN mm)

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)

SEZIONE B-B
(SECTION B-B)


SEZIONE A-A
(SECTION A-A)



ASSE CONNETTORE
(CONNECTOR CENTER LINE)

ASSE CAVITA'
(CAVITY CENTER LINE)





PASSO 5.0±0.15 TIP.
(PITCH 5.0±0.15 TYP.)



TIP. CAVITA' PER TERMINALI AMP JPT P/N 929939-...
OPPURE 929937-... E RELATIVI GOMMINI
AMP P/N 828904-1, 828905-1, 828536-1.
TAPPO CAVITA' P/N 828906-2
(TYP. CAV. FOR JPT CONT. P/N 929939-... A/O 929937-... AND REL.
SINGLE WIRE SEAL P/N 828904-1, 828905-1, 828536-1
CAVITY PLUG P/N 828906-2)


ROSSO (RED)	-----					
GIALLO (YELLOW)	-----					
MARRONE (BROWN)	-----					
BLU (BLUE)	-----					
VERDE (GREEN)	-----					
NATURALE (NATURAL)	-----					
GRIGIO (GREY)	282342-1	F				
NERO (BLACK)	-----					
COLORE COLOR	NUMERO PART. N°	ASSY REV.	N° (ITEM)	FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	DESCRIZIONE (DESCRIPTION)
			3	\\\\\\\\\\\\\\\\	ACCIAIO INOX (STAINLESS STEEL)	MOLLA (SPRING)
			2	NATURALE (NATURAL)	GOMMA (RUBBER)	GUARNIZIONE (RUBBER GASKET)
			1	\\\\\\\\\\\\\\\\	PA 6.6	BLOCCHETTO (HOUSING)
			CUSTOMER DWG. FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO	
			THIS DRAWING IS UNPUBLISHED		RELEASE FOR PUBLICATION	
			© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING			
N	ECR-14-003472	MP	24MAR 2014			
M1	REVISED PER ECR-09-015789	M.G.	3-8 2009			
M	REVISED FOR ET00-0385-99	M.P.	2-4 01			
L	AGGIOR. CON ET00-0221-96 REVISED FOR ET00-0221-96	A.F.	27-5 '96			
C	AGGIOR. CON ET00-0108-95 REVISED FOR ET00-0108-95	M.P.	11-5 '95			
B	AGG. FOGLIO 2 (ADDED SH.2)	R.M.	3-9 '92			
A	IN PRODUZIONE (IN PRODUCTION)	R.M.	13-10 '92			
1	P/N WAS C-91-51068-2	R.M.	2-3 '92			
REV. (REV.)	REVISIONI (REVISION RECORD)	DIS. (DR)	DATA (DATE)			
				ANGOLI (ANGLES)		
				DIS. 11 APR 91 (DR.)		
				CONT. 13 OCT 92 (CHK)		
				APP. (APP.)		
				LOC. SIZE NUMERO (DWG NO)		
				REV. FOGLIO (SHEET)		
				I A3 C-282342		
				1 DI (OF) 2		

DISTRIBUZIONE
(PRINT DIST.)



- 1 QUOTE APPLICABILI PER SFORMATURA PEZZO (DRAFT PERMITTED TO FACILITATE REMOVAL OF PART FROM THE MOULD)
- 2 MATERIALE LINGUETTE: LEGA DI RAME STAGNATA, ES. OTTONE STAGNATO. (TAB CONTACT MATERIAL: TIN PLATED COPPER ALLOY. E.G. BRASS TIN PLATED)
- 3 MATERIALE BLOCCHETTO: TERMOPLASTICO CARICATO FIBRA VETRO. (HOUSING MATERIAL: THERMOPLASTIC, GLASS FIBER FILLED)

FORMA ALTERNATIVA PERMESSA CON RAGGIO (ALLOWED ALTERNATIVE PROFILE WITH RADIUS)



FINITURA / COLORE (FINISH / COLOUR)		MATERIALE (MATERIAL)		NUMERO (PART NUMBER)	
CUSTOMER DWG. FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO		19	
THIS DRAWING IS UNPUBLISHED		RELEASE FOR PUBLICATION		19	
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING		TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)		DIAM. ISOLANTE (INS. DIA. RANGE)	
± 0.3		RANGO FILO (WIRE RANGE)		SCALA (SCALE)	
ANGOLI (ANGLES)		± 2°		Tyco Electronics Tyco Electronics AMP Italia S.r.l. Corso F.lli Cervi 15, Collegno (TO)	
DIS. (DR.)		DESCRIZIONE (DESCRIPTION)		4 POS. SPLASH PROOF CONN. ASS'Y w. SPEC. POLARIZATION AND SEC. LOCK	
CONT. (CHK)		LOC. SIZE		NUMERO (DWG NO)	
(SEE SHEET 1 OF 2)		I A3		C-282342	
REV. (REV.)		REVISIONI (REVISION RECORD)		DIS. DATA (DR) (DATE)	
APP. (APP.)		REV. (REV.)		FOGLIO (SHEET)	
I A3		C-282342		N 2	

DISTRIBUZIONE (PRINT DIST.)